

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924062

Luminaire Tested: DFN2DIP-4P3F0-050D030US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924062
REPORT IS A COMBINATION OF REPORTS P899045 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-050D030US950-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7255.1 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 71.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924062

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924062

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	52	72	62	55	49	55	50	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2115	2115	2115
5°	2117	2084	2099
10°	2099	2055	2070
15°	2066	2020	2025
20°	2023	1971	1979
25°	1981	1914	1925
30°	1927	1860	1858
35°	1877	1797	1787
40°	1814	1733	1719
45°	1752	1669	1649
50°	1684	1602	1569
55°	1613	1524	1494
60°	1533	1432	1410
65°	1444	1336	1309
70°	1332	1219	1201
75°	1177	1079	1101
80°	989	901	910
85°	697	596	596

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1752 cd/sqm

TEST NUMBER: P924062

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US950-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	2.4
10°-20°	491.5	6.8
20°-30°	722.3	10.0
30°-40°	838.9	11.6
40°-50°	837.9	11.5
50°-60°	730.6	10.1
60°-70°	540.1	7.4
70°-80°	305.6	4.2
80°-90°	83.2	1.1
90°-100°	56.0	0.8
100°-110°	178.0	2.5
110°-120°	304.6	4.2
120°-130°	400.5	5.5
130°-140°	449.6	6.2
140°-150°	440.9	6.1
150°-160°	369.8	5.1
160°-170°	245.3	3.4
170°-180°	85.7	1.2
0°-30°	1388.5	19.1
0°-40°	2227.5	30.7
0°-60°	3796.0	52.3
0°-90°	4724.9	65.1
90°-120°	538.5	7.4
90°-150°	1829.5	25.2
90°-180°	2530.0	34.9
0°-180°	7255.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1856	1856	1856	1856	1856	
5°	1856	1849	1829	1844	1840	176
15°	1767	1756	1733	1740	1731	498
25°	1599	1585	1554	1558	1554	736
35°	1380	1362	1333	1322	1314	862
45°	1123	1110	1083	1064	1057	866
55°	850	839	817	796	787	760
65°	573	562	544	528	519	567
75°	300	296	287	277	280	320
85°	73	71	70	64	62	82
90°	1	10	27	25	26	7
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	



TEST NUMBER: P924062

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1856.0	1856.0	1856.0	1856.0	1856.0
2.5°	1866.8	1857.9	1838.3	1856.0	1852.7
5°	1856.0	1849.0	1829.3	1843.5	1840.2
7.5°	1843.5	1832.9	1813.3	1827.7	1824.0
10°	1824.0	1811.6	1790.2	1804.3	1799.1
12.5°	1797.1	1786.6	1765.2	1774.1	1770.4
15°	1766.8	1756.2	1732.9	1740.2	1731.2
17.5°	1729.3	1718.7	1695.4	1704.3	1695.4
20°	1688.3	1677.7	1652.7	1658.0	1651.0
22.5°	1647.4	1631.2	1608.0	1608.0	1604.3
25°	1599.1	1584.9	1554.5	1558.0	1554.5
27.5°	1545.5	1533.0	1509.9	1504.6	1495.7
30°	1492.1	1477.7	1451.0	1445.7	1438.5
32.5°	1434.9	1424.3	1395.7	1384.9	1377.8
35°	1379.6	1361.8	1333.2	1322.4	1313.6
37.5°	1317.1	1301.1	1272.4	1259.9	1251.1
40°	1253.0	1238.6	1210.0	1194.0	1186.9
42.5°	1190.5	1176.1	1147.7	1129.6	1119.0
45°	1122.7	1110.2	1083.3	1063.8	1056.6
47.5°	1056.6	1044.1	1015.5	995.8	985.2
50°	986.9	978.0	953.0	928.1	919.1
52.5°	919.1	906.6	883.5	863.8	851.3
55°	849.6	838.9	817.4	796.0	787.1
57.5°	779.9	771.0	747.7	726.4	719.1
60°	710.3	703.3	678.3	658.5	653.3
62.5°	642.5	630.0	612.2	594.3	587.2
65°	573.0	562.2	544.4	528.3	519.4
67.5°	501.6	492.6	476.6	464.1	456.9
70°	435.5	428.3	412.2	399.7	392.8
72.5°	367.8	360.5	351.6	339.1	333.8
75°	299.7	296.3	287.2	276.7	280.3
77.5°	239.2	231.9	228.4	223.0	217.8
80°	178.6	176.7	173.1	167.8	164.2
82.5°	121.3	121.3	119.6	112.5	112.5
85°	73.1	71.4	69.6	64.2	62.5
87.5°	32.1	28.6	25.0	19.7	17.8
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P924062

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US950-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P924062

CATALOG NUMBER: DFN2DIP-4P3F0-050D030US950-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.13	12.15	11.95	12.98	14.02	10.69	11.70	11.50	12.54	13.58
	3H	12.80	13.71	13.63	14.56	15.62	12.31	13.22	13.14	14.07	15.13
	4H	13.39	14.25	14.23	15.11	16.18	12.90	13.76	13.74	14.61	15.69
	6H	13.79	14.59	14.65	15.45	16.54	13.29	14.09	14.15	14.95	16.04
	8H	13.90	14.66	14.77	15.54	16.63	13.40	14.16	14.27	15.04	16.13
	12H	13.95	14.67	14.82	15.55	16.67	13.44	14.17	14.32	15.04	16.16
4H	2H	11.61	12.47	12.46	13.32	14.40	11.25	12.11	12.10	12.97	14.04
	3H	13.48	14.20	14.34	15.09	16.18	13.07	13.79	13.93	14.68	15.77
	4H	14.20	14.85	15.07	15.74	16.86	13.77	14.43	14.65	15.31	16.43
	6H	14.72	15.28	15.61	16.19	17.31	14.28	14.85	15.17	15.76	16.88
	8H	14.87	15.40	15.76	16.30	17.44	14.43	14.96	15.32	15.86	17.00
	12H	14.95	15.42	15.86	16.35	17.49	14.50	14.98	15.41	15.90	17.04
8H	4H	14.40	14.93	15.29	15.84	16.97	14.03	14.55	14.92	15.46	16.59
	6H	15.03	15.47	15.95	16.42	17.55	14.65	15.09	15.57	16.03	17.17
	8H	15.25	15.64	16.18	16.58	17.73	14.86	15.25	15.79	16.19	17.34
	12H	15.39	15.73	16.32	16.66	17.86	14.98	15.32	15.91	16.25	17.45
12H	4H	14.39	14.87	15.31	15.79	16.93	14.03	14.50	14.94	15.43	16.57
	6H	15.06	15.45	15.99	16.39	17.54	14.69	15.08	15.62	16.02	17.17
	8H	15.31	15.65	16.24	16.58	17.78	14.93	15.27	15.86	16.20	17.40