

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924066

Luminaire Tested: DFN2DIP-4P3F0-050D040US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924066
REPORT IS A COMBINATION OF REPORTS P899055 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-050D040US950-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8099.4 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924066

CATALOG NUMBER: DFN2DIP-4P3F0-050D040US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924066

CATALOG NUMBER: DFN2DIP-4P3F0-050D040US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54
2	91	83	77	72	84	78	72	68	68	64	60	58	55	52	50	47	45
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2115	2115	2115
5°	2117	2084	2099
10°	2099	2055	2070
15°	2066	2020	2025
20°	2023	1971	1979
25°	1981	1914	1925
30°	1927	1860	1858
35°	1877	1797	1787
40°	1814	1733	1719
45°	1752	1669	1649
50°	1684	1602	1569
55°	1613	1524	1494
60°	1533	1432	1410
65°	1444	1336	1309
70°	1332	1219	1201
75°	1177	1079	1101
80°	989	901	910
85°	697	596	596

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1752 cd/sqm

TEST NUMBER: P924066

CATALOG NUMBER: DFN2DIP-4P3F0-050D040US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	2.2
10°-20°	491.5	6.1
20°-30°	722.3	8.9
30°-40°	838.9	10.4
40°-50°	837.9	10.3
50°-60°	730.6	9.0
60°-70°	540.1	6.7
70°-80°	305.6	3.8
80°-90°	84.1	1.0
90°-100°	74.7	0.9
100°-110°	237.3	2.9
110°-120°	406.1	5.0
120°-130°	534.0	6.6
130°-140°	599.4	7.4
140°-150°	587.8	7.3
150°-160°	493.1	6.1
160°-170°	327.0	4.0
170°-180°	114.3	1.4
0°-30°	1388.5	17.1
0°-40°	2227.5	27.5
0°-60°	3796.0	46.9
0°-90°	4725.7	58.3
90°-120°	718.0	8.9
90°-150°	2439.3	30.1
90°-180°	3374.0	41.7
0°-180°	8099.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1856	1856	1856	1856	1856	
5°	1856	1849	1829	1844	1840	176
15°	1767	1756	1733	1740	1731	498
25°	1599	1585	1554	1558	1554	736
35°	1380	1362	1333	1322	1314	862
45°	1123	1110	1083	1064	1057	866
55°	850	839	817	796	787	760
65°	573	562	544	528	519	567
75°	300	296	287	277	280	320
85°	73	71	70	64	62	82
90°	1	13	36	34	34	8
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	



TEST NUMBER: P924066

CATALOG NUMBER: DFN2DIP-4P3F0-050D040US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1856.0	1856.0	1856.0	1856.0	1856.0
2.5°	1866.8	1857.9	1838.3	1856.0	1852.7
5°	1856.0	1849.0	1829.3	1843.5	1840.2
7.5°	1843.5	1832.9	1813.3	1827.7	1824.0
10°	1824.0	1811.6	1790.2	1804.3	1799.1
12.5°	1797.1	1786.6	1765.2	1774.1	1770.4
15°	1766.8	1756.2	1732.9	1740.2	1731.2
17.5°	1729.3	1718.7	1695.4	1704.3	1695.4
20°	1688.3	1677.7	1652.7	1658.0	1651.0
22.5°	1647.4	1631.2	1608.0	1608.0	1604.3
25°	1599.1	1584.9	1554.5	1558.0	1554.5
27.5°	1545.5	1533.0	1509.9	1504.6	1495.7
30°	1492.1	1477.7	1451.0	1445.7	1438.5
32.5°	1434.9	1424.3	1395.7	1384.9	1377.8
35°	1379.6	1361.8	1333.2	1322.4	1313.6
37.5°	1317.1	1301.1	1272.4	1259.9	1251.1
40°	1253.0	1238.6	1210.0	1194.0	1186.9
42.5°	1190.5	1176.1	1147.7	1129.6	1119.0
45°	1122.7	1110.2	1083.3	1063.8	1056.6
47.5°	1056.6	1044.1	1015.5	995.8	985.2
50°	986.9	978.0	953.0	928.1	919.1
52.5°	919.1	906.6	883.5	863.8	851.3
55°	849.6	838.9	817.4	796.0	787.1
57.5°	779.9	771.0	747.7	726.4	719.1
60°	710.3	703.3	678.3	658.5	653.3
62.5°	642.5	630.0	612.2	594.3	587.2
65°	573.0	562.2	544.4	528.3	519.4
67.5°	501.6	492.6	476.6	464.1	456.9
70°	435.5	428.3	412.2	399.7	392.8
72.5°	367.8	360.5	351.6	339.1	333.8
75°	299.7	296.3	287.2	276.7	280.3
77.5°	239.2	231.9	228.4	223.0	217.8
80°	178.6	176.7	173.1	167.8	164.2
82.5°	121.3	121.3	119.6	112.5	112.5
85°	73.1	71.4	69.6	64.2	62.5
87.5°	32.1	28.6	25.0	19.7	17.8
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7

TEST NUMBER: P924066

CATALOG NUMBER: DFN2DIP-4P3F0-050D040US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8

TEST NUMBER: P924066

CATALOG NUMBER: DFN2DIP-4P3F0-050D040US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.58	11.52	11.46	12.42	13.57	10.13	11.07	11.01	11.98	13.12
	3H	12.24	13.08	13.13	14.00	15.17	11.75	12.59	12.64	13.51	14.68
	4H	12.83	13.63	13.74	14.54	15.73	12.33	13.13	13.24	14.05	15.23
	6H	13.23	13.96	14.15	14.89	16.08	12.73	13.46	13.65	14.39	15.58
	8H	13.33	14.03	14.26	14.98	16.17	12.83	13.53	13.76	14.48	15.67
	12H	13.38	14.05	14.32	14.99	16.20	12.87	13.54	13.81	14.48	15.70
4H	2H	11.04	11.84	11.96	12.76	13.94	10.69	11.49	11.60	12.41	13.59
	3H	12.91	13.58	13.84	14.53	15.72	12.50	13.17	13.43	14.12	15.32
	4H	13.63	14.23	14.56	15.18	16.40	13.20	13.81	14.14	14.75	15.98
	6H	14.14	14.67	15.09	15.63	16.86	13.71	14.23	14.66	15.20	16.42
	8H	14.29	14.78	15.24	15.74	16.98	13.85	14.34	14.80	15.31	16.54
	12H	14.36	14.81	15.34	15.79	17.03	13.92	14.36	14.89	15.34	16.58
8H	4H	13.82	14.32	14.78	15.28	16.51	13.45	13.94	14.40	14.90	16.14
	6H	14.45	14.86	15.43	15.86	17.10	14.07	14.48	15.05	15.48	16.71
	8H	14.67	15.03	15.66	16.02	17.27	14.28	14.64	15.27	15.63	16.88
	12H	14.80	15.12	15.79	16.10	17.40	14.39	14.71	15.38	15.69	16.99
12H	4H	13.81	14.26	14.78	15.23	16.48	13.44	13.89	14.42	14.87	16.11
	6H	14.48	14.84	15.47	15.83	17.09	14.11	14.47	15.10	15.46	16.71
	8H	14.72	15.04	15.71	16.02	17.32	14.34	14.66	15.33	15.64	16.94

END OF REPORT