

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924076

Luminaire Tested: DFN2DIP-4P3F0-050D060US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924076
REPORT IS A COMBINATION OF REPORTS P899076 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-050D060US950-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9120.3 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924076

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924076

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44			38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38			33
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33			28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28			25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25			22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22			19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20			17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18			16
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16			14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2247	2247	2247
5°	2249	2210	2224
10°	2225	2165	2151
15°	2193	2092	2039
20°	2151	1992	1901
25°	2108	1880	1768
30°	2051	1765	1599
35°	1995	1642	1451
40°	1938	1515	1281
45°	1871	1374	1128
50°	1803	1232	978
55°	1731	1081	833
60°	1648	922	685
65°	1551	762	616
70°	1435	612	556
75°	1289	536	505
80°	1077	446	435
85°	731	290	323

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1871 cd/sqm

TEST NUMBER: P924076

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.0
10°-20°	507.2	5.6
20°-30°	712.1	7.8
30°-40°	776.3	8.5
40°-50°	713.5	7.8
50°-60°	560.3	6.1
60°-70°	364.7	4.0
70°-80°	187.7	2.1
80°-90°	53.1	0.6
90°-100°	112.0	1.2
100°-110°	355.9	3.9
110°-120°	609.1	6.7
120°-130°	801.1	8.8
130°-140°	899.2	9.9
140°-150°	881.7	9.7
150°-160°	739.6	8.1
160°-170°	490.5	5.4
170°-180°	171.4	1.9
0°-30°	1404.1	15.4
0°-40°	2180.4	23.9
0°-60°	3454.1	37.9
0°-90°	4059.7	44.5
90°-120°	1077.0	11.8
90°-150°	3659.0	40.1
90°-180°	5061.0	55.5
0°-180°	9120.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1971	1963	1939	1955	1950	187
15°	1875	1855	1795	1761	1743	528
25°	1702	1645	1527	1454	1427	783
35°	1467	1376	1219	1106	1067	918
45°	1199	1079	892	765	722	926
55°	912	772	580	473	439	815
65°	616	471	310	250	244	610
75°	328	203	143	130	128	347
85°	77	39	34	34	34	88
90°	2	20	54	50	52	9
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	

TEST NUMBER: P924076

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1971.4	1971.4	1971.4	1971.4	1971.4
2.5°	1980.3	1971.4	1951.8	1969.7	1966.1
5°	1971.4	1962.6	1939.3	1955.3	1950.1
7.5°	1955.3	1944.7	1919.7	1926.8	1917.8
10°	1933.9	1921.5	1885.9	1880.4	1869.7
12.5°	1907.2	1891.2	1842.9	1832.3	1812.6
15°	1875.1	1855.4	1794.9	1761.0	1743.1
17.5°	1837.6	1809.1	1734.1	1694.9	1666.3
20°	1794.9	1759.1	1669.9	1625.4	1586.0
22.5°	1748.5	1707.4	1603.9	1543.3	1516.6
25°	1702.0	1644.9	1527.2	1454.1	1427.2
27.5°	1646.8	1586.0	1455.8	1371.9	1330.9
30°	1587.9	1520.0	1377.3	1286.4	1238.1
32.5°	1530.8	1448.6	1302.5	1195.4	1150.7
35°	1466.6	1375.6	1218.6	1106.2	1066.9
37.5°	1404.1	1305.9	1140.1	1016.9	972.4
40°	1338.1	1231.1	1057.9	931.3	884.9
42.5°	1270.3	1156.2	975.9	843.8	799.4
45°	1199.0	1079.4	892.1	765.3	722.5
47.5°	1131.2	1004.6	811.9	685.1	645.9
50°	1056.3	929.6	733.3	610.1	572.8
52.5°	983.0	849.2	658.4	540.6	506.8
55°	911.6	772.5	579.7	472.8	438.9
57.5°	838.6	695.8	510.3	410.4	381.8
60°	763.6	620.9	437.0	346.2	317.6
62.5°	690.5	547.8	374.6	289.1	274.8
65°	615.5	471.0	310.4	249.9	244.4
67.5°	544.2	399.6	249.9	219.4	214.1
70°	469.3	330.1	206.9	189.1	181.9
72.5°	397.9	265.8	173.1	158.8	155.2
75°	328.3	203.3	142.7	130.2	128.5
77.5°	258.7	144.4	112.5	105.2	101.6
80°	194.4	103.5	85.6	78.5	78.5
82.5°	135.6	69.6	58.9	55.2	55.2
85°	76.7	39.2	33.9	33.9	33.9
87.5°	28.6	14.2	14.2	12.5	12.5
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4

TEST NUMBER: P924076

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3

TEST NUMBER: P924076

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.39	10.18	10.40	11.19	12.54	5.35	6.14	6.36	7.15	8.50
	3H	11.06	11.76	12.08	12.79	14.16	6.53	7.23	7.55	8.26	9.63
	4H	11.66	12.33	12.69	13.36	14.73	6.97	7.64	8.00	8.67	10.04
	6H	12.08	12.69	13.12	13.72	15.11	7.29	7.90	8.33	8.93	10.32
	8H	12.20	12.78	13.25	13.83	15.22	7.37	7.95	8.42	9.00	10.39
	12H	12.26	12.81	13.31	13.85	15.26	7.41	7.96	8.46	9.00	10.41
4H	2H	9.40	10.07	10.44	11.09	12.47	5.94	6.60	6.98	7.63	9.01
	3H	11.22	11.77	12.27	12.83	14.22	7.28	7.83	8.32	8.89	10.28
	4H	11.91	12.41	12.96	13.46	14.87	7.82	8.32	8.87	9.37	10.78
	6H	12.42	12.85	13.48	13.92	15.33	8.23	8.66	9.29	9.73	11.14
	8H	12.59	12.99	13.65	14.06	15.48	8.35	8.76	9.41	9.82	11.24
	12H	12.68	13.04	13.76	14.12	15.55	8.41	8.78	9.49	9.85	11.28
8H	4H	11.87	12.28	12.93	13.34	14.76	8.09	8.50	9.15	9.56	10.98
	6H	12.43	12.76	13.51	13.87	15.29	8.60	8.93	9.69	10.04	11.46
	8H	12.64	12.94	13.74	14.02	15.46	8.78	9.08	9.88	10.17	11.61
	12H	12.78	13.03	13.87	14.12	15.60	8.90	9.16	9.99	10.24	11.72
12H	4H	11.82	12.19	12.90	13.26	14.69	8.09	8.46	9.17	9.54	10.97
	6H	12.40	12.70	13.50	13.79	15.23	8.65	8.94	9.74	10.03	11.47
	8H	12.62	12.88	13.71	13.96	15.44	8.85	9.11	9.95	10.19	11.67

END OF REPORT