

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902327

Luminaire Tested: DFN2DIP-4P4F0-050D040US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902327
REPORT IS A COMBINATION OF REPORTS P900615 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-050D040US830-FLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8398.1 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 80.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902327
CATALOG NUMBER: DFN2DIP-4P4F0-050D040US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P902327

CATALOG NUMBER: DFN2DIP-4P4F0-050D040US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56		
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	54	53	52	47		
2	90	83	76	71	84	77	72	67	66	62	59	57	54	51	48	46	44	39		
3	82	73	65	59	76	68	61	56	59	54	50	50	46	43	42	39	37	33		
4	75	64	56	50	70	60	53	48	52	47	42	45	40	37	38	35	32	29		
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25		
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25	22		
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19		
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17		
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16		
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1190	1190	1190
5°	1192	1173	1181
10°	1182	1158	1166
15°	1165	1139	1141
20°	1141	1113	1116
25°	1118	1082	1087
30°	1089	1053	1050
35°	1061	1018	1010
40°	1027	984	973
45°	993	949	935
50°	956	913	890
55°	917	870	850
60°	873	820	803
65°	826	768	748
70°	765	705	689
75°	680	630	636
80°	578	534	532
85°	420	367	359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 993 cd/sqm



TEST NUMBER: P902327

CATALOG NUMBER: DFN2DIP-4P4F0-050D040US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.6	2.1
10°-20°	485.6	5.8
20°-30°	713.7	8.5
30°-40°	828.9	9.9
40°-50°	827.8	9.9
50°-60°	721.8	8.6
60°-70°	533.6	6.4
70°-80°	301.9	3.6
80°-90°	81.9	1.0
90°-100°	41.9	0.5
100°-110°	156.4	1.9
110°-120°	414.8	4.9
120°-130°	688.0	8.2
130°-140°	730.8	8.7
140°-150°	679.2	8.1
150°-160°	546.1	6.5
160°-170°	351.9	4.2
170°-180°	121.1	1.4
0°-30°	1371.9	16.3
0°-40°	2200.7	26.2
0°-60°	3750.4	44.7
0°-90°	4667.8	55.6
90°-120°	613.2	7.3
90°-150°	2711.2	32.3
90°-180°	3730.0	44.4
0°-180°	8398.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1834	1834	1834	1834	1834	
5°	1834	1827	1807	1821	1818	174
15°	1746	1735	1712	1719	1710	492
25°	1580	1566	1536	1539	1536	727
35°	1363	1346	1317	1307	1298	851
45°	1109	1097	1070	1051	1044	856
55°	839	829	808	786	778	750
65°	566	555	538	522	513	560
75°	296	293	284	273	277	316
85°	72	70	69	63	62	81
90°	1	11	18	23	25	8
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	668
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	



TEST NUMBER: P902327

CATALOG NUMBER: DFN2DIP-4P4F0-050D040US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.7	1833.7	1833.7	1833.7	1833.7
2.5°	1844.4	1835.6	1816.2	1833.7	1830.4
5°	1833.7	1826.8	1807.3	1821.4	1818.1
7.5°	1821.4	1810.9	1791.5	1805.7	1802.1
10°	1802.1	1789.8	1768.7	1782.6	1777.4
12.5°	1775.6	1765.1	1744.0	1752.8	1749.2
15°	1745.6	1735.1	1712.1	1719.3	1710.4
17.5°	1708.5	1698.1	1675.1	1683.9	1675.1
20°	1668.0	1657.6	1632.9	1638.0	1631.2
22.5°	1627.6	1611.7	1588.7	1588.7	1585.1
25°	1579.9	1565.8	1535.9	1539.3	1535.9
27.5°	1526.9	1514.6	1491.8	1486.5	1477.7
30°	1474.1	1460.0	1433.6	1428.3	1421.3
32.5°	1417.7	1407.2	1378.9	1368.3	1361.2
35°	1363.0	1345.5	1317.2	1306.6	1297.8
37.5°	1301.3	1285.4	1257.2	1244.8	1236.0
40°	1237.9	1223.7	1195.4	1179.7	1172.6
42.5°	1176.2	1162.0	1133.9	1116.1	1105.6
45°	1109.2	1096.8	1070.3	1051.0	1043.9
47.5°	1043.9	1031.5	1003.3	983.8	973.4
50°	975.1	966.3	941.6	916.9	908.0
52.5°	908.0	895.7	872.9	853.5	841.1
55°	839.4	828.8	807.6	786.5	777.7
57.5°	770.5	761.8	738.8	717.7	710.5
60°	701.7	694.8	670.1	650.6	645.5
62.5°	634.8	622.5	604.8	587.2	580.1
65°	566.1	555.4	537.8	522.0	513.1
67.5°	495.6	486.6	470.9	458.5	451.4
70°	430.3	423.2	407.3	394.9	388.0
72.5°	363.4	356.2	347.4	335.1	329.8
75°	296.1	292.8	283.8	273.3	276.9
77.5°	236.3	229.1	225.6	220.4	215.2
80°	176.4	174.6	171.0	165.8	162.2
82.5°	119.9	119.9	118.2	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.8	28.3	24.7	19.4	17.6
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.6	56.2	66.3	69.9
107.5°	345.3	368.3	58.1	68.1	71.8
110°	407.9	427.2	161.2	69.1	72.7



TEST NUMBER: P902327

CATALOG NUMBER: DFN2DIP-4P4F0-050D040US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.1	141.8	75.6
117.5°	583.7	602.1	617.8	486.1	244.9
120°	644.5	658.3	674.9	686.0	561.7
122.5°	696.0	710.8	729.2	734.7	735.7
125°	748.5	760.5	778.0	784.5	787.2
127.5°	796.4	809.3	823.1	832.4	833.2
130°	841.5	856.3	866.3	876.5	875.6
132.5°	887.5	899.6	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.5	956.7
137.5°	966.7	977.7	987.0	996.2	993.4
140°	1006.3	1013.7	1023.8	1032.1	1027.5
142.5°	1039.5	1045.9	1057.9	1065.2	1060.6
145°	1074.5	1073.6	1089.1	1095.6	1091.0
147.5°	1104.8	1102.0	1117.7	1122.3	1118.7
150°	1134.3	1127.8	1142.6	1148.1	1143.5
152.5°	1159.1	1151.8	1165.5	1171.1	1164.7
155°	1183.1	1174.9	1185.9	1191.4	1184.0
157.5°	1202.4	1195.0	1203.4	1209.8	1202.4
160°	1219.0	1213.4	1219.0	1224.5	1218.0
162.5°	1233.7	1228.2	1232.8	1239.3	1231.0
165°	1246.6	1241.1	1243.9	1250.3	1243.9
167.5°	1256.8	1251.1	1254.1	1260.5	1252.2
170°	1265.1	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.1	1267.0	1273.4	1265.1
175°	1275.1	1268.7	1270.5	1277.0	1267.8
177.5°	1277.0	1270.5	1271.5	1278.0	1269.7
180°	1272.4	1272.4	1272.4	1272.4	1272.4



TEST NUMBER: P902327
 CATALOG NUMBER: DFN2DIP-4P4F0-050D040US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.39	9.31	9.30	10.24	11.42	7.95	8.86	8.86	9.79	10.98
	3H	10.06	10.88	10.98	11.82	13.03	9.57	10.39	10.49	11.33	12.54
	4H	10.66	11.43	11.59	12.38	13.60	10.16	10.94	11.10	11.88	13.10
	6H	11.07	11.78	12.01	12.73	13.96	10.57	11.28	11.51	12.23	13.46
	8H	11.17	11.86	12.13	12.82	14.05	10.67	11.35	11.63	12.32	13.55
	12H	11.23	11.87	12.19	12.83	14.09	10.72	11.36	11.68	12.32	13.58
4H	2H	8.86	9.64	9.80	10.58	11.80	8.51	9.28	9.45	10.23	11.45
	3H	10.74	11.39	11.69	12.36	13.60	10.33	10.98	11.28	11.95	13.19
	4H	11.46	12.05	12.42	13.02	14.28	11.04	11.63	12.00	12.59	13.86
	6H	11.98	12.49	12.96	13.48	14.74	11.55	12.06	12.53	13.05	14.31
	8H	12.14	12.61	13.11	13.60	14.87	11.70	12.18	12.68	13.16	14.44
	12H	12.22	12.65	13.21	13.65	14.93	11.77	12.20	12.76	13.20	14.48
8H	4H	11.66	12.14	12.64	13.12	14.40	11.29	11.76	12.26	12.75	14.02
	6H	12.30	12.70	13.30	13.72	15.00	11.92	12.31	12.92	13.34	14.61
	8H	12.53	12.88	13.54	13.89	15.18	12.14	12.48	13.14	13.50	14.79
	12H	12.67	12.97	13.68	13.98	15.32	12.25	12.56	13.27	13.57	14.90
12H	4H	11.65	12.08	12.64	13.08	14.36	11.28	11.71	12.28	12.71	13.99
	6H	12.33	12.68	13.34	13.69	14.99	11.96	12.31	12.97	13.32	14.61
	8H	12.58	12.89	13.59	13.90	15.23	12.20	12.51	13.21	13.52	14.85