

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902339

Luminaire Tested: DFN2DIP-4P4F0-050D070US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902339
REPORT IS A COMBINATION OF REPORTS P900651 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-050D070US830-FLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11197.4 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 111.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902339
CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P902339

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	49	49	49	42
1	96	92	88	84	87	84	80	78	69	67	65	55	54	52	43	42	41	41	41	41	35
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34	34	34	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	29	29	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	25	25	25	21
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	22	22	22	19
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	19	19	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	15	15	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	14	14	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1190	1190	1190
5°	1192	1173	1181
10°	1182	1158	1166
15°	1165	1139	1141
20°	1141	1113	1116
25°	1118	1082	1087
30°	1089	1053	1050
35°	1061	1018	1010
40°	1027	984	973
45°	993	949	935
50°	956	913	890
55°	917	870	850
60°	873	820	803
65°	826	768	748
70°	765	705	689
75°	680	630	636
80°	578	534	532
85°	420	367	359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1150 cd/sqm



TEST NUMBER: P902339

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.6	1.5
10°-20°	485.6	4.3
20°-30°	713.7	6.4
30°-40°	828.9	7.4
40°-50°	827.8	7.4
50°-60°	721.8	6.4
60°-70°	533.6	4.8
70°-80°	301.9	2.7
80°-90°	83.6	0.7
90°-100°	73.4	0.7
100°-110°	273.7	2.4
110°-120°	725.9	6.5
120°-130°	1204.0	10.8
130°-140°	1278.9	11.4
140°-150°	1188.6	10.6
150°-160°	955.6	8.5
160°-170°	615.8	5.5
170°-180°	211.9	1.9
0°-30°	1371.9	12.3
0°-40°	2200.7	19.7
0°-60°	3750.4	33.5
0°-90°	4669.5	41.7
90°-120°	1073.0	9.6
90°-150°	4744.6	42.4
90°-180°	6528.0	58.3
0°-180°	11197.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1834	1834	1834	1834	1834	
5°	1834	1827	1807	1821	1818	174
15°	1746	1735	1712	1719	1710	492
25°	1580	1566	1536	1539	1536	727
35°	1363	1346	1317	1307	1298	851
45°	1109	1097	1070	1051	1044	856
55°	839	829	808	786	778	750
65°	566	555	538	522	513	560
75°	296	293	284	273	277	316
85°	72	70	69	63	62	81
90°	2	19	32	40	44	10
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1362	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2182	2172	2177	2188	2177	616
175°	2232	2220	2224	2235	2219	212
180°	2227	2227	2227	2227	2227	



TEST NUMBER: P902339

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.7	1833.7	1833.7	1833.7	1833.7
2.5°	1844.4	1835.6	1816.2	1833.7	1830.4
5°	1833.7	1826.8	1807.3	1821.4	1818.1
7.5°	1821.4	1810.9	1791.5	1805.7	1802.1
10°	1802.1	1789.8	1768.7	1782.6	1777.4
12.5°	1775.6	1765.1	1744.0	1752.8	1749.2
15°	1745.6	1735.1	1712.1	1719.3	1710.4
17.5°	1708.5	1698.1	1675.1	1683.9	1675.1
20°	1668.0	1657.6	1632.9	1638.0	1631.2
22.5°	1627.6	1611.7	1588.7	1588.7	1585.1
25°	1579.9	1565.8	1535.9	1539.3	1535.9
27.5°	1526.9	1514.6	1491.8	1486.5	1477.7
30°	1474.1	1460.0	1433.6	1428.3	1421.3
32.5°	1417.7	1407.2	1378.9	1368.3	1361.2
35°	1363.0	1345.5	1317.2	1306.6	1297.8
37.5°	1301.3	1285.4	1257.2	1244.8	1236.0
40°	1237.9	1223.7	1195.4	1179.7	1172.6
42.5°	1176.2	1162.0	1133.9	1116.1	1105.6
45°	1109.2	1096.8	1070.3	1051.0	1043.9
47.5°	1043.9	1031.5	1003.3	983.8	973.4
50°	975.1	966.3	941.6	916.9	908.0
52.5°	908.0	895.7	872.9	853.5	841.1
55°	839.4	828.8	807.6	786.5	777.7
57.5°	770.5	761.8	738.8	717.7	710.5
60°	701.7	694.8	670.1	650.6	645.5
62.5°	634.8	622.5	604.8	587.2	580.1
65°	566.1	555.4	537.8	522.0	513.1
67.5°	495.6	486.6	470.9	458.5	451.4
70°	430.3	423.2	407.3	394.9	388.0
72.5°	363.4	356.2	347.4	335.1	329.8
75°	296.1	292.8	283.8	273.3	276.9
77.5°	236.3	229.1	225.6	220.4	215.2
80°	176.4	174.6	171.0	165.8	162.2
82.5°	119.9	119.9	118.2	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.8	28.3	24.7	19.4	17.6
90°	1.5	19.3	32.1	40.3	43.5
92.5°	40.3	33.8	38.6	41.9	43.5
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.2	644.4	101.6	119.2	125.7
110°	713.9	747.5	282.0	120.9	127.2



TEST NUMBER: P902339

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.8	994.1	248.2	132.2
117.5°	1021.5	1053.7	1081.2	850.6	428.6
120°	1127.8	1152.0	1181.1	1200.4	982.9
122.5°	1218.0	1243.8	1276.2	1285.7	1287.4
125°	1309.9	1330.9	1361.5	1372.8	1377.5
127.5°	1393.6	1416.2	1440.5	1456.6	1458.1
130°	1472.6	1498.5	1516.1	1533.9	1532.4
132.5°	1553.2	1574.2	1591.9	1606.4	1604.9
135°	1620.9	1646.7	1661.1	1677.3	1674.1
137.5°	1691.7	1711.1	1727.3	1743.4	1738.6
140°	1761.0	1774.0	1791.6	1806.1	1798.1
142.5°	1819.1	1830.4	1851.2	1864.1	1856.1
145°	1880.4	1878.7	1906.0	1917.3	1909.3
147.5°	1933.3	1928.6	1956.0	1964.0	1957.7
150°	1985.0	1973.8	1999.6	2009.1	2001.1
152.5°	2028.4	2015.6	2039.8	2049.5	2038.2
155°	2070.4	2056.0	2075.3	2084.9	2072.1
157.5°	2104.2	2091.4	2105.9	2117.2	2104.2
160°	2133.4	2123.5	2133.4	2142.9	2131.6
162.5°	2159.0	2149.4	2157.4	2168.7	2154.2
165°	2181.5	2172.0	2176.7	2188.0	2176.7
167.5°	2199.3	2189.5	2194.5	2205.8	2191.3
170°	2213.8	2204.1	2207.3	2218.7	2204.1
172.5°	2223.5	2213.8	2217.1	2228.4	2213.8
175°	2231.5	2220.2	2223.5	2234.7	2218.7
177.5°	2234.7	2223.5	2225.2	2236.5	2221.9
180°	2226.7	2226.7	2226.7	2226.7	2226.7



TEST NUMBER: P902339
 CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.08	7.87	8.10	8.90	10.28	6.63	7.42	7.66	8.46	9.84
	3H	8.74	9.45	9.77	10.49	11.89	8.25	8.95	9.28	10.00	11.40
	4H	9.32	10.00	10.37	11.04	12.45	8.83	9.50	9.88	10.55	11.96
	6H	9.73	10.34	10.78	11.39	12.82	9.22	9.84	10.28	10.89	12.32
	8H	9.83	10.42	10.89	11.48	12.90	9.33	9.92	10.39	10.98	12.40
	12H	9.88	10.44	10.95	11.50	12.94	9.37	9.93	10.44	10.99	12.43
4H	2H	7.53	8.20	8.58	9.25	10.66	7.17	7.85	8.23	8.89	10.30
	3H	9.39	9.96	10.46	11.03	12.45	8.99	9.55	10.05	10.62	12.05
	4H	10.11	10.62	11.18	11.69	13.13	9.69	10.20	10.75	11.26	12.71
	6H	10.63	11.07	11.70	12.16	13.60	10.20	10.64	11.27	11.72	13.16
	8H	10.78	11.19	11.86	12.27	13.73	10.34	10.75	11.42	11.83	13.29
	12H	10.85	11.22	11.95	12.32	13.78	10.40	10.77	11.50	11.87	13.33
8H	4H	10.30	10.72	11.38	11.79	13.25	9.93	10.34	11.00	11.42	12.87
	6H	10.94	11.28	12.04	12.40	13.85	10.55	10.90	11.65	12.02	13.47
	8H	11.16	11.46	12.27	12.56	14.04	10.77	11.07	11.88	12.17	13.64
	12H	11.29	11.56	12.40	12.66	14.17	10.88	11.15	11.99	12.24	13.76
12H	4H	10.28	10.66	11.38	11.75	13.21	9.92	10.29	11.01	11.38	12.85
	6H	10.97	11.27	12.07	12.37	13.84	10.60	10.90	11.70	12.00	13.47
	8H	11.21	11.47	12.32	12.57	14.08	10.83	11.09	11.94	12.19	13.70