

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902380

Luminaire Tested: DFN2DIP-4P4F0-070D050US830-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902380
REPORT IS A COMBINATION OF REPORTS P899112 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D050US830-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9778.8 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 114.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902380

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902380

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1769	1769	1769
5°	1772	1742	1753
10°	1755	1708	1696
15°	1731	1652	1609
20°	1699	1575	1501
25°	1666	1488	1397
30°	1622	1399	1265
35°	1579	1303	1149
40°	1536	1204	1016
45°	1485	1094	895
50°	1433	983	777
55°	1378	864	664
60°	1315	740	547
65°	1242	613	493
70°	1153	496	447
75°	1042	438	408
80°	882	370	356
85°	616	249	272

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1485 cd/sqm

TEST NUMBER: P902380

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.6	2.6
10°-20°	701.6	7.2
20°-30°	985.0	10.1
30°-40°	1073.7	11.0
40°-50°	986.9	10.1
50°-60°	775.0	7.9
60°-70°	504.5	5.2
70°-80°	259.7	2.7
80°-90°	70.5	0.7
90°-100°	92.2	0.9
100°-110°	293.0	3.0
110°-120°	501.5	5.1
120°-130°	659.5	6.7
130°-140°	740.3	7.6
140°-150°	725.9	7.4
150°-160°	609.0	6.2
160°-170°	403.9	4.1
170°-180°	141.2	1.4
0°-30°	1942.1	19.9
0°-40°	3015.8	30.8
0°-60°	4777.7	48.9
0°-90°	5612.3	57.4
90°-120°	886.7	9.1
90°-150°	3012.5	30.8
90°-180°	4167.0	42.6
0°-180°	9778.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2727	2727	2727	2727	2727	
5°	2727	2714	2682	2705	2697	259
15°	2594	2566	2483	2436	2411	731
25°	2354	2275	2112	2011	1974	1083
35°	2028	1903	1686	1530	1476	1270
45°	1658	1493	1234	1059	999	1281
55°	1261	1068	802	654	607	1127
65°	851	651	429	346	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	122
90°	1	16	44	41	43	10
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	



TEST NUMBER: P902380

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.9	2726.9	2726.9	2726.9	2726.9
2.5°	2739.1	2726.9	2699.6	2724.5	2719.5
5°	2726.9	2714.5	2682.4	2704.6	2697.3
7.5°	2704.6	2689.9	2655.4	2665.0	2652.8
10°	2675.0	2657.8	2608.5	2600.9	2586.2
12.5°	2638.1	2615.8	2549.1	2534.4	2507.2
15°	2593.6	2566.4	2482.6	2435.7	2411.1
17.5°	2541.8	2502.3	2398.6	2344.3	2304.8
20°	2482.6	2433.1	2309.8	2248.2	2193.8
22.5°	2418.5	2361.6	2218.4	2134.6	2097.7
25°	2354.3	2275.2	2112.3	2011.3	1974.2
27.5°	2277.8	2193.8	2013.6	1897.7	1840.9
30°	2196.4	2102.4	1905.0	1779.3	1712.6
32.5°	2117.3	2003.8	1801.6	1653.4	1591.6
35°	2028.5	1902.6	1685.6	1530.1	1475.6
37.5°	1942.2	1806.3	1577.0	1406.5	1345.0
40°	1850.8	1702.9	1463.3	1288.2	1224.0
42.5°	1757.1	1599.2	1349.9	1167.2	1105.7
45°	1658.4	1492.9	1234.0	1058.6	999.4
47.5°	1564.6	1389.5	1122.9	947.5	893.3
50°	1460.9	1285.8	1014.3	843.9	792.3
52.5°	1359.6	1174.5	910.6	747.7	700.9
55°	1260.9	1068.5	801.9	654.0	607.2
57.5°	1159.9	962.4	705.9	567.6	528.1
60°	1056.2	858.8	604.5	478.9	439.3
62.5°	955.1	757.7	518.1	399.8	380.1
65°	851.4	651.4	429.4	345.6	338.0
67.5°	752.7	552.7	345.6	303.4	296.1
70°	649.0	456.6	286.2	261.6	251.6
72.5°	550.4	367.6	239.3	219.7	214.7
75°	454.0	281.2	197.4	180.1	177.8
77.5°	357.9	199.7	155.5	145.5	140.6
80°	268.9	143.2	118.4	108.7	108.7
82.5°	187.5	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3



TEST NUMBER: P902380

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P902380

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.81	10.70	10.71	11.62	12.78	5.77	6.67	6.67	7.58	8.74
	3H	11.50	12.30	12.41	13.22	14.41	6.97	7.77	7.88	8.69	9.88
	4H	12.11	12.87	13.04	13.80	15.00	7.42	8.18	8.35	9.10	10.30
	6H	12.54	13.24	13.48	14.17	15.38	7.75	8.44	8.68	9.38	10.59
	8H	12.67	13.34	13.62	14.29	15.50	7.84	8.50	8.78	9.45	10.66
	12H	12.74	13.37	13.69	14.31	15.55	7.89	8.52	8.84	9.46	10.69
4H	2H	9.84	10.59	10.77	11.52	12.72	6.38	7.13	7.31	8.06	9.26
	3H	11.68	12.31	12.62	13.26	14.48	7.74	8.36	8.68	9.32	10.54
	4H	12.38	12.95	13.33	13.90	15.14	8.29	8.86	9.24	9.81	11.05
	6H	12.90	13.39	13.86	14.37	15.61	8.71	9.20	9.68	10.18	11.42
	8H	13.08	13.54	14.05	14.51	15.76	8.84	9.30	9.81	10.27	11.53
	12H	13.18	13.60	14.17	14.58	15.84	8.91	9.33	9.90	10.31	11.57
8H	4H	12.35	12.81	13.32	13.78	15.03	8.58	9.04	9.54	10.01	11.26
	6H	12.92	13.30	13.92	14.32	15.57	9.10	9.48	10.09	10.49	11.74
	8H	13.15	13.48	14.14	14.48	15.75	9.29	9.63	10.29	10.63	11.90
	12H	13.29	13.59	14.29	14.58	15.90	9.42	9.71	10.42	10.70	12.02
12H	4H	12.31	12.72	13.29	13.71	14.96	8.58	9.00	9.57	9.99	11.24
	6H	12.90	13.24	13.90	14.24	15.50	9.15	9.49	10.15	10.49	11.76
	8H	13.13	13.42	14.13	14.42	15.73	9.37	9.66	10.37	10.65	11.97

END OF REPORT