

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913335

Luminaire Tested: DFN2DIP-HX2F0-020D030US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913335
REPORT IS A COMBINATION OF REPORTS P900681 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D030US927-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3921.3 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913335
CATALOG NUMBER: DFN2DIP-HX2F0-020D030US927-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P913335
 CATALOG NUMBER: DFN2DIP-HX2F0-020D030US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	21
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1453	1453	1453
5°	1453	1429	1439
10°	1439	1406	1417
15°	1415	1380	1384
20°	1384	1344	1350
25°	1353	1302	1311
30°	1315	1263	1263
35°	1279	1217	1212
40°	1235	1171	1163
45°	1191	1124	1113
50°	1142	1075	1056
55°	1091	1019	1002
60°	1034	952	941
65°	970	883	868
70°	890	798	790
75°	780	696	714
80°	645	567	575
85°	437	355	357

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1191 cd/sqm



TEST NUMBER: P913335

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	1.5
10°-20°	163.3	4.2
20°-30°	239.9	6.1
30°-40°	278.7	7.1
40°-50°	278.3	7.1
50°-60°	242.7	6.2
60°-70°	179.4	4.6
70°-80°	101.5	2.6
80°-90°	28.2	0.7
90°-100°	26.5	0.7
100°-110°	98.6	2.5
110°-120°	261.5	6.7
120°-130°	433.7	11.1
130°-140°	460.7	11.7
140°-150°	428.1	10.9
150°-160°	344.2	8.8
160°-170°	221.8	5.7
170°-180°	76.3	1.9
0°-30°	461.2	11.8
0°-40°	739.9	18.9
0°-60°	1260.8	32.2
0°-90°	1569.9	40.0
90°-120°	386.5	9.9
90°-150°	1709.0	43.6
90°-180°	2351.0	60.0
0°-180°	3921.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	616	616	616	616	616	
5°	616	614	608	612	611	59
15°	587	583	576	578	575	165
25°	531	526	516	518	516	244
35°	458	452	443	439	436	286
45°	373	369	360	353	351	288
55°	282	279	272	264	261	252
65°	190	187	181	176	172	188
75°	100	98	95	92	93	106
85°	24	24	23	21	21	27
90°	1	7	12	15	16	4
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	



TEST NUMBER: P913335

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	616.5	616.5	616.5	616.5	616.5
2.5°	620.0	617.1	610.5	616.5	615.4
5°	616.5	614.2	607.6	612.4	611.2
7.5°	612.4	608.8	602.3	607.0	605.9
10°	605.9	601.7	594.6	599.3	597.5
12.5°	596.9	593.4	586.3	589.2	588.0
15°	586.8	583.4	575.6	578.0	575.0
17.5°	574.4	570.9	563.2	566.1	563.2
20°	560.8	557.2	548.9	550.7	548.3
22.5°	547.2	541.9	534.1	534.1	532.9
25°	531.2	526.4	516.3	517.5	516.3
27.5°	513.3	509.2	501.5	499.8	496.8
30°	495.6	490.8	482.0	480.2	477.8
32.5°	476.6	473.1	463.6	460.0	457.6
35°	458.3	452.3	442.8	439.3	436.3
37.5°	437.5	432.1	422.6	418.5	415.5
40°	416.1	411.4	401.9	396.6	394.2
42.5°	395.4	390.6	381.2	375.3	371.7
45°	372.9	368.8	359.8	353.3	350.9
47.5°	350.9	346.8	337.3	330.7	327.3
50°	327.8	324.9	316.6	308.2	305.3
52.5°	305.3	301.1	293.4	286.9	282.8
55°	282.2	278.6	271.5	264.4	261.4
57.5°	259.0	256.1	248.3	241.3	238.8
60°	235.9	233.6	225.3	218.7	217.0
62.5°	213.4	209.2	203.4	197.4	195.0
65°	190.3	186.7	180.9	175.5	172.5
67.5°	166.6	163.6	158.3	154.2	151.8
70°	144.7	142.3	136.9	132.8	130.5
72.5°	122.2	119.8	116.8	112.6	110.9
75°	99.6	98.5	95.4	91.9	93.1
77.5°	79.5	77.1	75.8	74.1	72.3
80°	59.3	58.7	57.5	55.7	54.5
82.5°	40.3	40.3	39.8	37.4	37.4
85°	24.2	23.7	23.1	21.3	20.8
87.5°	10.7	9.5	8.3	6.6	5.9
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9



TEST NUMBER: P913335

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1



TEST NUMBER: P913335
 CATALOG NUMBER: DFN2DIP-HX2F0-020D030US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.43	8.21	8.47	9.26	10.66	7.01	7.79	8.05	8.84	10.24
	3H	9.06	9.76	10.11	10.81	12.24	8.60	9.30	9.65	10.36	11.78
	4H	9.63	10.29	10.69	11.35	12.78	9.17	9.83	10.23	10.89	12.32
	6H	10.01	10.62	11.08	11.68	13.12	9.55	10.16	10.62	11.22	12.66
	8H	10.10	10.68	11.17	11.76	13.20	9.64	10.22	10.72	11.30	12.74
	12H	10.14	10.69	11.22	11.76	13.22	9.67	10.23	10.75	11.29	12.76
4H	2H	7.88	8.54	8.94	9.59	11.03	7.54	8.20	8.61	9.26	10.69
	3H	9.71	10.26	10.78	11.34	12.79	9.32	9.88	10.40	10.96	12.40
	4H	10.40	10.90	11.48	11.98	13.44	10.00	10.51	11.08	11.58	13.05
	6H	10.89	11.32	11.97	12.42	13.88	10.49	10.92	11.58	12.02	13.48
	8H	11.02	11.43	12.11	12.52	13.99	10.62	11.03	11.71	12.12	13.60
	12H	11.08	11.45	12.18	12.55	14.03	10.67	11.04	11.78	12.14	13.62
8H	4H	10.58	10.98	11.67	12.07	13.55	10.23	10.63	11.31	11.72	13.20
	6H	11.18	11.51	12.29	12.64	14.12	10.82	11.16	11.93	12.29	13.76
	8H	11.38	11.67	12.50	12.79	14.28	11.02	11.32	12.14	12.43	13.92
	12H	11.49	11.75	12.61	12.86	14.39	11.12	11.38	12.24	12.49	14.02
12H	4H	10.56	10.92	11.66	12.03	13.51	10.21	10.58	11.32	11.68	13.16
	6H	11.20	11.49	12.32	12.61	14.10	10.86	11.15	11.98	12.26	13.76
	8H	11.42	11.68	12.54	12.79	14.32	11.07	11.33	12.19	12.44	13.97