

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913343

Luminaire Tested: DFN2DIP-HX2F0-020D050US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913343
REPORT IS A COMBINATION OF REPORTS P900701 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D050US927-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5489.8 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913343

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913343

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1453	1453	1453
5°	1453	1429	1439
10°	1439	1406	1417
15°	1415	1380	1384
20°	1384	1344	1350
25°	1353	1302	1311
30°	1315	1263	1263
35°	1279	1217	1212
40°	1235	1171	1163
45°	1191	1124	1113
50°	1142	1075	1056
55°	1091	1019	1002
60°	1034	952	941
65°	970	883	868
70°	890	798	790
75°	780	696	714
80°	645	567	575
85°	437	355	357

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1223 cd/sqm

TEST NUMBER: P913343

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	1.1
10°-20°	163.3	3.0
20°-30°	239.9	4.4
30°-40°	278.7	5.1
40°-50°	278.3	5.1
50°-60°	242.7	4.4
60°-70°	179.4	3.3
70°-80°	101.5	1.8
80°-90°	29.1	0.5
90°-100°	44.1	0.8
100°-110°	164.3	3.0
110°-120°	435.8	7.9
120°-130°	722.8	13.2
130°-140°	767.8	14.0
140°-150°	713.6	13.0
150°-160°	573.7	10.5
160°-170°	369.7	6.7
170°-180°	127.2	2.3
0°-30°	461.2	8.4
0°-40°	739.9	13.5
0°-60°	1260.8	23.0
0°-90°	1570.9	28.6
90°-120°	644.2	11.7
90°-150°	2848.4	51.9
90°-180°	3919.0	71.4
0°-180°	5489.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	616	616	616	616	616	
5°	616	614	608	612	611	59
15°	587	583	576	578	575	165
25°	531	526	516	518	516	244
35°	458	452	443	439	436	286
45°	373	369	360	353	351	288
55°	282	279	272	264	261	252
65°	190	187	181	176	172	188
75°	100	98	95	92	93	106
85°	24	24	23	21	21	27
90°	1	12	19	24	26	5
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	573	597	149	79	548
125°	786	799	817	824	827	701
135°	973	989	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1252	1244	573
165°	1310	1304	1307	1314	1307	370
175°	1340	1333	1335	1342	1332	127
180°	1337	1337	1337	1337	1337	

TEST NUMBER: P913343

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	616.5	616.5	616.5	616.5	616.5
2.5°	620.0	617.1	610.5	616.5	615.4
5°	616.5	614.2	607.6	612.4	611.2
7.5°	612.4	608.8	602.3	607.0	605.9
10°	605.9	601.7	594.6	599.3	597.5
12.5°	596.9	593.4	586.3	589.2	588.0
15°	586.8	583.4	575.6	578.0	575.0
17.5°	574.4	570.9	563.2	566.1	563.2
20°	560.8	557.2	548.9	550.7	548.3
22.5°	547.2	541.9	534.1	534.1	532.9
25°	531.2	526.4	516.3	517.5	516.3
27.5°	513.3	509.2	501.5	499.8	496.8
30°	495.6	490.8	482.0	480.2	477.8
32.5°	476.6	473.1	463.6	460.0	457.6
35°	458.3	452.3	442.8	439.3	436.3
37.5°	437.5	432.1	422.6	418.5	415.5
40°	416.1	411.4	401.9	396.6	394.2
42.5°	395.4	390.6	381.2	375.3	371.7
45°	372.9	368.8	359.8	353.3	350.9
47.5°	350.9	346.8	337.3	330.7	327.3
50°	327.8	324.9	316.6	308.2	305.3
52.5°	305.3	301.1	293.4	286.9	282.8
55°	282.2	278.6	271.5	264.4	261.4
57.5°	259.0	256.1	248.3	241.3	238.8
60°	235.9	233.6	225.3	218.7	217.0
62.5°	213.4	209.2	203.4	197.4	195.0
65°	190.3	186.7	180.9	175.5	172.5
67.5°	166.6	163.6	158.3	154.2	151.8
70°	144.7	142.3	136.9	132.8	130.5
72.5°	122.2	119.8	116.8	112.6	110.9
75°	99.6	98.5	95.4	91.9	93.1
77.5°	79.5	77.1	75.8	74.1	72.3
80°	59.3	58.7	57.5	55.7	54.5
82.5°	40.3	40.3	39.8	37.4	37.4
85°	24.2	23.7	23.1	21.3	20.8
87.5°	10.7	9.5	8.3	6.6	5.9
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.2
100°	171.3	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.7	70.7
105°	294.1	323.1	59.0	69.6	73.5
107.5°	362.7	386.8	61.0	71.5	75.5
110°	428.6	448.8	169.3	72.6	76.4

TEST NUMBER: P913343

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.4	507.8	491.4	74.5	77.4
115°	556.2	572.6	596.8	149.0	79.4
117.5°	613.2	632.6	649.1	510.6	257.3
120°	677.1	691.6	709.0	720.6	590.0
122.5°	731.2	746.7	766.1	771.9	772.9
125°	786.3	799.0	817.4	824.1	827.0
127.5°	836.6	850.2	864.8	874.4	875.4
130°	884.1	899.6	910.1	920.8	920.0
132.5°	932.5	945.1	955.6	964.4	963.5
135°	973.1	988.6	997.2	1007.0	1005.0
137.5°	1015.6	1027.2	1037.0	1046.6	1043.8
140°	1057.2	1065.0	1075.5	1084.3	1079.5
142.5°	1092.1	1098.9	1111.4	1119.1	1114.3
145°	1128.9	1127.8	1144.2	1151.0	1146.2
147.5°	1160.7	1157.8	1174.3	1179.1	1175.3
150°	1191.7	1184.9	1200.4	1206.2	1201.3
152.5°	1217.7	1210.1	1224.6	1230.4	1223.6
155°	1242.9	1234.3	1245.9	1251.6	1244.0
157.5°	1263.2	1255.5	1264.2	1271.1	1263.2
160°	1280.7	1274.9	1280.7	1286.4	1279.7
162.5°	1296.1	1290.4	1295.1	1301.9	1293.2
165°	1309.6	1303.9	1306.8	1313.5	1306.8
167.5°	1320.3	1314.5	1317.5	1324.2	1315.5
170°	1329.0	1323.2	1325.2	1331.9	1323.2
172.5°	1334.8	1329.0	1331.0	1337.8	1329.0
175°	1339.7	1332.8	1334.8	1341.6	1331.9
177.5°	1341.6	1334.8	1335.9	1342.6	1333.9
180°	1336.7	1336.7	1336.7	1336.7	1336.7

TEST NUMBER: P913343

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.03	6.72	7.15	7.84	9.38	5.60	6.30	6.72	7.41	8.96
	3H	7.65	8.27	8.78	9.40	10.96	7.19	7.81	8.32	8.94	10.50
	4H	8.21	8.81	9.35	9.93	11.50	7.75	8.35	8.89	9.47	11.04
	6H	8.58	9.13	9.73	10.26	11.84	8.12	8.67	9.27	9.80	11.38
	8H	8.67	9.19	9.82	10.33	11.91	8.22	8.74	9.37	9.88	11.45
	12H	8.71	9.20	9.86	10.34	11.93	8.25	8.74	9.40	9.87	11.47
4H	2H	6.46	7.05	7.60	8.17	9.74	6.12	6.71	7.27	7.84	9.40
	3H	8.28	8.77	9.43	9.92	11.50	7.90	8.39	9.05	9.54	11.12
	4H	8.97	9.42	10.12	10.56	12.16	8.57	9.03	9.73	10.17	11.77
	6H	9.45	9.84	10.61	11.00	12.59	9.05	9.44	10.21	10.60	12.20
	8H	9.58	9.95	10.74	11.10	12.71	9.19	9.55	10.35	10.70	12.31
	12H	9.64	9.97	10.81	11.13	12.74	9.23	9.56	10.41	10.73	12.34
8H	4H	9.14	9.50	10.30	10.66	12.26	8.79	9.15	9.95	10.30	11.91
	6H	9.73	10.04	10.91	11.23	12.83	9.38	9.68	10.56	10.88	12.48
	8H	9.94	10.20	11.12	11.37	13.00	9.58	9.84	10.77	11.02	12.64
	12H	10.04	10.27	11.23	11.45	13.10	9.68	9.91	10.86	11.08	12.73
12H	4H	9.11	9.44	10.29	10.61	12.22	8.77	9.10	9.95	10.26	11.88
	6H	9.76	10.02	10.94	11.19	12.82	9.42	9.68	10.60	10.85	12.48
	8H	9.97	10.20	11.16	11.37	13.03	9.63	9.86	10.82	11.03	12.69

END OF REPORT