

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913344

Luminaire Tested: DFN2DIP-HX2F0-020D050US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913344
REPORT IS A COMBINATION OF REPORTS P899182 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D050US927-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4852.1 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913344

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913344

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	25	24	23
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	29	26	24	21	19	17
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1543	1543	1543
5°	1543	1515	1525
10°	1525	1481	1473
15°	1502	1429	1394
20°	1471	1358	1297
25°	1441	1279	1204
30°	1400	1199	1087
35°	1360	1113	984
40°	1319	1024	867
45°	1271	926	761
50°	1223	827	658
55°	1171	723	559
60°	1112	614	457
65°	1043	503	409
70°	959	400	366
75°	854	346	327
80°	703	280	276
85°	458	172	192

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1683 cd/sqm

TEST NUMBER: P913344

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	1.3
10°-20°	168.5	3.5
20°-30°	236.5	4.9
30°-40°	257.8	5.3
40°-50°	237.0	4.9
50°-60°	186.1	3.8
60°-70°	121.2	2.5
70°-80°	62.3	1.3
80°-90°	19.5	0.4
90°-100°	77.5	1.6
100°-110°	246.3	5.1
110°-120°	421.5	8.7
120°-130°	554.3	11.4
130°-140°	622.2	12.8
140°-150°	610.1	12.6
150°-160°	511.8	10.5
160°-170°	339.4	7.0
170°-180°	118.6	2.4
0°-30°	466.4	9.6
0°-40°	724.2	14.9
0°-60°	1147.3	23.6
0°-90°	1350.3	27.8
90°-120°	745.3	15.4
90°-150°	2532.0	52.2
90°-180°	3502.0	72.2
0°-180°	4852.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	655	652	644	650	648	62
15°	623	616	596	585	579	176
25°	565	546	507	483	474	260
35°	487	457	405	367	354	305
45°	398	358	296	254	240	308
55°	303	257	193	157	146	271
65°	204	156	103	83	81	203
75°	109	68	47	43	43	115
85°	25	13	11	11	11	29
90°	1	14	37	35	36	5
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	

TEST NUMBER: P913344

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	654.8	654.8	654.8	654.8	654.8
2.5°	657.7	654.8	648.2	654.3	653.1
5°	654.8	651.9	644.1	649.5	647.7
7.5°	649.5	645.9	637.6	640.0	637.0
10°	642.4	638.2	626.4	624.6	621.1
12.5°	633.5	628.1	612.1	608.6	602.1
15°	622.8	616.2	596.1	584.9	579.0
17.5°	610.4	600.9	576.0	562.9	553.5
20°	596.1	584.2	554.7	539.9	526.8
22.5°	580.7	567.1	532.7	512.6	503.7
25°	565.4	546.4	507.2	483.0	474.0
27.5°	547.0	526.8	483.5	455.7	442.0
30°	527.4	504.9	457.5	427.3	411.2
32.5°	508.4	481.2	432.6	397.0	382.2
35°	487.1	456.9	404.8	367.4	354.3
37.5°	466.4	433.7	378.7	337.8	323.0
40°	444.4	408.9	351.4	309.3	293.9
42.5°	421.9	384.0	324.2	280.3	265.5
45°	398.2	358.5	296.4	254.2	240.0
47.5°	375.7	333.7	269.7	227.5	214.5
50°	350.9	308.8	243.6	202.6	190.3
52.5°	326.5	282.0	218.6	179.6	168.3
55°	302.8	256.6	192.6	157.1	145.8
57.5°	278.5	231.1	169.5	136.3	126.8
60°	253.7	206.2	145.2	115.0	105.5
62.5°	229.3	182.0	124.5	96.0	91.3
65°	204.5	156.5	103.1	83.0	81.2
67.5°	180.8	132.7	83.0	72.9	71.1
70°	155.8	109.6	68.7	62.8	60.4
72.5°	132.1	88.2	57.4	52.8	51.6
75°	109.0	67.5	47.4	43.3	42.7
77.5°	86.0	48.0	37.3	34.9	33.7
80°	64.6	34.4	28.4	26.1	26.1
82.5°	45.0	23.1	19.6	18.4	18.4
85°	25.4	13.0	11.2	11.2	11.2
87.5°	9.5	4.8	4.8	4.1	4.1
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5

TEST NUMBER: P913344

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7

TEST NUMBER: P913344

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US927-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.97	6.65	7.10	7.77	9.33	1.96	2.63	3.09	3.75	5.31
	3H	7.61	8.22	8.75	9.35	10.92	3.12	3.72	4.25	4.85	6.42
	4H	8.20	8.77	9.35	9.90	11.48	3.55	4.12	4.70	5.25	6.83
	6H	8.59	9.12	9.75	10.25	11.84	3.85	4.37	5.00	5.50	7.09
	8H	8.70	9.20	9.86	10.35	11.93	3.92	4.43	5.08	5.57	7.16
	12H	8.75	9.22	9.91	10.36	11.97	3.95	4.43	5.12	5.57	7.18
4H	2H	5.97	6.54	7.12	7.67	9.25	2.52	3.09	3.67	4.22	5.80
	3H	7.75	8.23	8.91	9.39	10.98	3.83	4.31	4.99	5.47	7.06
	4H	8.42	8.86	9.58	10.00	11.61	4.36	4.80	5.53	5.95	7.56
	6H	8.90	9.28	10.07	10.45	12.05	4.75	5.13	5.92	6.30	7.90
	8H	9.06	9.41	10.23	10.57	12.19	4.87	5.22	6.04	6.38	8.00
	12H	9.14	9.45	10.32	10.62	12.24	4.92	5.24	6.10	6.41	8.03
8H	4H	8.37	8.72	9.54	9.88	11.50	4.62	4.97	5.78	6.12	7.74
	6H	8.91	9.20	10.09	10.40	12.01	5.10	5.39	6.29	6.59	8.21
	8H	9.11	9.36	10.30	10.54	12.17	5.28	5.53	6.47	6.71	8.35
	12H	9.22	9.44	10.42	10.62	12.28	5.38	5.60	6.58	6.78	8.44
12H	4H	8.32	8.63	9.50	9.80	11.43	4.61	4.93	5.79	6.10	7.72
	6H	8.88	9.13	10.07	10.31	11.94	5.15	5.40	6.34	6.58	8.21
	8H	9.08	9.30	10.27	10.47	12.14	5.34	5.56	6.53	6.73	8.40

END OF REPORT