

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902394

Luminaire Tested: DFN2DIP-4P4F0-080D030US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902394
REPORT IS A COMBINATION OF REPORTS P899089 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D030US830-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9967.4 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 108.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902394
CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P902394

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	79	79	79	75
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67	67	67	67	63
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	62	59	56	56	56	56	53
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48	48	48	48	45
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41	41	41	41	38
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	36	36	36	33
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32	32	32	32	29
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	28	28	28	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	25	25	25	25	23
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	23	23	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1903	1903	1903
5°	1907	1877	1890
10°	1891	1853	1865
15°	1864	1823	1826
20°	1826	1781	1786
25°	1789	1731	1739
30°	1742	1685	1680
35°	1698	1629	1617
40°	1644	1574	1557
45°	1589	1518	1496
50°	1530	1460	1425
55°	1468	1392	1360
60°	1397	1312	1285
65°	1321	1229	1197
70°	1223	1128	1103
75°	1088	1008	1017
80°	926	854	851
85°	672	587	574

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1589 cd/sqm



TEST NUMBER: P902394

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	2.8
10°-20°	777.0	7.8
20°-30°	1141.8	11.5
30°-40°	1326.2	13.3
40°-50°	1324.5	13.3
50°-60°	1155.0	11.6
60°-70°	853.8	8.6
70°-80°	483.0	4.8
80°-90°	130.0	1.3
90°-100°	55.3	0.6
100°-110°	175.8	1.8
110°-120°	300.9	3.0
120°-130°	395.7	4.0
130°-140°	444.2	4.5
140°-150°	435.6	4.4
150°-160°	365.4	3.7
160°-170°	242.3	2.4
170°-180°	84.7	0.8
0°-30°	2195.0	22.0
0°-40°	3521.1	35.3
0°-60°	6000.6	60.2
0°-90°	7467.5	74.9
90°-120°	532.1	5.3
90°-150°	1807.5	18.1
90°-180°	2500.0	25.1
0°-180°	9967.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	279
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2458	2463	2458	1163
35°	2181	2153	2108	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	896
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	1	10	26	25	26	9
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	



TEST NUMBER: P902394

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2933.9	2933.9	2933.9	2933.9	2933.9
2.5°	2951.0	2937.0	2905.9	2933.9	2928.6
5°	2933.9	2922.9	2891.8	2914.2	2908.9
7.5°	2914.2	2897.5	2866.4	2889.1	2883.4
10°	2883.4	2863.6	2829.8	2852.2	2843.9
12.5°	2840.9	2824.1	2790.3	2804.3	2798.7
15°	2793.0	2776.3	2739.4	2750.8	2736.8
17.5°	2733.7	2717.0	2680.1	2694.3	2680.1
20°	2668.8	2652.0	2612.5	2620.9	2609.8
22.5°	2604.2	2578.7	2541.8	2541.8	2536.2
25°	2527.8	2505.4	2457.5	2462.9	2457.5
27.5°	2443.1	2423.4	2386.8	2378.4	2364.4
30°	2358.7	2335.9	2293.8	2285.4	2274.0
32.5°	2268.3	2251.5	2206.3	2189.2	2177.9
35°	2180.9	2152.8	2107.5	2090.5	2076.4
37.5°	2082.1	2056.6	2011.5	1991.7	1977.6
40°	1980.7	1957.8	1912.7	1887.5	1876.1
42.5°	1881.9	1859.1	1814.2	1785.7	1769.1
45°	1774.7	1754.9	1712.4	1681.6	1670.3
47.5°	1670.3	1650.5	1605.2	1574.1	1557.4
50°	1560.1	1546.1	1506.5	1467.0	1452.9
52.5°	1452.9	1433.1	1396.7	1365.6	1345.8
55°	1343.0	1326.0	1292.2	1258.4	1244.3
57.5°	1232.9	1218.9	1182.0	1148.2	1136.8
60°	1122.8	1111.7	1072.1	1041.0	1032.6
62.5°	1015.6	995.9	967.7	939.6	928.2
65°	905.8	888.7	860.5	835.1	821.0
67.5°	792.9	778.5	753.4	733.7	722.3
70°	688.4	677.0	651.7	631.9	620.8
72.5°	581.3	570.0	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.1	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4



TEST NUMBER: P902394

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3



TEST NUMBER: P902394
 CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.57	12.71	12.28	13.44	14.30	11.12	12.26	11.83	12.99	13.86
	3H	13.25	14.28	13.98	15.02	15.91	12.76	13.79	13.49	14.53	15.42
	4H	13.86	14.82	14.60	15.57	16.48	13.36	14.33	14.10	15.08	15.99
	6H	14.28	15.17	15.03	15.93	16.85	13.77	14.67	14.53	15.43	16.35
	8H	14.39	15.24	15.15	16.02	16.95	13.89	14.74	14.65	15.52	16.44
	12H	14.45	15.26	15.22	16.03	16.99	13.94	14.75	14.71	15.52	16.48
4H	2H	12.06	13.03	12.81	13.78	14.69	11.71	12.67	12.45	13.42	14.33
	3H	13.96	14.77	14.72	15.55	16.48	13.55	14.36	14.31	15.14	16.07
	4H	14.69	15.42	15.46	16.21	17.16	14.26	15.00	15.04	15.78	16.74
	6H	15.22	15.86	16.01	16.67	17.63	14.79	15.43	15.58	16.24	17.20
	8H	15.38	15.98	16.18	16.79	17.76	14.95	15.54	15.74	16.35	17.32
	12H	15.47	16.01	16.29	16.84	17.82	15.02	15.56	15.84	16.39	17.37
8H	4H	14.91	15.50	15.70	16.31	17.28	14.53	15.13	15.33	15.93	16.91
	6H	15.56	16.05	16.38	16.90	17.87	15.17	15.67	16.00	16.52	17.49
	8H	15.78	16.22	16.62	17.07	18.06	15.39	15.83	16.23	16.68	17.67
	12H	15.93	16.32	16.77	17.16	18.21	15.52	15.91	16.36	16.75	17.79
12H	4H	14.91	15.44	15.72	16.27	17.25	14.54	15.08	15.35	15.90	16.88
	6H	15.59	16.03	16.43	16.88	17.87	15.22	15.66	16.05	16.50	17.50
	8H	15.85	16.24	16.69	17.07	18.12	15.47	15.86	16.31	16.69	17.74