

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902405

Luminaire Tested: DFN2DIP-4P4F0-080D050US830-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902405
REPORT IS A COMBINATION OF REPORTS P900634 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D050US830-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open
No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11074.9 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 126
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902405

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902405

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55
2	92	84	79	74	85	79	74	69	69	65	62	59	57	54	51	49	47
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	43	41
4	77	67	59	53	72	62	56	50	55	49	45	48	44	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	27	23	20
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2022	2022	2022
5°	2025	1990	2003
10°	2005	1952	1939
15°	1978	1888	1839
20°	1941	1800	1716
25°	1904	1700	1597
30°	1854	1599	1446
35°	1805	1489	1313
40°	1755	1376	1161
45°	1697	1250	1023
50°	1637	1123	888
55°	1575	988	758
60°	1502	846	625
65°	1419	701	563
70°	1318	566	511
75°	1191	501	467
80°	1008	422	407
85°	704	285	311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1697 cd/sqm

TEST NUMBER: P902405

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US830-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	2.6
10°-20°	801.8	7.2
20°-30°	1125.7	10.2
30°-40°	1227.1	11.1
40°-50°	1127.8	10.2
50°-60°	885.7	8.0
60°-70°	576.5	5.2
70°-80°	296.8	2.7
80°-90°	78.5	0.7
90°-100°	52.5	0.5
100°-110°	195.5	1.8
110°-120°	518.5	4.7
120°-130°	860.0	7.8
130°-140°	913.5	8.2
140°-150°	849.0	7.7
150°-160°	682.6	6.2
160°-170°	439.8	4.0
170°-180°	151.4	1.4
0°-30°	2219.6	20.0
0°-40°	3446.7	31.1
0°-60°	5460.2	49.3
0°-90°	6412.1	57.9
90°-120°	766.5	6.9
90°-150°	3389.0	30.6
90°-180°	4663.0	42.1
0°-180°	11074.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3066	3091	3083	296
15°	2964	2933	2837	2784	2756	835
25°	2691	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	1	14	23	29	31	10
95°	75	37	45	51	50	89
105°	350	384	70	83	88	374
115°	662	681	710	177	94	651
125°	936	951	972	980	984	834
135°	1158	1176	1186	1198	1196	894
145°	1343	1342	1361	1370	1364	840
155°	1479	1469	1482	1489	1480	681
165°	1558	1551	1555	1563	1555	440
175°	1594	1586	1588	1596	1585	152
180°	1590	1590	1590	1590	1590	

TEST NUMBER: P902405

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.4	3116.4	3116.4	3116.4	3116.4
2.5°	3130.5	3116.4	3085.3	3113.7	3108.0
5°	3116.4	3102.4	3065.5	3091.0	3082.6
7.5°	3091.0	3074.2	3034.7	3045.8	3031.7
10°	3057.1	3037.4	2981.2	2972.5	2955.7
12.5°	3015.0	2989.6	2913.2	2896.4	2865.3
15°	2964.1	2933.0	2837.2	2783.7	2755.5
17.5°	2904.8	2859.7	2741.2	2679.3	2634.0
20°	2837.2	2780.7	2639.8	2569.5	2507.2
22.5°	2763.9	2699.0	2535.3	2439.6	2397.4
25°	2690.6	2600.3	2414.1	2298.7	2256.2
27.5°	2603.2	2507.2	2301.3	2168.8	2103.8
30°	2510.2	2402.7	2177.2	2033.5	1957.2
32.5°	2419.8	2290.0	2059.0	1889.6	1819.0
35°	2318.4	2174.4	1926.4	1748.7	1686.4
37.5°	2219.6	2064.4	1802.2	1607.4	1537.1
40°	2115.3	1946.2	1672.4	1472.2	1398.8
42.5°	2008.1	1827.7	1542.8	1334.0	1263.6
45°	1895.3	1706.2	1410.2	1209.8	1142.2
47.5°	1788.2	1588.0	1283.4	1082.9	1021.0
50°	1669.6	1469.5	1159.2	964.4	905.4
52.5°	1553.9	1342.3	1040.7	854.6	801.1
55°	1441.1	1221.2	916.5	747.4	693.9
57.5°	1325.6	1099.9	806.7	648.8	603.5
60°	1207.0	981.5	690.9	547.2	502.1
62.5°	1091.6	865.9	592.2	456.9	434.5
65°	973.1	744.4	490.7	395.0	386.3
67.5°	860.3	631.7	395.0	346.8	338.5
70°	741.8	521.9	327.1	298.9	287.6
72.5°	629.0	420.1	273.5	251.1	245.3
75°	518.9	321.4	225.6	205.9	203.2
77.5°	409.1	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.3	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	1.1	13.8	23.0	28.8	31.0
92.5°	28.8	24.2	27.6	30.0	31.0
95°	74.7	36.8	44.9	50.7	49.5
97.5°	134.6	40.3	58.6	62.2	63.2
100°	203.8	46.1	65.6	74.7	77.1
102.5°	279.7	277.4	68.0	80.5	84.1
105°	349.9	384.5	70.2	82.8	87.5
107.5°	431.6	460.2	72.6	85.1	89.8
110°	509.9	534.0	201.4	86.3	90.9



TEST NUMBER: P902405

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	583.5	604.2	584.7	88.6	92.1
115°	661.8	681.3	710.1	177.3	94.4
117.5°	729.6	752.6	772.3	607.6	306.1
120°	805.6	822.8	843.6	857.4	702.0
122.5°	870.0	888.4	911.5	918.4	919.6
125°	935.6	950.6	972.5	980.5	984.0
127.5°	995.4	1011.5	1029.0	1040.4	1041.5
130°	1051.9	1070.4	1082.9	1095.6	1094.6
132.5°	1109.5	1124.5	1137.0	1147.5	1146.3
135°	1157.8	1176.3	1186.5	1198.2	1195.8
137.5°	1208.3	1222.2	1233.8	1245.3	1241.9
140°	1257.8	1267.2	1279.7	1290.1	1284.4
142.5°	1299.4	1307.5	1322.4	1331.5	1325.8
145°	1343.1	1341.9	1361.4	1369.5	1363.8
147.5°	1381.0	1377.5	1397.1	1402.9	1398.4
150°	1417.9	1409.9	1428.2	1435.1	1429.4
152.5°	1448.9	1439.7	1457.0	1464.0	1455.9
155°	1478.8	1468.6	1482.3	1489.2	1480.1
157.5°	1503.0	1493.8	1504.2	1512.3	1503.0
160°	1523.8	1516.8	1523.8	1530.6	1522.6
162.5°	1542.1	1535.3	1541.0	1549.1	1538.7
165°	1558.2	1551.4	1554.8	1562.8	1554.8
167.5°	1570.9	1564.0	1567.5	1575.6	1565.2
170°	1581.3	1574.3	1576.7	1584.7	1574.3
172.5°	1588.2	1581.3	1583.7	1591.7	1581.3
175°	1593.9	1585.8	1588.2	1596.2	1584.7
177.5°	1596.2	1588.2	1589.4	1597.4	1587.1
180°	1590.4	1590.4	1590.4	1590.4	1590.4

TEST NUMBER: P902405

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.32	11.22	11.21	12.13	13.28	6.28	7.18	7.17	8.09	9.24
	3H	12.01	12.81	12.91	13.73	14.91	7.48	8.28	8.38	9.20	10.38
	4H	12.62	13.38	13.54	14.31	15.50	7.93	8.69	8.85	9.61	10.80
	6H	13.05	13.75	13.99	14.68	15.89	8.26	8.96	9.19	9.88	11.09
	8H	13.18	13.85	14.12	14.80	16.00	8.35	9.01	9.29	9.96	11.16
	12H	13.25	13.88	14.20	14.82	16.05	8.40	9.03	9.34	9.97	11.20
4H	2H	10.35	11.10	11.27	12.03	13.22	6.89	7.65	7.81	8.57	9.76
	3H	12.19	12.82	13.12	13.77	14.98	8.25	8.88	9.18	9.83	11.04
	4H	12.89	13.46	13.83	14.41	15.64	8.80	9.37	9.74	10.32	11.55
	6H	13.41	13.91	14.37	14.88	16.11	9.22	9.72	10.18	10.69	11.92
	8H	13.59	14.05	14.55	15.02	16.26	9.35	9.82	10.32	10.78	12.03
	12H	13.69	14.11	14.67	15.09	16.34	9.42	9.84	10.40	10.82	12.07
8H	4H	12.86	13.32	13.82	14.29	15.53	9.09	9.55	10.05	10.51	11.76
	6H	13.44	13.82	14.42	14.82	16.07	9.61	9.99	10.60	11.00	12.24
	8H	13.66	13.99	14.65	14.99	16.25	9.80	10.14	10.80	11.14	12.40
	12H	13.80	14.10	14.80	15.09	16.40	9.93	10.22	10.92	11.21	12.52
12H	4H	12.82	13.23	13.80	14.21	15.46	9.10	9.51	10.08	10.49	11.74
	6H	13.41	13.75	14.41	14.74	16.01	9.66	10.00	10.66	10.99	12.26
	8H	13.64	13.94	14.64	14.93	16.23	9.88	10.17	10.87	11.16	12.47

END OF REPORT