

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913378

Luminaire Tested: DFN2DIP-HX2F0-040D040US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913378
REPORT IS A COMBINATION OF REPORTS P899175 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D040US927-FLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5941.4 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913378

CATALOG NUMBER: DFN2DIP-HX2F0-040D040US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913378

CATALOG NUMBER: DFN2DIP-HX2F0-040D040US927-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85		71	71	71		59
1	98	94	90	87	91	87	84	81	74	72	70		63	61	59		52
2	90	82	76	71	83	76	71	66	65	61	58		55	52	50		46
3	82	72	65	59	75	67	61	55	58	53	49		49	45	42		41
4	75	64	56	50	69	60	52	47	51	46	41		43	39	36		36
5	69	57	49	43	63	53	46	40	46	40	36		39	35	31		33
6	63	51	43	37	58	48	40	35	41	36	31		35	31	27		30
7	59	46	38	33	54	43	36	31	37	32	28		32	28	24		27
8	54	42	34	29	50	39	32	27	34	29	24		29	25	22		25
9	51	38	31	26	47	36	29	24	31	26	22		27	23	19		23
10	47	35	28	23	44	33	26	22	29	23	20		25	21	18		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2905	2905	2905
5°	2905	2858	2878
10°	2877	2812	2834
15°	2830	2759	2768
20°	2768	2688	2701
25°	2706	2604	2623
30°	2631	2526	2527
35°	2558	2434	2425
40°	2470	2342	2327
45°	2381	2249	2227
50°	2285	2151	2111
55°	2183	2038	2004
60°	2067	1905	1881
65°	1941	1765	1737
70°	1780	1596	1579
75°	1560	1392	1427
80°	1291	1133	1152
85°	877	712	712

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2381 cd/sqm

TEST NUMBER: P913378

CATALOG NUMBER: DFN2DIP-HX2F0-040D040US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	2.0
10°-20°	326.5	5.5
20°-30°	479.8	8.1
30°-40°	557.3	9.4
40°-50°	556.6	9.4
50°-60°	485.3	8.2
60°-70°	358.8	6.0
70°-80°	203.0	3.4
80°-90°	56.4	0.9
90°-100°	62.0	1.0
100°-110°	197.0	3.3
110°-120°	337.2	5.7
120°-130°	443.5	7.5
130°-140°	497.8	8.4
140°-150°	488.1	8.2
150°-160°	409.5	6.9
160°-170°	271.5	4.6
170°-180°	94.9	1.6
0°-30°	922.4	15.5
0°-40°	1479.7	24.9
0°-60°	2521.7	42.4
0°-90°	3139.9	52.8
90°-120°	596.2	10.0
90°-150°	2025.6	34.1
90°-180°	2801.0	47.1
0°-180°	5941.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	1	11	30	28	29	6
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	

TEST NUMBER: P913378

CATALOG NUMBER: DFN2DIP-HX2F0-040D040US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5

TEST NUMBER: P913378

CATALOG NUMBER: DFN2DIP-HX2F0-040D040US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1

TEST NUMBER: P913378

CATALOG NUMBER: DFN2DIP-HX2F0-040D040US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.10	11.99	12.03	12.94	14.17	10.68	11.56	11.61	12.51	13.74
	3H	12.74	13.53	13.68	14.49	15.74	12.28	13.07	13.22	14.03	15.28
	4H	13.31	14.06	14.27	15.03	16.29	12.85	13.60	13.81	14.57	15.83
	6H	13.69	14.38	14.66	15.35	16.63	13.23	13.93	14.20	14.89	16.17
	8H	13.79	14.45	14.76	15.43	16.70	13.33	13.99	14.30	14.98	16.25
	12H	13.83	14.45	14.81	15.43	16.73	13.36	13.99	14.34	14.97	16.27
4H	2H	11.55	12.31	12.52	13.27	14.53	11.21	11.97	12.18	12.93	14.19
	3H	13.39	14.02	14.37	15.01	16.29	13.01	13.64	13.98	14.63	15.91
	4H	14.09	14.66	15.07	15.65	16.95	13.69	14.27	14.68	15.26	16.56
	6H	14.58	15.08	15.58	16.09	17.39	14.19	14.68	15.18	15.69	16.99
	8H	14.72	15.18	15.72	16.19	17.50	14.32	14.79	15.32	15.79	17.10
	12H	14.78	15.20	15.80	16.22	17.54	14.38	14.80	15.39	15.82	17.13
8H	4H	14.28	14.74	15.27	15.74	17.06	13.92	14.39	14.92	15.39	16.70
	6H	14.88	15.26	15.90	16.31	17.62	14.53	14.91	15.55	15.96	17.27
	8H	15.08	15.42	16.11	16.45	17.78	14.73	15.07	15.76	16.10	17.43
	12H	15.20	15.50	16.23	16.52	17.90	14.83	15.13	15.86	16.15	17.53
12H	4H	14.26	14.68	15.28	15.70	17.02	13.92	14.33	14.93	15.35	16.67
	6H	14.90	15.24	15.93	16.27	17.60	14.56	14.90	15.59	15.93	17.26
	8H	15.13	15.43	16.16	16.45	17.83	14.78	15.08	15.82	16.11	17.48

END OF REPORT