

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913383

Luminaire Tested: DFN2DIP-HX2F0-040D050US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913383
REPORT IS A COMBINATION OF REPORTS P900705 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D050US927-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7058.3 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 74.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913383

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913383

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	106	106	106	106	97	97	97	97		80	80	80		65	65	65		51	51	51
1	97	92	88	85	88	85	81	78		70	68	66		57	56	54		45	44	43
2	88	81	74	69	80	74	69	64		62	58	55		50	48	45		40	38	36
3	80	71	64	58	73	65	59	54		54	50	46		44	41	38		35	33	31
4	73	63	55	49	67	58	51	46		48	43	39		40	36	33		31	29	27
5	67	56	48	42	61	51	44	39		43	38	34		35	31	28		28	25	23
6	62	50	42	36	57	46	39	34		39	33	29		32	28	25		26	23	20
7	57	45	37	32	52	42	35	30		35	30	26		29	25	22		23	20	18
8	53	41	33	28	49	38	31	26		32	27	23		27	23	20		22	19	16
9	49	37	30	25	45	35	28	23		29	24	20		25	20	18		20	17	15
10	46	34	27	22	42	32	25	21		27	22	18		23	19	16		18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2905	2905	2905
5°	2905	2858	2878
10°	2877	2812	2834
15°	2830	2759	2768
20°	2768	2688	2701
25°	2706	2604	2623
30°	2631	2526	2527
35°	2558	2434	2425
40°	2470	2342	2327
45°	2381	2249	2227
50°	2285	2151	2111
55°	2183	2038	2004
60°	2067	1905	1881
65°	1941	1765	1737
70°	1780	1596	1579
75°	1560	1392	1427
80°	1291	1133	1152
85°	877	712	712

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2381 cd/sqm

TEST NUMBER: P913383

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	1.6
10°-20°	326.5	4.6
20°-30°	479.8	6.8
30°-40°	557.3	7.9
40°-50°	556.6	7.9
50°-60°	485.3	6.9
60°-70°	358.8	5.1
70°-80°	203.0	2.9
80°-90°	55.9	0.8
90°-100°	44.1	0.6
100°-110°	164.3	2.3
110°-120°	435.8	6.2
120°-130°	722.8	10.2
130°-140°	767.8	10.9
140°-150°	713.6	10.1
150°-160°	573.7	8.1
160°-170°	369.7	5.2
170°-180°	127.2	1.8
0°-30°	922.4	13.1
0°-40°	1479.7	21.0
0°-60°	2521.7	35.7
0°-90°	3139.4	44.5
90°-120°	644.2	9.1
90°-150°	2848.4	40.4
90°-180°	3919.0	55.5
0°-180°	7058.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	1	12	19	24	26	7
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	573	597	149	79	548
125°	786	799	817	824	827	701
135°	973	989	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1252	1244	573
165°	1310	1304	1307	1314	1307	370
175°	1340	1333	1335	1342	1332	127
180°	1337	1337	1337	1337	1337	

TEST NUMBER: P913383

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.2
100°	171.3	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.7	70.7
105°	294.1	323.1	59.0	69.6	73.5
107.5°	362.7	386.8	61.0	71.5	75.5
110°	428.6	448.8	169.3	72.6	76.4

TEST NUMBER: P913383

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.4	507.8	491.4	74.5	77.4
115°	556.2	572.6	596.8	149.0	79.4
117.5°	613.2	632.6	649.1	510.6	257.3
120°	677.1	691.6	709.0	720.6	590.0
122.5°	731.2	746.7	766.1	771.9	772.9
125°	786.3	799.0	817.4	824.1	827.0
127.5°	836.6	850.2	864.8	874.4	875.4
130°	884.1	899.6	910.1	920.8	920.0
132.5°	932.5	945.1	955.6	964.4	963.5
135°	973.1	988.6	997.2	1007.0	1005.0
137.5°	1015.6	1027.2	1037.0	1046.6	1043.8
140°	1057.2	1065.0	1075.5	1084.3	1079.5
142.5°	1092.1	1098.9	1111.4	1119.1	1114.3
145°	1128.9	1127.8	1144.2	1151.0	1146.2
147.5°	1160.7	1157.8	1174.3	1179.1	1175.3
150°	1191.7	1184.9	1200.4	1206.2	1201.3
152.5°	1217.7	1210.1	1224.6	1230.4	1223.6
155°	1242.9	1234.3	1245.9	1251.6	1244.0
157.5°	1263.2	1255.5	1264.2	1271.1	1263.2
160°	1280.7	1274.9	1280.7	1286.4	1279.7
162.5°	1296.1	1290.4	1295.1	1301.9	1293.2
165°	1309.6	1303.9	1306.8	1313.5	1306.8
167.5°	1320.3	1314.5	1317.5	1324.2	1315.5
170°	1329.0	1323.2	1325.2	1331.9	1323.2
172.5°	1334.8	1329.0	1331.0	1337.8	1329.0
175°	1339.7	1332.8	1334.8	1341.6	1331.9
177.5°	1341.6	1334.8	1335.9	1342.6	1333.9
180°	1336.7	1336.7	1336.7	1336.7	1336.7

TEST NUMBER: P913383

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.31	11.12	11.31	12.13	13.48	9.88	10.70	10.89	11.71	13.06
	3H	11.94	12.67	12.95	13.69	15.06	11.48	12.21	12.49	13.23	14.60
	4H	12.51	13.20	13.53	14.22	15.60	12.05	12.74	13.07	13.77	15.14
	6H	12.89	13.52	13.92	14.55	15.94	12.43	13.06	13.46	14.09	15.48
	8H	12.98	13.59	14.02	14.63	16.02	12.52	13.13	13.56	14.17	15.56
	12H	13.02	13.59	14.06	14.63	16.04	12.55	13.13	13.60	14.17	15.58
4H	2H	10.75	11.44	11.79	12.47	13.85	10.41	11.11	11.45	12.13	13.51
	3H	12.59	13.16	13.63	14.22	15.61	12.20	12.78	13.24	13.83	15.22
	4H	13.28	13.81	14.33	14.85	16.26	12.88	13.41	13.93	14.46	15.87
	6H	13.77	14.22	14.82	15.29	16.70	13.37	13.83	14.43	14.89	16.30
	8H	13.90	14.33	14.96	15.39	16.81	13.51	13.93	14.57	14.99	16.41
	12H	13.96	14.35	15.04	15.42	16.85	13.56	13.94	14.63	15.02	16.44
8H	4H	13.46	13.88	14.52	14.95	16.37	13.11	13.53	14.17	14.59	16.02
	6H	14.06	14.41	15.14	15.51	16.93	13.71	14.06	14.79	15.16	16.58
	8H	14.26	14.57	15.35	15.66	17.10	13.91	14.22	15.00	15.30	16.74
	12H	14.38	14.65	15.47	15.73	17.21	14.01	14.28	15.10	15.36	16.84
12H	4H	13.44	13.82	14.52	14.90	16.33	13.10	13.48	14.17	14.56	15.98
	6H	14.08	14.39	15.17	15.48	16.92	13.74	14.05	14.83	15.14	16.58
	8H	14.31	14.58	15.40	15.66	17.14	13.96	14.23	15.05	15.31	16.79