

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913405

Luminaire Tested: DFN2DIP-HX2F0-050D050US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913405
REPORT IS A COMBINATION OF REPORTS P900708 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-050D050US927-RLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7288.1 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 86
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913405
CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P913405
 CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46			46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40			40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39	34			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34	29			29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	26			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23			23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16			16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3857	3857	3857
5°	3857	3787	3813
10°	3813	3703	3682
15°	3754	3572	3484
20°	3679	3395	3243
25°	3601	3198	3010
30°	3499	2997	2718
35°	3399	2781	2461
40°	3297	2559	2169
45°	3179	2315	1903
50°	3056	2068	1645
55°	2928	1806	1397
60°	2779	1534	1143
65°	2606	1258	1022
70°	2398	1001	915
75°	2135	865	818
80°	1756	701	688
85°	1150	432	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3179 cd/sqm



TEST NUMBER: P913405

CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	2.1
10°-20°	421.2	5.8
20°-30°	591.3	8.1
30°-40°	644.6	8.8
40°-50°	592.4	8.1
50°-60°	465.3	6.4
60°-70°	302.9	4.2
70°-80°	155.9	2.1
80°-90°	42.2	0.6
90°-100°	44.1	0.6
100°-110°	164.3	2.3
110°-120°	435.8	6.0
120°-130°	722.8	9.9
130°-140°	767.8	10.5
140°-150°	713.6	9.8
150°-160°	573.7	7.9
160°-170°	369.7	5.1
170°-180°	127.2	1.7
0°-30°	1165.9	16.0
0°-40°	1810.5	24.8
0°-60°	2868.2	39.4
0°-90°	3369.1	46.2
90°-120°	644.2	8.8
90°-150°	2848.4	39.1
90°-180°	3919.0	53.8
0°-180°	7288.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1630	1610	1624	1619	155
15°	1557	1541	1490	1462	1448	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	996	896	741	636	600	769
55°	757	641	481	393	364	676
65°	511	391	258	208	203	507
75°	273	169	118	108	107	288
85°	64	33	28	28	28	73
90°	1	12	19	24	26	7
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	573	597	149	79	548
125°	786	799	817	824	827	701
135°	973	989	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1252	1244	573
165°	1310	1304	1307	1314	1307	370
175°	1340	1333	1335	1342	1332	127
180°	1337	1337	1337	1337	1337	



TEST NUMBER: P913405

CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.0	1637.0	1637.0	1637.0	1637.0
2.5°	1644.4	1637.0	1620.7	1635.6	1632.6
5°	1637.0	1629.7	1610.3	1623.7	1619.3
7.5°	1623.7	1614.9	1594.1	1600.0	1592.5
10°	1605.9	1595.5	1566.0	1561.5	1552.6
12.5°	1583.7	1570.4	1530.3	1521.5	1505.1
15°	1557.0	1540.7	1490.4	1462.3	1447.5
17.5°	1525.9	1502.2	1439.9	1407.4	1383.6
20°	1490.4	1460.7	1386.6	1349.7	1317.0
22.5°	1451.9	1417.8	1331.8	1281.5	1259.3
25°	1413.3	1365.9	1268.1	1207.4	1185.1
27.5°	1367.5	1317.0	1208.9	1139.2	1105.2
30°	1318.6	1262.2	1143.7	1068.2	1028.1
32.5°	1271.1	1202.9	1081.6	992.6	955.5
35°	1217.8	1142.2	1011.9	918.5	885.9
37.5°	1165.9	1084.4	946.7	844.4	807.5
40°	1111.1	1022.3	878.4	773.3	734.8
42.5°	1054.9	960.0	810.4	700.7	663.8
45°	995.6	896.3	740.8	635.5	599.9
47.5°	939.3	834.2	674.1	568.9	536.3
50°	877.1	771.9	608.9	506.6	475.6
52.5°	816.3	705.1	546.7	448.9	420.8
55°	757.0	641.4	481.4	392.6	364.5
57.5°	696.3	577.8	423.7	340.8	317.0
60°	634.1	515.6	362.9	287.5	263.7
62.5°	573.4	454.9	311.1	240.0	228.2
65°	511.1	391.1	257.8	207.5	203.0
67.5°	451.9	331.8	207.5	182.2	177.8
70°	389.7	274.1	171.8	157.0	151.1
72.5°	330.4	220.7	143.7	131.9	128.9
75°	272.6	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.4
80°	161.4	86.0	71.1	65.2	65.2
82.5°	112.6	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.2
100°	171.3	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.7	70.7
105°	294.1	323.1	59.0	69.6	73.5
107.5°	362.7	386.8	61.0	71.5	75.5
110°	428.6	448.8	169.3	72.6	76.4



TEST NUMBER: P913405

CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.4	507.8	491.4	74.5	77.4
115°	556.2	572.6	596.8	149.0	79.4
117.5°	613.2	632.6	649.1	510.6	257.3
120°	677.1	691.6	709.0	720.6	590.0
122.5°	731.2	746.7	766.1	771.9	772.9
125°	786.3	799.0	817.4	824.1	827.0
127.5°	836.6	850.2	864.8	874.4	875.4
130°	884.1	899.6	910.1	920.8	920.0
132.5°	932.5	945.1	955.6	964.4	963.5
135°	973.1	988.6	997.2	1007.0	1005.0
137.5°	1015.6	1027.2	1037.0	1046.6	1043.8
140°	1057.2	1065.0	1075.5	1084.3	1079.5
142.5°	1092.1	1098.9	1111.4	1119.1	1114.3
145°	1128.9	1127.8	1144.2	1151.0	1146.2
147.5°	1160.7	1157.8	1174.3	1179.1	1175.3
150°	1191.7	1184.9	1200.4	1206.2	1201.3
152.5°	1217.7	1210.1	1224.6	1230.4	1223.6
155°	1242.9	1234.3	1245.9	1251.6	1244.0
157.5°	1263.2	1255.5	1264.2	1271.1	1263.2
160°	1280.7	1274.9	1280.7	1286.4	1279.7
162.5°	1296.1	1290.4	1295.1	1301.9	1293.2
165°	1309.6	1303.9	1306.8	1313.5	1306.8
167.5°	1320.3	1314.5	1317.5	1324.2	1315.5
170°	1329.0	1323.2	1325.2	1331.9	1323.2
172.5°	1334.8	1329.0	1331.0	1337.8	1329.0
175°	1339.7	1332.8	1334.8	1341.6	1331.9
177.5°	1341.6	1334.8	1335.9	1342.6	1333.9
180°	1336.7	1336.7	1336.7	1336.7	1336.7



TEST NUMBER: P913405
 CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.34	12.14	12.33	13.14	14.47	7.32	8.12	8.32	9.12	10.45
	3H	12.99	13.70	13.99	14.71	16.06	8.49	9.21	9.50	10.22	11.56
	4H	13.58	14.25	14.60	15.27	16.62	8.93	9.60	9.95	10.62	11.97
	6H	13.98	14.60	15.01	15.62	16.99	9.23	9.85	10.26	10.87	12.24
	8H	14.09	14.68	15.13	15.72	17.08	9.31	9.91	10.35	10.94	12.30
	12H	14.14	14.71	15.18	15.73	17.12	9.35	9.91	10.39	10.94	12.33
4H	2H	11.35	12.02	12.37	13.04	14.40	7.90	8.57	8.92	9.59	10.95
	3H	13.15	13.71	14.18	14.75	16.12	9.23	9.79	10.26	10.83	12.20
	4H	13.82	14.33	14.86	15.37	16.76	9.76	10.27	10.80	11.31	12.70
	6H	14.31	14.75	15.36	15.81	17.19	10.16	10.60	11.21	11.66	13.04
	8H	14.47	14.88	15.52	15.93	17.33	10.28	10.69	11.33	11.74	13.14
	12H	14.55	14.92	15.62	15.99	17.39	10.33	10.70	11.40	11.77	13.17
8H	4H	13.78	14.19	14.83	15.24	16.64	10.02	10.43	11.07	11.48	12.89
	6H	14.32	14.66	15.39	15.75	17.15	10.51	10.85	11.59	11.95	13.35
	8H	14.52	14.82	15.60	15.89	17.31	10.69	10.99	11.77	12.07	13.49
	12H	14.64	14.90	15.72	15.97	17.43	10.80	11.06	11.88	12.13	13.59
12H	4H	13.73	14.10	14.80	15.17	16.57	10.02	10.39	11.09	11.46	12.86
	6H	14.29	14.59	15.37	15.67	17.08	10.56	10.86	11.64	11.93	13.35
	8H	14.49	14.75	15.58	15.83	17.29	10.75	11.01	11.83	12.09	13.55