

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913420

Luminaire Tested: DFN2DIP-HX2F0-060D040US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913420
REPORT IS A COMBINATION OF REPORTS P899180 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D040US927-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6844.4 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 88.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913420

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913420

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US927-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4629	4629	4629
5°	4629	4544	4576
10°	4575	4444	4418
15°	4505	4286	4180
20°	4414	4074	3891
25°	4322	3838	3613
30°	4199	3596	3262
35°	4079	3338	2954
40°	3956	3071	2602
45°	3815	2778	2284
50°	3668	2482	1974
55°	3513	2168	1676
60°	3334	1841	1372
65°	3128	1510	1225
70°	2876	1201	1097
75°	2561	1038	982
80°	2108	840	827
85°	1379	518	579

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3815 cd/sqm

TEST NUMBER: P913420

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	2.7
10°-20°	505.4	7.4
20°-30°	709.6	10.4
30°-40°	773.5	11.3
40°-50°	710.9	10.4
50°-60°	558.3	8.2
60°-70°	363.4	5.3
70°-80°	187.1	2.7
80°-90°	50.6	0.7
90°-100°	62.0	0.9
100°-110°	197.0	2.9
110°-120°	337.2	4.9
120°-130°	443.5	6.5
130°-140°	497.8	7.3
140°-150°	488.1	7.1
150°-160°	409.5	6.0
160°-170°	271.5	4.0
170°-180°	94.9	1.4
0°-30°	1399.1	20.4
0°-40°	2172.6	31.7
0°-60°	3441.9	50.3
0°-90°	4043.0	59.1
90°-120°	596.2	8.7
90°-150°	2025.6	29.6
90°-180°	2801.0	40.9
0°-180°	6844.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1956	1932	1948	1943	186
15°	1868	1849	1788	1755	1737	527
25°	1696	1639	1522	1449	1422	780
35°	1461	1371	1214	1102	1063	915
45°	1195	1076	889	763	720	923
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	203	142	130	128	346
85°	76	39	34	34	34	88
90°	1	11	30	28	29	7
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	

TEST NUMBER: P913420

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.5	1964.5	1964.5	1964.5	1964.5
2.5°	1973.3	1964.5	1944.8	1962.7	1959.1
5°	1964.5	1955.6	1932.4	1948.4	1943.1
7.5°	1948.4	1937.8	1913.0	1919.9	1911.1
10°	1927.1	1914.6	1879.2	1873.7	1863.1
12.5°	1900.5	1884.4	1836.4	1825.8	1806.2
15°	1868.4	1848.8	1788.4	1754.7	1736.9
17.5°	1831.1	1802.6	1727.9	1688.9	1660.4
20°	1788.4	1752.8	1664.0	1619.6	1580.4
22.5°	1742.2	1701.3	1598.1	1537.8	1511.2
25°	1696.1	1639.1	1521.8	1449.0	1422.2
27.5°	1641.0	1580.4	1450.6	1367.1	1326.2
30°	1582.3	1514.6	1372.4	1281.8	1233.7
32.5°	1525.3	1443.5	1297.9	1191.1	1146.6
35°	1461.4	1370.7	1214.3	1102.2	1063.0
37.5°	1399.2	1301.2	1136.1	1013.3	968.9
40°	1333.3	1226.8	1054.2	928.0	881.8
42.5°	1265.8	1152.1	972.5	840.8	796.5
45°	1194.7	1075.5	889.0	762.6	719.9
47.5°	1127.2	1001.0	809.0	682.6	643.6
50°	1052.5	926.3	730.7	607.9	570.8
52.5°	979.5	846.1	656.0	538.7	504.9
55°	908.4	769.8	577.7	471.2	437.4
57.5°	835.6	693.3	508.5	408.9	380.4
60°	760.9	618.7	435.5	345.0	316.5
62.5°	688.1	545.9	373.3	288.0	273.9
65°	613.4	469.3	309.3	249.0	243.5
67.5°	542.2	398.2	249.0	218.6	213.3
70°	467.5	328.9	206.1	188.5	181.3
72.5°	396.5	264.8	172.4	158.3	154.6
75°	327.1	202.6	142.2	129.8	128.1
77.5°	257.9	143.9	112.0	104.9	101.3
80°	193.7	103.1	85.2	78.3	78.3
82.5°	135.1	69.4	58.6	55.1	55.1
85°	76.4	39.1	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5

TEST NUMBER: P913420

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1

TEST NUMBER: P913420

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.14	14.05	14.02	14.95	16.09	9.12	10.03	10.00	10.93	12.07
	3H	14.80	15.61	15.69	16.52	17.68	10.30	11.11	11.19	12.02	13.19
	4H	15.39	16.16	16.30	17.07	18.25	10.74	11.51	11.65	12.42	13.60
	6H	15.80	16.51	16.72	17.43	18.61	11.05	11.76	11.97	12.68	13.87
	8H	15.92	16.59	16.85	17.53	18.71	11.14	11.81	12.07	12.75	13.93
	12H	15.97	16.61	16.90	17.54	18.75	11.18	11.82	12.11	12.75	13.96
4H	2H	13.16	13.93	14.08	14.84	16.02	9.71	10.48	10.63	11.39	12.57
	3H	14.97	15.61	15.90	16.55	17.74	11.05	11.69	11.98	12.63	13.82
	4H	15.65	16.23	16.58	17.17	18.38	11.59	12.17	12.52	13.11	14.32
	6H	16.14	16.64	17.09	17.61	18.82	11.99	12.49	12.94	13.46	14.67
	8H	16.31	16.77	17.26	17.73	18.96	12.11	12.58	13.07	13.54	14.77
	12H	16.39	16.81	17.36	17.79	19.02	12.17	12.59	13.14	13.57	14.80
8H	4H	15.62	16.08	16.57	17.04	18.27	11.86	12.33	12.81	13.28	14.51
	6H	16.16	16.54	17.14	17.54	18.77	12.36	12.74	13.33	13.74	14.97
	8H	16.36	16.70	17.35	17.69	18.93	12.53	12.88	13.52	13.86	15.11
	12H	16.48	16.78	17.47	17.76	19.06	12.64	12.94	13.63	13.92	15.22
12H	4H	15.57	15.99	16.54	16.97	18.20	11.86	12.28	12.83	13.26	14.49
	6H	16.13	16.47	17.12	17.46	18.71	12.40	12.74	13.39	13.73	14.97
	8H	16.34	16.64	17.33	17.62	18.91	12.60	12.90	13.59	13.88	15.17