

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907733

Luminaire Tested: DFN2DIP-4P4F0-030D030US840-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907733
REPORT IS A COMBINATION OF REPORTS P900600 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-030D030US840-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5574.5 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 50.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907733

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907733

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	812	812	812
5°	814	800	805
10°	806	784	779
15°	795	759	739
20°	780	723	689
25°	765	683	642
30°	745	642	581
35°	725	598	528
40°	705	553	466
45°	682	502	411
50°	658	451	357
55°	633	397	305
60°	603	340	251
65°	570	282	226
70°	530	228	205
75°	479	201	187
80°	405	169	164
85°	283	115	125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 682 cd/sqm

TEST NUMBER: P907733

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	2.1
10°-20°	322.1	5.8
20°-30°	452.3	8.1
30°-40°	493.0	8.8
40°-50°	453.1	8.1
50°-60°	355.9	6.4
60°-70°	231.6	4.2
70°-80°	119.2	2.1
80°-90°	32.2	0.6
90°-100°	33.7	0.6
100°-110°	125.7	2.3
110°-120°	333.3	6.0
120°-130°	552.9	9.9
130°-140°	587.3	10.5
140°-150°	545.8	9.8
150°-160°	438.8	7.9
160°-170°	282.8	5.1
170°-180°	97.3	1.7
0°-30°	891.8	16.0
0°-40°	1384.8	24.8
0°-60°	2193.8	39.4
0°-90°	2576.9	46.2
90°-120°	492.7	8.8
90°-150°	2178.7	39.1
90°-180°	2998.0	53.8
0°-180°	5574.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	9	15	19	20	5
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P907733

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5

TEST NUMBER: P907733

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5

TEST NUMBER: P907733

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.08	6.88	7.08	7.88	9.21	2.04	2.84	3.04	3.84	5.17
	3H	7.76	8.48	8.77	9.49	10.84	3.23	3.94	4.23	4.96	6.30
	4H	8.37	9.05	9.39	10.06	11.42	3.68	4.36	4.70	5.37	6.73
	6H	8.80	9.42	9.83	10.44	11.81	4.00	4.62	5.03	5.64	7.01
	8H	8.93	9.52	9.96	10.55	11.92	4.09	4.68	5.12	5.72	7.08
	12H	8.99	9.55	10.03	10.58	11.97	4.13	4.70	5.17	5.73	7.11
4H	2H	6.09	6.77	7.12	7.79	9.14	2.63	3.31	3.66	4.33	5.68
	3H	7.93	8.49	8.96	9.53	10.90	3.98	4.55	5.02	5.59	6.96
	4H	8.62	9.14	9.66	10.17	11.56	4.53	5.05	5.57	6.08	7.47
	6H	9.14	9.58	10.19	10.64	12.03	4.95	5.39	6.00	6.45	7.84
	8H	9.32	9.73	10.37	10.78	12.19	5.08	5.50	6.13	6.55	7.95
	12H	9.42	9.79	10.49	10.85	12.26	5.15	5.52	6.22	6.59	7.99
8H	4H	8.59	9.00	9.64	10.05	11.45	4.81	5.23	5.87	6.28	7.68
	6H	9.16	9.50	10.23	10.59	11.99	5.34	5.68	6.41	6.77	8.17
	8H	9.38	9.68	10.46	10.76	12.18	5.53	5.83	6.61	6.90	8.32
	12H	9.52	9.78	10.61	10.86	12.32	5.65	5.91	6.73	6.98	8.44
12H	4H	8.54	8.91	9.61	9.98	11.39	4.82	5.19	5.89	6.26	7.66
	6H	9.14	9.43	10.22	10.51	11.93	5.39	5.68	6.47	6.76	8.18
	8H	9.36	9.62	10.44	10.69	12.15	5.60	5.86	6.68	6.93	8.39

END OF REPORT