

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916098

Luminaire Tested: DFN2DIP-HX2F0-040D020US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916098
REPORT IS A COMBINATION OF REPORTS P899155 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D020US930-FLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4671.7 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916098

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916098

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US930-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30
7	61	48	40	34	58	46	39	33	42	35	31	38	33	29	34	30	26
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2990	2990	2990
5°	2990	2941	2963
10°	2961	2894	2917
15°	2912	2840	2849
20°	2849	2766	2779
25°	2785	2680	2700
30°	2707	2600	2600
35°	2633	2505	2495
40°	2542	2410	2395
45°	2451	2314	2292
50°	2351	2213	2173
55°	2247	2097	2063
60°	2128	1960	1936
65°	1998	1817	1787
70°	1832	1642	1625
75°	1605	1433	1469
80°	1329	1166	1186
85°	903	732	733

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2451 cd/sqm

TEST NUMBER: P916098

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	2.6
10°-20°	336.0	7.2
20°-30°	493.8	10.6
30°-40°	573.6	12.3
40°-50°	572.9	12.3
50°-60°	499.5	10.7
60°-70°	369.3	7.9
70°-80°	208.9	4.5
80°-90°	56.6	1.2
90°-100°	31.9	0.7
100°-110°	101.4	2.2
110°-120°	173.5	3.7
120°-130°	228.2	4.9
130°-140°	256.1	5.5
140°-150°	251.2	5.4
150°-160°	210.7	4.5
160°-170°	139.7	3.0
170°-180°	48.8	1.0
0°-30°	949.3	20.3
0°-40°	1522.9	32.6
0°-60°	2595.3	55.6
0°-90°	3230.1	69.1
90°-120°	306.8	6.6
90°-150°	1042.3	22.3
90°-180°	1442.0	30.9
0°-180°	4671.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	0	6	15	14	15	4
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	

TEST NUMBER: P916098

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0

TEST NUMBER: P916098

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7

TEST NUMBER: P916098

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.54	13.61	13.32	14.40	15.37	12.12	13.18	12.89	13.98	14.95
	3H	14.19	15.15	14.98	15.96	16.95	13.73	14.69	14.52	15.49	16.49
	4H	14.77	15.68	15.58	16.49	17.50	14.31	15.22	15.12	16.03	17.04
	6H	15.16	16.00	15.98	16.82	17.84	14.70	15.54	15.52	16.36	17.38
	8H	15.26	16.06	16.09	16.90	17.92	14.81	15.60	15.63	16.44	17.47
	12H	15.31	16.07	16.14	16.90	17.95	14.85	15.61	15.68	16.44	17.49
4H	2H	13.02	13.92	13.83	14.74	15.75	12.68	13.58	13.49	14.40	15.41
	3H	14.87	15.63	15.69	16.48	17.50	14.49	15.24	15.31	16.09	17.12
	4H	15.58	16.26	16.41	17.11	18.16	15.18	15.87	16.02	16.71	17.77
	6H	16.08	16.67	16.93	17.54	18.60	15.68	16.28	16.53	17.15	18.21
	8H	16.22	16.78	17.08	17.64	18.71	15.82	16.38	16.68	17.25	18.32
	12H	16.29	16.79	17.17	17.68	18.76	15.89	16.39	16.76	17.27	18.35
8H	4H	15.78	16.33	16.63	17.20	18.27	15.43	15.98	16.28	16.85	17.92
	6H	16.39	16.85	17.27	17.76	18.83	16.04	16.50	16.92	17.40	18.48
	8H	16.59	17.00	17.49	17.90	18.99	16.24	16.65	17.13	17.55	18.64
	12H	16.72	17.08	17.61	17.97	19.11	16.35	16.71	17.25	17.60	18.75
12H	4H	15.77	16.27	16.65	17.16	18.23	15.43	15.93	16.30	16.81	17.89
	6H	16.42	16.82	17.31	17.73	18.81	16.07	16.48	16.97	17.38	18.47
	8H	16.65	17.01	17.54	17.90	19.04	16.30	16.66	17.20	17.56	18.70