

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916129

Luminaire Tested: DFN2DIP-HX2F0-050D040US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916129
REPORT IS A COMBINATION OF REPORTS P900698 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-050D040US930-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6693.5 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916129

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916129

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	99	95	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43
3	83	74	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	35	32
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3970	3970	3970
5°	3970	3897	3924
10°	3924	3811	3789
15°	3864	3676	3585
20°	3786	3494	3337
25°	3706	3291	3098
30°	3602	3084	2798
35°	3499	2863	2533
40°	3393	2634	2232
45°	3272	2382	1959
50°	3146	2129	1693
55°	3013	1859	1438
60°	2860	1579	1176
65°	2682	1295	1051
70°	2467	1030	941
75°	2197	890	842
80°	1808	721	708
85°	1182	444	496

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3272 cd/sqm

TEST NUMBER: P916129

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	2.4
10°-20°	433.5	6.5
20°-30°	608.6	9.1
30°-40°	663.4	9.9
40°-50°	609.7	9.1
50°-60°	478.8	7.2
60°-70°	311.7	4.7
70°-80°	160.4	2.4
80°-90°	42.9	0.6
90°-100°	36.3	0.5
100°-110°	135.3	2.0
110°-120°	358.8	5.4
120°-130°	595.1	8.9
130°-140°	632.1	9.4
140°-150°	587.5	8.8
150°-160°	472.3	7.1
160°-170°	304.4	4.5
170°-180°	104.8	1.6
0°-30°	1200.0	17.9
0°-40°	1863.4	27.8
0°-60°	2951.9	44.1
0°-90°	3466.9	51.8
90°-120°	530.4	7.9
90°-150°	2345.2	35.0
90°-180°	3227.0	48.2
0°-180°	6693.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1685	1677	1657	1671	1667	160
15°	1602	1586	1534	1505	1490	452
25°	1455	1406	1305	1243	1220	669
35°	1253	1176	1042	945	912	784
45°	1025	922	762	654	617	791
55°	779	660	496	404	375	696
65°	526	402	265	214	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	1	10	16	20	21	6
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	

TEST NUMBER: P916129

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.8	1684.8	1684.8	1684.8	1684.8
2.5°	1692.4	1684.8	1668.0	1683.3	1680.2
5°	1684.8	1677.2	1657.3	1671.0	1666.6
7.5°	1671.0	1662.0	1640.6	1646.7	1639.0
10°	1652.8	1642.1	1611.7	1607.0	1597.9
12.5°	1629.9	1616.2	1575.0	1565.9	1549.1
15°	1602.5	1585.7	1533.9	1505.0	1489.7
17.5°	1570.4	1546.1	1482.0	1448.5	1424.0
20°	1533.9	1503.3	1427.1	1389.1	1355.4
22.5°	1494.3	1459.1	1370.7	1318.9	1296.1
25°	1454.6	1405.7	1305.1	1242.7	1219.7
27.5°	1407.4	1355.4	1244.1	1172.5	1137.4
30°	1357.1	1299.0	1177.0	1099.3	1058.1
32.5°	1308.2	1238.0	1113.1	1021.6	983.4
35°	1253.4	1175.6	1041.5	945.3	911.7
37.5°	1200.0	1116.1	974.4	869.0	831.0
40°	1143.5	1052.1	904.1	795.9	756.3
42.5°	1085.7	988.1	834.1	721.1	683.1
45°	1024.7	922.4	762.4	654.0	617.4
47.5°	966.7	858.5	693.8	585.5	552.0
50°	902.7	794.4	626.7	521.4	489.5
52.5°	840.1	725.7	562.6	462.0	433.1
55°	779.1	660.1	495.5	404.1	375.1
57.5°	716.6	594.7	436.1	350.7	326.3
60°	652.6	530.6	373.5	295.9	271.4
62.5°	590.1	468.1	320.2	247.0	234.9
65°	526.0	402.5	265.3	213.5	208.9
67.5°	465.0	341.5	213.5	187.5	183.0
70°	401.0	282.1	176.8	161.6	155.5
72.5°	340.1	227.1	147.9	135.7	132.6
75°	280.5	173.7	122.0	111.3	109.8
77.5°	221.1	123.4	96.1	89.9	86.8
80°	166.2	88.5	73.1	67.1	67.1
82.5°	115.9	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.5	12.1	12.1	10.7	10.7
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9



TEST NUMBER: P916129

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P916129

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.97	12.81	12.92	13.77	15.02	7.95	8.79	8.90	9.75	11.00
	3H	13.62	14.38	14.58	15.34	16.62	9.12	9.88	10.08	10.85	12.12
	4H	14.21	14.93	15.19	15.90	17.18	9.56	10.28	10.54	11.25	12.53
	6H	14.61	15.27	15.60	16.25	17.54	9.87	10.53	10.85	11.50	12.80
	8H	14.73	15.36	15.72	16.35	17.64	9.95	10.58	10.94	11.57	12.86
	12H	14.78	15.38	15.78	16.37	17.68	9.99	10.58	10.98	11.57	12.88
4H	2H	11.98	12.70	12.96	13.67	14.95	8.53	9.25	9.51	10.22	11.50
	3H	13.78	14.38	14.77	15.38	16.67	9.86	10.46	10.85	11.46	12.75
	4H	14.46	15.00	15.46	16.00	17.31	10.40	10.94	11.40	11.94	13.25
	6H	14.95	15.42	15.96	16.44	17.75	10.80	11.27	11.81	12.28	13.60
	8H	15.11	15.55	16.12	16.56	17.89	10.92	11.35	11.93	12.37	13.70
	12H	15.19	15.59	16.22	16.61	17.95	10.97	11.37	12.00	12.39	13.73
8H	4H	14.42	14.86	15.43	15.87	17.20	10.66	11.10	11.67	12.11	13.44
	6H	14.96	15.32	16.00	16.38	17.70	11.16	11.52	12.19	12.57	13.90
	8H	15.16	15.48	16.20	16.52	17.87	11.34	11.65	12.38	12.69	14.04
	12H	15.28	15.56	16.33	16.60	17.99	11.44	11.72	12.49	12.76	14.15
12H	4H	14.37	14.77	15.40	15.79	17.13	10.67	11.06	11.69	12.09	13.42
	6H	14.94	15.25	15.98	16.29	17.64	11.20	11.52	12.24	12.56	13.91
	8H	15.14	15.42	16.18	16.45	17.84	11.40	11.68	12.44	12.71	14.10