

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918789

Luminaire Tested: DFN2DIP-HX2F0-020D020US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918789
REPORT IS A COMBINATION OF REPORTS P900672 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D020US935-RLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3168.5 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 30.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918789
CATALOG NUMBER: DFN2DIP-HX2F0-020D020US935-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P918789
 CATALOG NUMBER: DFN2DIP-HX2F0-020D020US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46			46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40			40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39	34			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34	29			29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	26			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23			23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16			16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1677	1677	1677
5°	1677	1646	1658
10°	1658	1610	1601
15°	1632	1553	1515
20°	1599	1476	1410
25°	1566	1390	1309
30°	1521	1303	1182
35°	1478	1209	1070
40°	1433	1113	943
45°	1382	1006	827
50°	1329	900	715
55°	1273	785	607
60°	1208	667	497
65°	1133	547	444
70°	1042	435	398
75°	928	376	356
80°	764	305	299
85°	498	188	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1382 cd/sqm



TEST NUMBER: P918789

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	2.1
10°-20°	183.1	5.8
20°-30°	257.1	8.1
30°-40°	280.2	8.8
40°-50°	257.6	8.1
50°-60°	202.3	6.4
60°-70°	131.7	4.2
70°-80°	67.8	2.1
80°-90°	18.3	0.6
90°-100°	19.2	0.6
100°-110°	71.4	2.3
110°-120°	189.5	6.0
120°-130°	314.2	9.9
130°-140°	333.8	10.5
140°-150°	310.2	9.8
150°-160°	249.4	7.9
160°-170°	160.7	5.1
170°-180°	55.3	1.7
0°-30°	506.9	16.0
0°-40°	787.1	24.8
0°-60°	1247.0	39.4
0°-90°	1464.7	46.2
90°-120°	280.0	8.8
90°-150°	1238.3	39.1
90°-180°	1704.0	53.8
0°-180°	3168.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	0	5	8	10	11	3
95°	27	13	16	18	18	32
105°	128	140	26	30	32	137
115°	242	249	260	65	34	238
125°	342	347	355	358	360	305
135°	423	430	434	438	437	327
145°	491	490	498	500	498	307
155°	540	537	542	544	541	249
165°	569	567	568	571	568	161
175°	582	580	580	583	579	55
180°	581	581	581	581	581	



TEST NUMBER: P918789

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	0.4	5.1	8.4	10.5	11.4
92.5°	10.5	8.9	10.1	10.9	11.4
95°	27.3	13.4	16.4	18.5	18.1
97.5°	49.2	14.7	21.4	22.7	23.2
100°	74.5	16.8	23.9	27.3	28.2
102.5°	102.2	101.3	24.8	29.4	30.7
105°	127.9	140.4	25.7	30.2	31.9
107.5°	157.7	168.2	26.5	31.1	32.8
110°	186.3	195.1	73.6	31.6	33.2



TEST NUMBER: P918789

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US935-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.2	220.8	213.6	32.4	33.7
115°	241.8	248.9	259.5	64.7	34.5
117.5°	266.6	275.0	282.1	222.1	111.8
120°	294.4	300.7	308.2	313.3	256.5
122.5°	317.9	324.6	333.0	335.5	336.0
125°	341.9	347.3	355.3	358.3	359.6
127.5°	363.8	369.6	376.0	380.1	380.6
130°	384.3	391.1	395.7	400.4	399.9
132.5°	405.4	410.9	415.4	419.2	418.9
135°	423.1	429.8	433.5	437.8	437.0
137.5°	441.5	446.6	450.8	455.0	453.7
140°	459.6	463.0	467.6	471.4	469.3
142.5°	474.8	477.8	483.2	486.5	484.4
145°	490.8	490.3	497.5	500.4	498.3
147.5°	504.6	503.3	510.5	512.6	510.9
150°	518.1	515.1	521.9	524.3	522.3
152.5°	529.4	526.1	532.4	534.9	531.9
155°	540.4	536.6	541.7	544.2	540.8
157.5°	549.2	545.9	549.7	552.6	549.2
160°	556.8	554.2	556.8	559.3	556.4
162.5°	563.4	560.9	563.1	566.0	562.2
165°	569.4	566.9	568.1	571.1	568.1
167.5°	574.0	571.4	572.7	575.7	571.9
170°	577.8	575.2	576.1	579.0	575.2
172.5°	580.3	577.8	578.7	581.6	577.8
175°	582.4	579.5	580.3	583.2	579.0
177.5°	583.2	580.3	580.7	583.7	579.9
180°	581.2	581.2	581.2	581.2	581.2



TEST NUMBER: P918789
 CATALOG NUMBER: DFN2DIP-HX2F0-020D020US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.44	9.24	9.44	10.25	11.57	4.43	5.23	5.42	6.23	7.56
	3H	10.09	10.81	11.10	11.82	13.17	5.60	6.31	6.60	7.32	8.67
	4H	10.68	11.36	11.70	12.37	13.73	6.03	6.71	7.05	7.73	9.08
	6H	11.08	11.71	12.11	12.72	14.09	6.34	6.96	7.37	7.98	9.35
	8H	11.20	11.79	12.23	12.83	14.19	6.42	7.01	7.45	8.05	9.41
	12H	11.25	11.81	12.29	12.84	14.23	6.46	7.02	7.49	8.05	9.43
4H	2H	8.45	9.13	9.48	10.15	11.50	5.01	5.68	6.03	6.70	8.05
	3H	10.25	10.81	11.28	11.86	13.23	6.33	6.89	7.37	7.94	9.31
	4H	10.92	11.44	11.96	12.47	13.86	6.86	7.38	7.90	8.41	9.81
	6H	11.41	11.85	12.46	12.91	14.30	7.26	7.70	8.31	8.76	10.15
	8H	11.57	11.99	12.62	13.04	14.44	7.38	7.79	8.43	8.84	10.25
	12H	11.65	12.03	12.72	13.09	14.50	7.44	7.81	8.50	8.87	10.28
8H	4H	10.88	11.30	11.94	12.35	13.75	7.13	7.54	8.18	8.59	9.99
	6H	11.42	11.76	12.50	12.86	14.26	7.62	7.96	8.69	9.05	10.45
	8H	11.62	11.92	12.70	13.00	14.42	7.80	8.10	8.88	9.17	10.59
	12H	11.74	12.00	12.83	13.08	14.54	7.90	8.16	8.99	9.24	10.70
12H	4H	10.83	11.21	11.90	12.27	13.68	7.13	7.50	8.20	8.56	9.97
	6H	11.40	11.70	12.48	12.77	14.19	7.66	7.96	8.74	9.04	10.46
	8H	11.60	11.86	12.68	12.93	14.39	7.86	8.12	8.94	9.19	10.65