

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918794

Luminaire Tested: DFN2DIP-HX2F0-020D040US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918794
REPORT IS A COMBINATION OF REPORTS P899171 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D040US935-FLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4752.7 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918794

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918794

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1579	1579	1579
5°	1579	1553	1564
10°	1563	1528	1540
15°	1538	1499	1504
20°	1504	1461	1468
25°	1471	1415	1426
30°	1429	1373	1373
35°	1390	1323	1318
40°	1342	1273	1264
45°	1294	1222	1210
50°	1242	1169	1147
55°	1186	1107	1089
60°	1123	1035	1022
65°	1054	960	944
70°	967	867	858
75°	847	757	776
80°	702	616	625
85°	475	386	388

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1462 cd/sqm

TEST NUMBER: P918794

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.3
10°-20°	177.4	3.7
20°-30°	260.8	5.5
30°-40°	302.9	6.4
40°-50°	302.5	6.4
50°-60°	263.8	5.5
60°-70°	195.0	4.1
70°-80°	110.3	2.3
80°-90°	32.2	0.7
90°-100°	67.4	1.4
100°-110°	214.2	4.5
110°-120°	366.5	7.7
120°-130°	482.0	10.1
130°-140°	541.0	11.4
140°-150°	530.5	11.2
150°-160°	445.0	9.4
160°-170°	295.1	6.2
170°-180°	103.2	2.2
0°-30°	501.3	10.5
0°-40°	804.1	16.9
0°-60°	1370.4	28.8
0°-90°	1707.9	35.9
90°-120°	648.0	13.6
90°-150°	2201.5	46.3
90°-180°	3045.0	64.1
0°-180°	4752.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	670	670	670	670	670	
5°	670	668	660	666	664	64
15°	638	634	626	628	625	180
25°	577	572	561	562	561	266
35°	498	492	481	477	474	311
45°	405	401	391	384	381	313
55°	307	303	295	287	284	274
65°	207	203	197	191	188	205
75°	108	107	104	100	101	116
85°	26	26	25	23	23	29
90°	1	12	32	30	31	5
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	

TEST NUMBER: P918794

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	670.0	670.0	670.0	670.0	670.0
2.5°	673.9	670.7	663.6	670.0	668.8
5°	670.0	667.5	660.4	665.6	664.3
7.5°	665.6	661.7	654.6	659.8	658.5
10°	658.5	654.0	646.3	651.3	649.5
12.5°	648.8	645.0	637.2	640.4	639.1
15°	637.8	634.0	625.6	628.2	625.0
17.5°	624.3	620.5	612.1	615.3	612.1
20°	609.5	605.6	596.6	598.6	596.0
22.5°	594.7	588.9	580.5	580.5	579.2
25°	577.3	572.1	561.2	562.4	561.2
27.5°	557.9	553.4	545.1	543.2	539.9
30°	538.6	533.5	523.8	521.9	519.3
32.5°	518.0	514.2	503.9	500.0	497.4
35°	498.1	491.6	481.3	477.4	474.2
37.5°	475.5	469.7	459.3	454.9	451.6
40°	452.3	447.1	436.8	431.1	428.4
42.5°	429.7	424.6	414.3	407.9	404.0
45°	405.3	400.8	391.1	384.0	381.4
47.5°	381.4	376.9	366.6	359.5	355.7
50°	356.3	353.1	344.1	335.0	331.8
52.5°	331.8	327.3	318.9	311.9	307.4
55°	306.7	302.8	295.1	287.4	284.1
57.5°	281.5	278.4	269.9	262.3	259.6
60°	256.4	253.9	244.9	237.7	235.8
62.5°	232.0	227.4	221.0	214.6	212.0
65°	206.8	202.9	196.6	190.7	187.5
67.5°	181.1	177.8	172.0	167.6	165.0
70°	157.2	154.6	148.8	144.3	141.8
72.5°	132.8	130.2	126.9	122.4	120.5
75°	108.2	107.0	103.7	99.9	101.2
77.5°	86.4	83.8	82.4	80.5	78.6
80°	64.5	63.8	62.5	60.5	59.2
82.5°	43.8	43.8	43.2	40.6	40.6
85°	26.3	25.7	25.1	23.2	22.6
87.5°	11.6	10.3	9.0	7.1	6.5
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1

TEST NUMBER: P918794

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2

TEST NUMBER: P918794

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.26	8.01	8.33	9.08	10.54	6.84	7.58	7.90	8.65	10.11
	3H	8.88	9.55	9.96	10.63	12.11	8.42	9.09	9.50	10.17	11.65
	4H	9.45	10.09	10.54	11.17	12.65	8.99	9.63	10.08	10.71	12.19
	6H	9.82	10.41	10.92	11.49	12.99	9.37	9.95	10.46	11.04	12.53
	8H	9.92	10.47	11.02	11.57	13.06	9.46	10.02	10.56	11.12	12.60
	12H	9.95	10.48	11.06	11.57	13.09	9.49	10.02	10.60	11.11	12.63
4H	2H	7.70	8.33	8.79	9.41	10.90	7.36	7.99	8.45	9.07	10.56
	3H	9.52	10.05	10.62	11.16	12.66	9.14	9.67	10.24	10.78	12.27
	4H	10.21	10.70	11.32	11.80	13.31	9.82	10.31	10.93	11.40	12.92
	6H	10.70	11.12	11.81	12.24	13.75	10.30	10.72	11.42	11.84	13.35
	8H	10.83	11.22	11.95	12.34	13.86	10.43	10.82	11.55	11.94	13.46
	12H	10.89	11.24	12.02	12.37	13.90	10.48	10.84	11.62	11.96	13.49
8H	4H	10.39	10.78	11.50	11.89	13.42	10.04	10.43	11.15	11.54	13.07
	6H	10.99	11.31	12.12	12.46	13.99	10.63	10.96	11.77	12.11	13.63
	8H	11.19	11.47	12.33	12.61	14.15	10.83	11.11	11.97	12.25	13.79
	12H	11.30	11.55	12.44	12.68	14.26	10.93	11.18	12.08	12.31	13.89
12H	4H	10.37	10.72	11.50	11.84	13.38	10.02	10.38	11.15	11.50	13.03
	6H	11.01	11.29	12.15	12.43	13.97	10.67	10.95	11.81	12.09	13.63
	8H	11.23	11.48	12.37	12.61	14.19	10.88	11.13	12.03	12.26	13.84