

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918797

Luminaire Tested: DFN2DIP-HX2F0-020D040US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918797
REPORT IS A COMBINATION OF REPORTS P900692 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D040US935-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4873.2 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918797

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918797

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1677	1677	1677
5°	1677	1646	1658
10°	1658	1610	1601
15°	1632	1553	1515
20°	1599	1476	1410
25°	1566	1390	1309
30°	1521	1303	1182
35°	1478	1209	1070
40°	1433	1113	943
45°	1382	1006	827
50°	1329	900	715
55°	1273	785	607
60°	1208	667	497
65°	1133	547	444
70°	1042	435	398
75°	928	376	356
80°	764	305	299
85°	498	188	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1382 cd/sqm

TEST NUMBER: P918797

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.4
10°-20°	183.1	3.8
20°-30°	257.1	5.3
30°-40°	280.2	5.8
40°-50°	257.6	5.3
50°-60°	202.3	4.2
60°-70°	131.7	2.7
70°-80°	67.8	1.4
80°-90°	19.3	0.4
90°-100°	38.3	0.8
100°-110°	142.9	2.9
110°-120°	378.9	7.8
120°-130°	628.5	12.9
130°-140°	667.6	13.7
140°-150°	620.4	12.7
150°-160°	498.8	10.2
160°-170°	321.4	6.6
170°-180°	110.6	2.3
0°-30°	506.9	10.4
0°-40°	787.1	16.2
0°-60°	1247.0	25.6
0°-90°	1465.8	30.1
90°-120°	560.1	11.5
90°-150°	2476.6	50.8
90°-180°	3407.0	69.9
0°-180°	4873.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	1	10	17	21	23	5
95°	55	27	33	37	36	65
105°	256	281	51	60	64	273
115°	484	498	519	130	69	476
125°	684	695	711	717	719	610
135°	846	860	867	876	874	654
145°	982	981	995	1001	997	614
155°	1081	1073	1083	1088	1082	498
165°	1139	1134	1136	1142	1136	322
175°	1165	1159	1161	1166	1158	111
180°	1162	1162	1162	1162	1162	

TEST NUMBER: P918797

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	0.8	10.1	16.8	21.1	22.6
92.5°	21.1	17.7	20.1	21.9	22.6
95°	54.6	26.9	32.7	37.0	36.2
97.5°	98.4	29.4	42.9	45.5	46.2
100°	148.9	33.7	48.0	54.6	56.3
102.5°	204.3	202.8	49.6	58.8	61.4
105°	255.6	280.9	51.3	60.5	63.9
107.5°	315.4	336.4	53.0	62.3	65.6
110°	372.6	390.2	147.2	63.1	66.4

TEST NUMBER: P918797

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	426.5	441.5	427.2	64.7	67.3
115°	483.5	497.8	518.9	129.5	69.1
117.5°	533.2	550.0	564.4	444.0	223.7
120°	588.8	601.3	616.5	626.6	513.1
122.5°	635.8	649.3	666.2	671.1	672.0
125°	683.7	694.7	710.7	716.6	719.1
127.5°	727.5	739.3	751.9	760.3	761.1
130°	768.7	782.2	791.3	800.6	799.9
132.5°	810.7	821.7	830.9	838.5	837.8
135°	846.1	859.6	867.1	875.5	873.9
137.5°	883.0	893.1	901.6	910.0	907.5
140°	919.2	926.0	935.2	942.8	938.6
142.5°	949.6	955.4	966.4	973.0	968.9
145°	981.5	980.7	994.9	1000.8	996.6
147.5°	1009.2	1006.7	1021.0	1025.2	1021.9
150°	1036.1	1030.3	1043.8	1048.8	1044.6
152.5°	1058.9	1052.1	1064.7	1069.8	1063.9
155°	1080.7	1073.2	1083.3	1088.3	1081.6
157.5°	1098.4	1091.7	1099.3	1105.2	1098.4
160°	1113.5	1108.4	1113.5	1118.5	1112.7
162.5°	1127.0	1122.0	1126.2	1132.0	1124.5
165°	1138.8	1133.8	1136.3	1142.1	1136.3
167.5°	1148.1	1142.9	1145.6	1151.4	1143.8
170°	1155.6	1150.6	1152.2	1158.1	1150.6
172.5°	1160.6	1155.6	1157.4	1163.2	1155.6
175°	1164.8	1158.9	1160.6	1166.5	1158.1
177.5°	1166.5	1160.6	1161.5	1167.4	1159.9
180°	1162.3	1162.3	1162.3	1162.3	1162.3

TEST NUMBER: P918797

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.59	7.28	7.70	8.38	9.91	2.57	3.26	3.69	4.37	5.90
	3H	8.23	8.84	9.35	9.96	11.51	3.73	4.35	4.85	5.46	7.01
	4H	8.81	9.40	9.95	10.51	12.07	4.16	4.75	5.30	5.86	7.42
	6H	9.21	9.74	10.35	10.86	12.43	4.46	5.00	5.60	6.12	7.68
	8H	9.32	9.83	10.46	10.96	12.52	4.54	5.05	5.68	6.19	7.74
	12H	9.36	9.85	10.51	10.98	12.56	4.57	5.06	5.72	6.18	7.76
4H	2H	6.58	7.17	7.72	8.28	9.84	3.13	3.72	4.27	4.84	6.39
	3H	8.37	8.86	9.52	10.00	11.56	4.45	4.94	5.60	6.08	7.65
	4H	9.04	9.48	10.19	10.62	12.20	4.98	5.43	6.13	6.56	8.14
	6H	9.52	9.90	10.68	11.06	12.63	5.37	5.75	6.53	6.91	8.48
	8H	9.68	10.04	10.83	11.18	12.77	5.49	5.84	6.64	6.99	8.58
	12H	9.75	10.08	10.92	11.23	12.83	5.54	5.86	6.71	7.02	8.61
8H	4H	8.99	9.35	10.14	10.49	12.09	5.23	5.59	6.39	6.74	8.33
	6H	9.52	9.82	10.70	11.01	12.60	5.72	6.02	6.90	7.20	8.79
	8H	9.72	9.98	10.90	11.15	12.76	5.90	6.16	7.08	7.32	8.93
	12H	9.84	10.06	11.02	11.23	12.87	6.00	6.22	7.18	7.39	9.03
12H	4H	8.93	9.26	10.11	10.42	12.01	5.23	5.55	6.40	6.71	8.31
	6H	9.50	9.75	10.68	10.92	12.53	5.76	6.02	6.94	7.19	8.80
	8H	9.69	9.92	10.88	11.08	12.73	5.95	6.18	7.14	7.34	8.99

END OF REPORT