

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907826

Luminaire Tested: DFN2DIP-4P4F0-070D030US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907826
REPORT IS A COMBINATION OF REPORTS P899087 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D030US840-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9679.6 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 97.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907826

CATALOG NUMBER: DFN2DIP-4P4F0-070D030US840-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907826

CATALOG NUMBER: DFN2DIP-4P4F0-070D030US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	81	79	76	74	72	68	66	65
2	94	86	80	74	89	82	76	71	74	69	65	66	63	60	60	57	55
3	85	76	68	62	81	72	65	60	65	60	55	59	54	51	53	49	46
4	78	67	59	52	74	64	56	51	58	52	47	52	48	44	47	43	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	35	31	27
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1784	1784	1784
5°	1787	1760	1772
10°	1773	1737	1749
15°	1747	1709	1712
20°	1712	1670	1674
25°	1677	1623	1630
30°	1633	1579	1575
35°	1592	1528	1516
40°	1541	1476	1459
45°	1490	1423	1402
50°	1434	1369	1336
55°	1376	1305	1275
60°	1310	1230	1205
65°	1238	1153	1122
70°	1147	1058	1034
75°	1020	945	954
80°	868	801	798
85°	630	550	538

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1490 cd/sqm

TEST NUMBER: P907826

CATALOG NUMBER: DFN2DIP-4P4F0-070D030US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.9	2.7
10°-20°	728.4	7.5
20°-30°	1070.5	11.1
30°-40°	1243.3	12.8
40°-50°	1241.7	12.8
50°-60°	1082.8	11.2
60°-70°	800.4	8.3
70°-80°	452.9	4.7
80°-90°	122.3	1.3
90°-100°	59.3	0.6
100°-110°	188.4	1.9
110°-120°	322.4	3.3
120°-130°	424.0	4.4
130°-140°	475.9	4.9
140°-150°	466.7	4.8
150°-160°	391.5	4.0
160°-170°	259.6	2.7
170°-180°	90.7	0.9
0°-30°	2057.8	21.3
0°-40°	3301.1	34.1
0°-60°	5625.6	58.1
0°-90°	7001.1	72.3
90°-120°	570.1	5.9
90°-150°	1936.6	20.0
90°-180°	2678.0	27.7
0°-180°	9679.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2751	2751	2751	2751	2751	
5°	2751	2740	2711	2732	2727	261
15°	2618	2603	2568	2579	2566	737
25°	2370	2349	2304	2309	2304	1090
35°	2045	2018	1976	1960	1947	1277
45°	1664	1645	1605	1576	1566	1284
55°	1259	1243	1211	1180	1166	1126
65°	849	833	807	783	770	840
75°	444	439	426	410	415	474
85°	108	106	103	95	93	121
90°	1	10	28	27	28	9
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P907826

CATALOG NUMBER: DFN2DIP-4P4F0-070D030US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.6	2750.6	2750.6	2750.6	2750.6
2.5°	2766.6	2753.4	2724.2	2750.6	2745.5
5°	2750.6	2740.3	2711.1	2732.1	2727.0
7.5°	2732.1	2716.3	2687.2	2708.6	2703.2
10°	2703.2	2684.6	2652.9	2674.0	2666.1
12.5°	2663.3	2647.7	2616.0	2629.1	2623.7
15°	2618.5	2602.7	2568.2	2578.9	2565.7
17.5°	2562.8	2547.2	2512.6	2525.9	2512.6
20°	2501.9	2486.3	2449.2	2457.1	2446.7
22.5°	2441.3	2417.5	2383.0	2383.0	2377.6
25°	2369.9	2348.7	2303.9	2309.0	2303.9
27.5°	2290.4	2271.9	2237.7	2229.8	2216.6
30°	2211.3	2189.9	2150.4	2142.5	2131.8
32.5°	2126.5	2110.8	2068.4	2052.5	2041.7
35°	2044.6	2018.2	1975.8	1959.8	1946.6
37.5°	1952.0	1928.1	1885.7	1867.2	1854.0
40°	1856.8	1835.5	1793.1	1769.6	1758.9
42.5°	1764.2	1742.9	1700.8	1674.2	1658.4
45°	1663.8	1645.3	1605.4	1576.5	1565.8
47.5°	1565.8	1547.3	1504.9	1475.7	1460.1
50°	1462.6	1449.4	1412.3	1375.3	1362.1
52.5°	1362.1	1343.6	1309.4	1280.2	1261.6
55°	1259.1	1243.1	1211.4	1179.7	1166.5
57.5°	1155.9	1142.7	1108.1	1076.4	1065.8
60°	1052.6	1042.2	1005.2	976.0	968.2
62.5°	952.1	933.6	907.3	880.9	870.2
65°	849.2	833.1	806.8	782.9	769.7
67.5°	743.4	729.9	706.3	687.8	677.1
70°	645.4	634.8	610.9	592.4	582.0
72.5°	544.9	534.3	521.1	502.6	494.7
75°	444.2	439.2	425.7	410.0	415.4
77.5°	354.5	343.8	338.4	330.5	322.8
80°	264.6	261.9	256.5	248.6	243.3
82.5°	179.9	179.9	177.3	166.7	166.7
85°	108.4	105.8	103.3	95.1	92.6
87.5°	47.7	42.4	37.1	29.2	26.4
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0

TEST NUMBER: P907826

CATALOG NUMBER: DFN2DIP-4P4F0-070D030US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P907826

CATALOG NUMBER: DFN2DIP-4P4F0-070D030US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.15	12.25	11.89	13.01	13.93	10.70	11.81	11.44	12.57	13.48
	3H	12.83	13.83	13.58	14.60	15.54	12.34	13.34	13.09	14.10	15.05
	4H	13.43	14.37	14.20	15.15	16.11	12.94	13.88	13.71	14.66	15.61
	6H	13.85	14.72	14.63	15.51	16.47	13.35	14.22	14.13	15.00	15.97
	8H	13.97	14.79	14.76	15.60	16.57	13.46	14.29	14.26	15.10	16.07
	12H	14.02	14.81	14.82	15.61	16.61	13.51	14.30	14.31	15.10	16.10
4H	2H	11.64	12.58	12.41	13.36	14.31	11.28	12.22	12.06	13.00	13.96
	3H	13.53	14.32	14.32	15.13	16.10	13.13	13.91	13.91	14.72	15.69
	4H	14.26	14.97	15.06	15.79	16.79	13.84	14.55	14.64	15.36	16.36
	6H	14.80	15.41	15.61	16.25	17.26	14.36	14.98	15.18	15.82	16.82
	8H	14.95	15.53	15.78	16.37	17.38	14.52	15.09	15.34	15.93	16.95
	12H	15.04	15.56	15.88	16.42	17.44	14.59	15.11	15.43	15.97	16.99
8H	4H	14.48	15.06	15.30	15.89	16.91	14.10	14.68	14.92	15.51	16.53
	6H	15.13	15.61	15.98	16.48	17.50	14.74	15.22	15.59	16.10	17.12
	8H	15.35	15.78	16.22	16.65	17.69	14.96	15.39	15.82	16.26	17.29
	12H	15.50	15.88	16.36	16.74	17.83	15.09	15.46	15.95	16.33	17.42
12H	4H	14.48	15.00	15.32	15.85	16.87	14.11	14.63	14.95	15.48	16.51
	6H	15.16	15.59	16.02	16.46	17.49	14.79	15.21	15.65	16.08	17.12
	8H	15.42	15.79	16.28	16.65	17.75	15.04	15.41	15.90	16.27	17.37

END OF REPORT