

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918830

Luminaire Tested: DFN2DIP-HX2F0-040D030US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918830
REPORT IS A COMBINATION OF REPORTS P899165 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D030US935-FLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5695.4 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918830

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918830

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3157	3157	3157
5°	3157	3106	3129
10°	3127	3057	3080
15°	3076	2999	3009
20°	3009	2921	2935
25°	2942	2830	2851
30°	2859	2745	2746
35°	2780	2646	2635
40°	2685	2545	2529
45°	2588	2444	2420
50°	2483	2337	2295
55°	2373	2215	2178
60°	2247	2070	2045
65°	2109	1918	1888
70°	1934	1734	1716
75°	1695	1513	1551
80°	1403	1231	1252
85°	953	773	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2588 cd/sqm

TEST NUMBER: P918830

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	2.2
10°-20°	354.9	6.2
20°-30°	521.5	9.2
30°-40°	605.7	10.6
40°-50°	605.0	10.6
50°-60°	527.5	9.3
60°-70°	389.9	6.8
70°-80°	220.6	3.9
80°-90°	60.5	1.1
90°-100°	50.6	0.9
100°-110°	160.6	2.8
110°-120°	274.9	4.8
120°-130°	361.5	6.3
130°-140°	405.7	7.1
140°-150°	397.9	7.0
150°-160°	333.8	5.9
160°-170°	221.3	3.9
170°-180°	77.4	1.4
0°-30°	1002.5	17.6
0°-40°	1608.3	28.2
0°-60°	2740.7	48.1
0°-90°	3411.8	59.9
90°-120°	486.0	8.5
90°-150°	1651.1	29.0
90°-180°	2284.0	40.1
0°-180°	5695.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1340	1335	1321	1331	1329	127
15°	1276	1268	1251	1256	1250	359
25°	1154	1144	1122	1125	1122	531
35°	996	983	963	955	948	622
45°	810	802	782	768	763	626
55°	614	606	590	575	568	548
65°	414	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	59
90°	1	9	24	23	23	5
95°	36	43	44	44	43	40
105°	148	150	152	153	153	156
115°	276	280	278	278	276	273
125°	401	407	405	403	402	358
135°	519	526	528	527	525	401
145°	630	635	639	640	637	394
155°	720	722	724	728	726	332
165°	784	783	783	788	784	221
175°	816	814	812	817	813	77
180°	817	817	817	817	817	

TEST NUMBER: P918830

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.1	1340.1	1340.1	1340.1	1340.1
2.5°	1347.9	1341.4	1327.2	1340.1	1337.6
5°	1340.1	1335.0	1320.8	1331.0	1328.6
7.5°	1331.0	1323.4	1309.1	1319.6	1317.0
10°	1317.0	1307.9	1292.5	1302.8	1298.9
12.5°	1297.5	1289.9	1274.4	1280.9	1278.2
15°	1275.7	1268.0	1251.2	1256.4	1250.0
17.5°	1248.6	1241.0	1224.2	1230.5	1224.2
20°	1218.9	1211.3	1193.3	1197.0	1192.1
22.5°	1189.4	1177.8	1161.0	1161.0	1158.4
25°	1154.5	1144.3	1122.4	1124.9	1122.4
27.5°	1115.9	1106.8	1090.2	1086.3	1079.9
30°	1077.3	1066.9	1047.7	1043.8	1038.6
32.5°	1036.0	1028.4	1007.7	1000.0	994.7
35°	996.1	983.3	962.6	954.8	948.4
37.5°	951.0	939.3	918.7	909.7	903.3
40°	904.7	894.2	873.6	862.1	857.0
42.5°	859.5	849.1	828.6	815.6	808.0
45°	810.5	801.6	782.1	768.1	762.8
47.5°	762.8	753.8	733.2	719.0	711.4
50°	712.6	706.1	688.1	670.0	663.6
52.5°	663.6	654.6	637.9	623.7	614.7
55°	613.5	605.6	590.2	574.7	568.3
57.5°	563.1	556.7	539.8	524.4	519.3
60°	512.8	507.7	489.7	475.5	471.7
62.5°	463.9	454.9	442.0	429.1	424.0
65°	413.7	405.9	393.0	381.4	375.1
67.5°	362.1	355.6	344.1	335.1	329.9
70°	314.4	309.3	297.6	288.6	283.5
72.5°	265.5	260.3	253.9	244.9	241.0
75°	216.5	214.0	207.4	199.8	202.3
77.5°	172.6	167.5	164.9	161.0	157.2
80°	128.9	127.5	124.9	121.1	118.6
82.5°	87.6	87.6	86.4	81.2	81.2
85°	52.8	51.6	50.3	46.3	45.1
87.5°	23.2	20.7	18.1	14.2	12.8
90°	0.8	8.9	24.1	22.6	23.4
92.5°	15.2	20.7	21.4	22.1	22.1
95°	36.0	42.9	44.1	44.1	42.9
97.5°	59.8	66.2	69.0	69.0	69.0
100°	87.4	93.1	95.1	95.1	94.4
102.5°	116.5	120.7	123.4	124.2	123.4
105°	148.3	150.2	151.7	152.9	152.9
107.5°	179.8	182.7	182.7	183.2	179.8
110°	210.3	214.3	214.3	214.3	212.3

TEST NUMBER: P918830

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.3	247.5	246.8	244.8	243.3
115°	275.9	279.7	278.5	277.8	275.9
117.5°	308.1	313.5	310.0	308.1	306.1
120°	340.6	346.0	340.6	340.6	338.4
122.5°	370.1	377.0	373.6	371.6	370.1
125°	401.2	407.3	405.4	403.1	402.4
127.5°	431.4	439.1	436.4	433.4	431.4
130°	459.8	468.6	467.4	466.0	463.2
132.5°	491.5	498.4	498.9	495.5	493.5
135°	518.9	526.5	528.0	527.3	525.3
137.5°	549.4	555.6	556.8	556.4	553.4
140°	576.3	582.5	585.9	585.9	583.2
142.5°	603.9	610.0	612.0	612.8	610.0
145°	630.0	634.9	638.9	639.5	636.9
147.5°	653.4	659.5	662.5	663.7	661.0
150°	677.5	681.7	684.4	686.6	684.4
152.5°	699.0	703.1	706.5	709.3	706.5
155°	720.4	722.3	724.5	728.0	725.8
157.5°	738.8	740.3	741.6	746.5	743.0
160°	755.4	756.8	757.6	761.7	758.8
162.5°	770.6	770.6	771.4	776.0	772.6
165°	783.7	782.9	782.9	787.8	784.4
167.5°	795.5	793.2	793.2	798.1	794.7
170°	804.3	802.4	801.7	806.6	802.4
172.5°	810.5	808.6	807.8	812.7	808.6
175°	815.5	813.5	812.0	816.9	812.7
177.5°	818.1	816.1	814.7	818.9	814.7
180°	816.9	816.9	816.9	816.9	816.9

TEST NUMBER: P918830

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.00	12.95	12.86	13.84	14.96	11.57	12.53	12.44	13.42	14.54
	3H	13.64	14.50	14.52	15.40	16.54	13.18	14.04	14.06	14.94	16.08
	4H	14.21	15.03	15.11	15.93	17.09	13.75	14.57	14.65	15.47	16.63
	6H	14.60	15.35	15.51	16.26	17.43	14.14	14.89	15.05	15.80	16.97
	8H	14.70	15.41	15.61	16.34	17.51	14.24	14.95	15.15	15.88	17.05
	12H	14.74	15.42	15.66	16.34	17.54	14.28	14.96	15.20	15.88	17.07
4H	2H	12.46	13.27	13.36	14.18	15.33	12.12	12.93	13.02	13.84	14.99
	3H	14.30	14.98	15.22	15.92	17.09	13.92	14.60	14.83	15.53	16.71
	4H	15.00	15.62	15.93	16.55	17.75	14.61	15.23	15.53	16.16	17.36
	6H	15.50	16.03	16.44	16.99	18.19	15.10	15.64	16.04	16.59	17.79
	8H	15.64	16.14	16.58	17.09	18.30	15.24	15.74	16.18	16.69	17.90
	12H	15.71	16.16	16.66	17.12	18.34	15.30	15.75	16.26	16.72	17.94
8H	4H	15.20	15.70	16.13	16.64	17.86	14.84	15.34	15.78	16.29	17.51
	6H	15.80	16.22	16.77	17.21	18.42	15.45	15.86	16.42	16.85	18.07
	8H	16.01	16.37	16.98	17.35	18.58	15.65	16.02	16.63	17.00	18.23
	12H	16.13	16.45	17.10	17.42	18.70	15.76	16.08	16.74	17.05	18.33
12H	4H	15.18	15.63	16.14	16.60	17.82	14.84	15.29	15.80	16.26	17.48
	6H	15.83	16.19	16.80	17.17	18.40	15.49	15.85	16.46	16.83	18.06
	8H	16.06	16.38	17.03	17.35	18.63	15.71	16.03	16.69	17.01	18.28