

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907847

Luminaire Tested: DFN2DIP-4P4F0-070D080US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907847
REPORT IS A COMBINATION OF REPORTS P900667 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D080US840-FLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14996.5 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 147.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907847

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907847

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45			39
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38			33
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32			28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28			24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	27	24			21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	25	27	24	21			18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19			16
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	22	19	17			15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15			13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1784	1784	1784
5°	1787	1760	1772
10°	1773	1737	1749
15°	1747	1709	1712
20°	1712	1670	1674
25°	1677	1623	1630
30°	1633	1579	1575
35°	1592	1528	1516
40°	1541	1476	1459
45°	1490	1423	1402
50°	1434	1369	1336
55°	1376	1305	1275
60°	1310	1230	1205
65°	1238	1153	1122
70°	1147	1058	1034
75°	1020	945	954
80°	868	801	798
85°	630	550	538

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1490 cd/sqm

TEST NUMBER: P907847

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.9	1.7
10°-20°	728.4	4.9
20°-30°	1070.5	7.1
30°-40°	1243.3	8.3
40°-50°	1241.7	8.3
50°-60°	1082.8	7.2
60°-70°	800.4	5.3
70°-80°	452.9	3.0
80°-90°	124.3	0.8
90°-100°	89.9	0.6
100°-110°	335.1	2.2
110°-120°	888.9	5.9
120°-130°	1474.3	9.8
130°-140°	1566.0	10.4
140°-150°	1455.4	9.7
150°-160°	1170.1	7.8
160°-170°	754.0	5.0
170°-180°	259.5	1.7
0°-30°	2057.8	13.7
0°-40°	3301.1	22.0
0°-60°	5625.6	37.5
0°-90°	7003.2	46.7
90°-120°	1314.0	8.8
90°-150°	5809.7	38.7
90°-180°	7993.0	53.3
0°-180°	14996.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2751	2751	2751	2751	2751	
5°	2751	2740	2711	2732	2727	261
15°	2618	2603	2568	2579	2566	737
25°	2370	2349	2304	2309	2304	1090
35°	2045	2018	1976	1960	1947	1277
45°	1664	1645	1605	1576	1566	1284
55°	1259	1243	1211	1180	1166	1126
65°	849	833	807	783	770	840
75°	444	439	426	410	415	474
85°	108	106	103	95	93	121
90°	2	24	39	49	53	14
95°	128	63	77	87	85	152
105°	600	659	120	142	150	641
115°	1134	1168	1217	304	162	1117
125°	1604	1630	1667	1681	1687	1430
135°	1985	2016	2034	2054	2050	1533
145°	2302	2300	2334	2348	2338	1440
155°	2535	2518	2541	2553	2537	1168
165°	2671	2660	2665	2679	2665	755
175°	2732	2719	2723	2736	2717	260
180°	2726	2726	2726	2726	2726	

TEST NUMBER: P907847

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.6	2750.6	2750.6	2750.6	2750.6
2.5°	2766.6	2753.4	2724.2	2750.6	2745.5
5°	2750.6	2740.3	2711.1	2732.1	2727.0
7.5°	2732.1	2716.3	2687.2	2708.6	2703.2
10°	2703.2	2684.6	2652.9	2674.0	2666.1
12.5°	2663.3	2647.7	2616.0	2629.1	2623.7
15°	2618.5	2602.7	2568.2	2578.9	2565.7
17.5°	2562.8	2547.2	2512.6	2525.9	2512.6
20°	2501.9	2486.3	2449.2	2457.1	2446.7
22.5°	2441.3	2417.5	2383.0	2383.0	2377.6
25°	2369.9	2348.7	2303.9	2309.0	2303.9
27.5°	2290.4	2271.9	2237.7	2229.8	2216.6
30°	2211.3	2189.9	2150.4	2142.5	2131.8
32.5°	2126.5	2110.8	2068.4	2052.5	2041.7
35°	2044.6	2018.2	1975.8	1959.8	1946.6
37.5°	1952.0	1928.1	1885.7	1867.2	1854.0
40°	1856.8	1835.5	1793.1	1769.6	1758.9
42.5°	1764.2	1742.9	1700.8	1674.2	1658.4
45°	1663.8	1645.3	1605.4	1576.5	1565.8
47.5°	1565.8	1547.3	1504.9	1475.7	1460.1
50°	1462.6	1449.4	1412.3	1375.3	1362.1
52.5°	1362.1	1343.6	1309.4	1280.2	1261.6
55°	1259.1	1243.1	1211.4	1179.7	1166.5
57.5°	1155.9	1142.7	1108.1	1076.4	1065.8
60°	1052.6	1042.2	1005.2	976.0	968.2
62.5°	952.1	933.6	907.3	880.9	870.2
65°	849.2	833.1	806.8	782.9	769.7
67.5°	743.4	729.9	706.3	687.8	677.1
70°	645.4	634.8	610.9	592.4	582.0
72.5°	544.9	534.3	521.1	502.6	494.7
75°	444.2	439.2	425.7	410.0	415.4
77.5°	354.5	343.8	338.4	330.5	322.8
80°	264.6	261.9	256.5	248.6	243.3
82.5°	179.9	179.9	177.3	166.7	166.7
85°	108.4	105.8	103.3	95.1	92.6
87.5°	47.7	42.4	37.1	29.2	26.4
90°	1.9	23.6	39.4	49.4	53.2
92.5°	49.4	41.5	47.4	51.3	53.2
95°	128.2	63.0	76.9	86.9	84.8
97.5°	230.8	69.1	100.5	106.6	108.5
100°	349.3	79.0	112.5	128.2	132.1
102.5°	479.4	475.5	116.4	137.9	144.1
105°	599.8	659.0	120.4	142.0	150.0
107.5°	739.8	789.0	124.4	145.9	153.9
110°	874.1	915.3	345.4	148.0	155.8



TEST NUMBER: P907847

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1000.4	1035.7	1002.3	151.8	157.9
115°	1134.4	1167.9	1217.3	303.9	161.9
117.5°	1250.8	1290.2	1323.9	1041.6	524.8
120°	1381.1	1410.6	1446.2	1469.9	1203.5
122.5°	1491.4	1523.1	1562.7	1574.4	1576.5
125°	1603.9	1629.6	1667.1	1680.9	1686.8
127.5°	1706.5	1734.1	1763.9	1783.5	1785.4
130°	1803.2	1834.8	1856.4	1878.2	1876.3
132.5°	1901.9	1927.6	1949.2	1967.0	1965.1
135°	1984.8	2016.4	2034.0	2054.0	2049.9
137.5°	2071.5	2095.2	2115.1	2134.8	2128.9
140°	2156.3	2172.2	2193.8	2211.6	2201.7
142.5°	2227.6	2241.3	2266.8	2282.6	2272.7
145°	2302.5	2300.4	2333.9	2347.7	2337.8
147.5°	2367.4	2361.6	2395.0	2404.9	2397.1
150°	2430.6	2416.8	2448.4	2460.1	2450.3
152.5°	2483.9	2468.1	2497.6	2509.6	2495.8
155°	2535.2	2517.6	2541.2	2552.9	2537.3
157.5°	2576.6	2560.9	2578.7	2592.5	2576.6
160°	2612.2	2600.3	2612.2	2623.9	2610.1
162.5°	2643.6	2631.9	2641.7	2655.5	2637.8
165°	2671.3	2659.6	2665.4	2679.2	2665.4
167.5°	2693.0	2681.1	2687.2	2701.0	2683.2
170°	2710.9	2698.9	2702.9	2716.7	2698.9
172.5°	2722.6	2710.9	2714.8	2728.7	2710.9
175°	2732.4	2718.6	2722.6	2736.3	2716.7
177.5°	2736.3	2722.6	2724.6	2738.5	2720.7
180°	2726.5	2726.5	2726.5	2726.5	2726.5

TEST NUMBER: P907847

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.99	9.82	9.97	10.82	12.14	8.54	9.38	9.53	10.37	11.69
	3H	10.65	11.40	11.65	12.41	13.75	10.16	10.91	11.16	11.92	13.25
	4H	11.24	11.95	12.25	12.96	14.31	10.75	11.46	11.76	12.47	13.81
	6H	11.65	12.30	12.67	13.31	14.67	11.15	11.80	12.17	12.81	14.17
	8H	11.75	12.37	12.78	13.40	14.76	11.25	11.87	12.28	12.90	14.26
	12H	11.80	12.39	12.83	13.42	14.80	11.29	11.88	12.32	12.91	14.29
4H	2H	9.45	10.16	10.46	11.17	12.51	9.09	9.80	10.11	10.81	12.16
	3H	11.32	11.91	12.34	12.95	14.31	10.91	11.50	11.93	12.54	13.90
	4H	12.04	12.58	13.07	13.61	14.99	11.61	12.15	12.64	13.18	14.57
	6H	12.55	13.02	13.60	14.07	15.45	12.12	12.59	13.16	13.64	15.02
	8H	12.71	13.14	13.75	14.19	15.58	12.27	12.70	13.31	13.75	15.14
	12H	12.78	13.17	13.84	14.23	15.63	12.33	12.72	13.39	13.78	15.18
8H	4H	12.23	12.66	13.27	13.71	15.11	11.85	12.29	12.90	13.33	14.73
	6H	12.87	13.23	13.93	14.31	15.71	12.48	12.84	13.55	13.93	15.32
	8H	13.09	13.41	14.17	14.48	15.89	12.70	13.01	13.77	14.09	15.50
	12H	13.23	13.50	14.30	14.57	16.02	12.81	13.09	13.89	14.16	15.61
12H	4H	12.22	12.61	13.28	13.67	15.07	11.85	12.24	12.91	13.30	14.70
	6H	12.90	13.21	13.97	14.29	15.70	12.53	12.84	13.60	13.91	15.33
	8H	13.14	13.42	14.22	14.49	15.94	12.76	13.04	13.84	14.11	15.56