

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921529

Luminaire Tested: DFN2DIP-HX2F0-020D050US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921529
REPORT IS A COMBINATION OF REPORTS P900702 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D050US940-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5929.9 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921529

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921529

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20					20				20
RC	80				70				50					30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	88	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29	22
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	23	21	16
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19	14
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	36	29	25	28	24	20	21	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1737	1737	1737
5°	1737	1705	1717
10°	1717	1667	1658
15°	1690	1608	1569
20°	1656	1529	1460
25°	1622	1440	1355
30°	1576	1349	1224
35°	1530	1253	1108
40°	1484	1153	976
45°	1431	1042	857
50°	1376	931	741
55°	1318	814	629
60°	1251	691	515
65°	1174	567	460
70°	1079	450	412
75°	961	389	369
80°	791	315	309
85°	516	195	218

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1431 cd/sqm

TEST NUMBER: P921529

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	1.2
10°-20°	189.6	3.2
20°-30°	266.3	4.5
30°-40°	290.2	4.9
40°-50°	266.8	4.5
50°-60°	209.5	3.5
60°-70°	136.4	2.3
70°-80°	70.2	1.2
80°-90°	20.6	0.3
90°-100°	49.6	0.8
100°-110°	185.0	3.1
110°-120°	490.6	8.3
120°-130°	813.6	13.7
130°-140°	864.3	14.6
140°-150°	803.2	13.5
150°-160°	645.8	10.9
160°-170°	416.1	7.0
170°-180°	143.2	2.4
0°-30°	525.0	8.9
0°-40°	815.2	13.7
0°-60°	1291.4	21.8
0°-90°	1518.6	25.6
90°-120°	725.2	12.2
90°-150°	3206.2	54.1
90°-180°	4411.0	74.4
0°-180°	5929.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	737	734	725	731	729	70
15°	701	694	671	658	652	198
25°	636	615	571	544	534	293
35°	548	514	456	414	399	343
45°	448	404	334	286	270	346
55°	341	289	217	177	164	305
65°	230	176	116	94	91	228
75°	123	76	53	49	48	130
85°	29	15	13	13	13	33
90°	1	13	22	27	29	6
95°	71	35	42	48	47	84
105°	331	364	66	78	83	354
115°	626	644	672	168	89	616
125°	885	899	920	928	931	789
135°	1095	1113	1122	1134	1131	846
145°	1271	1270	1288	1296	1290	795
155°	1399	1389	1402	1409	1400	645
165°	1474	1468	1471	1478	1471	416
175°	1508	1500	1502	1510	1499	144
180°	1505	1505	1505	1505	1505	

TEST NUMBER: P921529

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US940-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	737.1	737.1	737.1	737.1	737.1
2.5°	740.4	737.1	729.7	736.5	735.1
5°	737.1	733.8	725.0	731.1	729.1
7.5°	731.1	727.1	717.7	720.4	717.0
10°	723.1	718.4	705.1	703.0	699.1
12.5°	713.1	707.0	689.0	685.1	677.7
15°	701.1	693.7	671.0	658.3	651.8
17.5°	687.1	676.4	648.4	633.6	623.0
20°	671.0	657.6	624.4	607.7	593.0
22.5°	653.7	638.4	599.7	577.0	567.0
25°	636.4	615.0	571.0	543.7	533.6
27.5°	615.7	593.0	544.3	512.9	497.6
30°	593.7	568.3	515.0	481.0	462.9
32.5°	572.3	541.6	487.0	446.9	430.3
35°	548.3	514.3	455.7	413.6	398.9
37.5°	524.9	488.2	426.2	380.2	363.6
40°	500.2	460.3	395.6	348.2	330.8
42.5°	474.9	432.3	364.9	315.5	298.9
45°	448.3	403.5	333.6	286.1	270.1
47.5°	422.9	375.6	303.5	256.1	241.5
50°	394.9	347.6	274.2	228.1	214.2
52.5°	367.5	317.4	246.1	202.2	189.5
55°	340.8	288.8	216.8	176.8	164.1
57.5°	313.5	260.1	190.8	153.5	142.8
60°	285.5	232.1	163.5	129.5	118.8
62.5°	258.2	204.8	140.1	108.1	102.7
65°	230.2	176.1	116.1	93.5	91.4
67.5°	203.5	149.4	93.5	82.0	80.1
70°	175.4	123.4	77.3	70.7	68.0
72.5°	148.7	99.3	64.6	59.4	58.1
75°	122.7	76.0	53.3	48.7	48.1
77.5°	96.8	54.0	42.0	39.3	38.0
80°	72.7	38.7	32.0	29.3	29.3
82.5°	50.6	26.0	22.0	20.7	20.7
85°	28.6	14.6	12.7	12.7	12.7
87.5°	10.7	5.4	5.4	4.6	4.6
90°	1.1	13.0	21.8	27.3	29.3
92.5°	27.3	22.9	26.1	28.4	29.3
95°	70.7	34.8	42.4	48.0	46.8
97.5°	127.3	38.2	55.5	58.9	59.8
100°	192.8	43.6	62.1	70.7	72.9
102.5°	264.6	262.4	64.3	76.2	79.5
105°	331.0	363.7	66.4	78.4	82.8
107.5°	408.3	435.4	68.7	80.5	85.0
110°	482.4	505.2	190.6	81.7	86.0

TEST NUMBER: P921529

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	552.1	571.6	553.1	83.8	87.1
115°	626.1	644.5	671.8	167.7	89.3
117.5°	690.3	712.0	730.7	574.8	289.6
120°	762.1	778.5	798.1	811.2	664.1
122.5°	823.0	840.5	862.4	868.9	870.0
125°	885.1	899.4	920.1	927.6	930.9
127.5°	941.7	957.0	973.5	984.3	985.3
130°	995.1	1012.6	1024.5	1036.5	1035.5
132.5°	1049.6	1063.8	1075.7	1085.6	1084.5
135°	1095.4	1112.9	1122.5	1133.5	1131.3
137.5°	1143.2	1156.3	1167.2	1178.1	1174.9
140°	1190.0	1198.8	1210.7	1220.5	1215.1
142.5°	1229.3	1237.0	1251.1	1259.7	1254.3
145°	1270.7	1269.5	1288.0	1295.7	1290.2
147.5°	1306.5	1303.2	1321.8	1327.2	1322.9
150°	1341.4	1333.8	1351.2	1357.7	1352.3
152.5°	1370.7	1362.1	1378.4	1385.0	1377.3
155°	1399.1	1389.4	1402.4	1408.9	1400.3
157.5°	1421.9	1413.3	1423.1	1430.7	1421.9
160°	1441.6	1435.0	1441.6	1448.0	1440.5
162.5°	1458.9	1452.5	1457.9	1465.5	1455.7
165°	1474.2	1467.8	1471.0	1478.5	1471.0
167.5°	1486.2	1479.6	1483.0	1490.6	1480.8
170°	1496.0	1489.4	1491.7	1499.2	1489.4
172.5°	1502.5	1496.0	1498.3	1505.8	1496.0
175°	1508.0	1500.3	1502.5	1510.1	1499.2
177.5°	1510.1	1502.5	1503.7	1511.3	1501.5
180°	1504.7	1504.7	1504.7	1504.7	1504.7

TEST NUMBER: P921529

CATALOG NUMBER: DFN2DIP-HX2F0-020D050US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.05	6.72	7.20	7.85	9.43	2.04	2.70	3.18	3.83	5.42
	3H	7.69	8.28	8.84	9.43	11.02	3.20	3.79	4.35	4.93	6.53
	4H	8.27	8.84	9.44	9.98	11.58	3.63	4.19	4.79	5.33	6.94
	6H	8.67	9.19	9.84	10.33	11.94	3.92	4.44	5.09	5.59	7.20
	8H	8.78	9.27	9.95	10.43	12.04	4.00	4.50	5.17	5.65	7.26
	12H	8.82	9.29	10.00	10.44	12.07	4.03	4.50	5.21	5.65	7.28
4H	2H	6.05	6.61	7.22	7.75	9.35	2.60	3.16	3.77	4.30	5.91
	3H	7.83	8.30	9.01	9.47	11.08	3.91	4.38	5.09	5.55	7.16
	4H	8.50	8.93	9.67	10.08	11.72	4.44	4.87	5.62	6.03	7.66
	6H	8.98	9.35	10.16	10.53	12.15	4.83	5.20	6.01	6.38	8.00
	8H	9.14	9.48	10.32	10.65	12.29	4.95	5.29	6.13	6.46	8.10
	12H	9.21	9.52	10.41	10.70	12.35	4.99	5.31	6.19	6.49	8.13
8H	4H	8.45	8.79	9.63	9.96	11.60	4.69	5.04	5.87	6.20	7.85
	6H	8.98	9.27	10.18	10.48	12.11	5.18	5.46	6.38	6.67	8.31
	8H	9.18	9.43	10.38	10.62	12.27	5.36	5.60	6.56	6.79	8.45
	12H	9.29	9.51	10.50	10.70	12.39	5.46	5.67	6.66	6.86	8.55
12H	4H	8.39	8.70	9.59	9.88	11.53	4.68	5.00	5.88	6.18	7.82
	6H	8.95	9.20	10.16	10.39	12.05	5.22	5.47	6.43	6.66	8.31
	8H	9.15	9.37	10.36	10.55	12.24	5.41	5.63	6.62	6.81	8.50

END OF REPORT