

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921548

Luminaire Tested: DFN2DIP-HX2F0-030D050US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921548
REPORT IS A COMBINATION OF REPORTS P899184 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-030D050US940-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6219.7 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921548

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921548

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32
3	79	70	64	58	72	64	58	53	52	48	45	41	39	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	38	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	16	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2605	2605	2605
5°	2605	2557	2575
10°	2575	2501	2487
15°	2536	2412	2353
20°	2485	2293	2190
25°	2432	2160	2033
30°	2364	2024	1836
35°	2296	1878	1662
40°	2227	1729	1465
45°	2147	1563	1286
50°	2064	1397	1111
55°	1977	1220	944
60°	1876	1036	772
65°	1760	850	690
70°	1619	676	617
75°	1441	584	553
80°	1187	473	466
85°	776	292	326

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2147 cd/sqm

TEST NUMBER: P921548

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.7
10°-20°	284.5	4.6
20°-30°	399.4	6.4
30°-40°	435.3	7.0
40°-50°	400.1	6.4
50°-60°	314.2	5.1
60°-70°	204.5	3.3
70°-80°	105.3	1.7
80°-90°	30.9	0.5
90°-100°	87.3	1.4
100°-110°	277.2	4.5
110°-120°	474.5	7.6
120°-130°	624.0	10.0
130°-140°	700.4	11.3
140°-150°	686.8	11.0
150°-160°	576.1	9.3
160°-170°	382.1	6.1
170°-180°	133.5	2.1
0°-30°	787.5	12.7
0°-40°	1222.8	19.7
0°-60°	1937.2	31.1
0°-90°	2277.8	36.6
90°-120°	838.9	13.5
90°-150°	2850.1	45.8
90°-180°	3942.0	63.4
0°-180°	6219.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1106	1101	1088	1097	1094	105
15°	1052	1040	1007	988	978	296
25°	955	922	856	816	800	439
35°	822	771	683	620	598	515
45°	672	605	500	429	405	519
55°	511	433	325	265	246	457
65°	345	264	174	140	137	342
75°	184	114	80	73	72	195
85°	43	22	19	19	19	49
90°	1	15	42	39	40	6
95°	62	74	76	76	74	69
105°	256	259	262	264	264	270
115°	476	483	481	480	476	471
125°	692	703	700	696	695	619
135°	896	909	911	910	907	692
145°	1087	1096	1103	1104	1099	679
155°	1243	1247	1251	1257	1253	572
165°	1353	1351	1351	1360	1354	382
175°	1408	1404	1402	1410	1403	134
180°	1410	1410	1410	1410	1410	

TEST NUMBER: P921548

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1105.6	1105.6	1105.6	1105.6	1105.6
2.5°	1110.6	1105.6	1094.6	1104.7	1102.7
5°	1105.6	1100.6	1087.6	1096.6	1093.6
7.5°	1096.6	1090.7	1076.7	1080.6	1075.6
10°	1084.6	1077.6	1057.7	1054.5	1048.7
12.5°	1069.6	1060.6	1033.6	1027.6	1016.5
15°	1051.6	1040.5	1006.6	987.6	977.6
17.5°	1030.5	1014.6	972.5	950.6	934.5
20°	1006.6	986.5	936.5	911.6	889.5
22.5°	980.6	957.5	899.5	865.5	850.5
25°	954.6	922.5	856.5	815.5	800.4
27.5°	923.5	889.5	816.5	769.5	746.4
30°	890.6	852.5	772.4	721.5	694.4
32.5°	858.4	812.4	730.5	670.4	645.3
35°	822.5	771.4	683.4	620.4	598.3
37.5°	787.5	732.4	639.4	570.2	545.4
40°	750.5	690.5	593.3	522.3	496.3
42.5°	712.4	648.5	547.3	473.2	448.3
45°	672.4	605.3	500.3	429.2	405.2
47.5°	634.4	563.4	455.3	384.1	362.2
50°	592.4	521.3	411.3	342.1	321.2
52.5°	551.3	476.3	369.3	303.2	284.2
55°	511.2	433.2	325.1	265.2	246.2
57.5°	470.3	390.2	286.2	230.2	214.1
60°	428.2	348.2	245.1	194.1	178.2
62.5°	387.3	307.2	210.1	162.1	154.2
65°	345.2	264.1	174.1	140.1	137.1
67.5°	305.2	224.1	140.1	123.1	120.0
70°	263.1	185.1	116.0	106.0	102.0
72.5°	223.1	149.0	97.0	89.1	87.0
75°	184.0	114.0	80.1	73.0	72.1
77.5°	145.1	81.0	63.0	59.0	57.0
80°	109.1	58.1	48.0	44.1	44.1
82.5°	76.0	39.1	33.0	31.0	31.0
85°	43.0	21.9	19.0	19.0	19.0
87.5°	16.1	7.9	7.9	7.0	7.0
90°	1.2	15.3	41.6	39.1	40.4
92.5°	26.4	35.7	37.0	38.3	38.3
95°	62.1	74.0	76.1	76.1	74.0
97.5°	103.3	114.3	119.0	119.0	119.0
100°	150.9	160.7	164.1	164.1	162.8
102.5°	201.1	208.3	212.9	214.3	212.9
105°	255.9	259.3	261.9	263.9	263.9
107.5°	310.3	315.4	315.4	316.3	310.3
110°	363.0	369.9	369.9	369.9	366.4

TEST NUMBER: P921548

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	420.0	427.2	426.0	422.6	420.0
115°	476.1	483.0	480.8	479.6	476.1
117.5°	531.8	541.2	535.2	531.8	528.4
120°	587.9	597.3	587.9	587.9	584.1
122.5°	638.9	650.9	644.9	641.5	638.9
125°	692.5	703.1	699.7	695.9	694.6
127.5°	744.8	758.0	753.3	748.1	744.8
130°	793.7	809.0	806.8	804.3	799.6
132.5°	848.6	860.4	861.3	855.3	851.9
135°	895.7	908.8	911.4	910.2	906.8
137.5°	948.4	959.0	961.2	960.3	955.2
140°	994.7	1005.4	1011.3	1011.3	1006.7
142.5°	1042.3	1053.0	1056.4	1057.7	1053.0
145°	1087.4	1095.9	1102.7	1104.0	1099.3
147.5°	1127.8	1138.4	1143.5	1145.7	1140.9
150°	1169.5	1176.7	1181.3	1185.2	1181.3
152.5°	1206.5	1213.7	1219.6	1224.3	1219.6
155°	1243.4	1246.8	1250.6	1256.6	1252.8
157.5°	1275.3	1277.8	1280.0	1288.5	1282.5
160°	1303.8	1306.4	1307.6	1314.8	1309.7
162.5°	1330.2	1330.2	1331.4	1339.5	1333.6
165°	1352.7	1351.4	1351.4	1359.9	1354.0
167.5°	1373.1	1369.2	1369.2	1377.8	1371.8
170°	1388.4	1385.0	1383.8	1392.2	1385.0
172.5°	1399.0	1395.6	1394.4	1402.8	1395.6
175°	1407.6	1404.1	1401.6	1410.1	1402.8
177.5°	1412.2	1408.8	1406.2	1413.5	1406.2
180°	1410.1	1410.1	1410.1	1410.1	1410.1

TEST NUMBER: P921548

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.94	9.67	10.01	10.74	12.19	4.92	5.66	5.99	6.72	8.18
	3H	10.58	11.24	11.66	12.32	13.79	6.09	6.74	7.17	7.82	9.29
	4H	11.17	11.79	12.26	12.87	14.35	6.52	7.14	7.61	8.22	9.70
	6H	11.57	12.14	12.67	13.22	14.71	6.82	7.39	7.92	8.47	9.96
	8H	11.68	12.22	12.78	13.32	14.80	6.90	7.45	8.01	8.54	10.02
	12H	11.73	12.24	12.84	13.33	14.84	6.94	7.45	8.04	8.54	10.05
4H	2H	8.94	9.56	10.04	10.64	12.12	5.49	6.11	6.59	7.19	8.67
	3H	10.73	11.25	11.84	12.35	13.84	6.81	7.33	7.92	8.43	9.92
	4H	11.40	11.88	12.51	12.97	14.48	7.34	7.82	8.45	8.91	10.42
	6H	11.89	12.29	13.00	13.41	14.92	7.74	8.14	8.85	9.26	10.77
	8H	12.05	12.43	13.16	13.54	15.06	7.86	8.23	8.97	9.34	10.86
	12H	12.12	12.47	13.26	13.59	15.11	7.91	8.25	9.04	9.37	10.90
8H	4H	11.36	11.74	12.47	12.85	14.37	7.60	7.98	8.72	9.09	10.61
	6H	11.89	12.21	13.03	13.36	14.87	8.09	8.40	9.23	9.56	11.07
	8H	12.09	12.37	13.24	13.50	15.04	8.27	8.54	9.41	9.68	11.21
	12H	12.21	12.45	13.36	13.58	15.15	8.37	8.61	9.52	9.74	11.31
12H	4H	11.30	11.65	12.44	12.77	14.29	7.60	7.94	8.73	9.06	10.59
	6H	11.87	12.14	13.01	13.27	14.81	8.14	8.41	9.28	9.54	11.08
	8H	12.07	12.31	13.21	13.44	15.01	8.33	8.57	9.47	9.69	11.27