

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910527

Luminaire Tested: DFN2DIP-4P4F0-050D080US850-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P910527  
REPORT IS A COMBINATION OF REPORTS P900663 AND P897523  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P4F0-050D080US850-FLLONL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14272.9 lumens  
Efficiency: N/A  
Efficacy: 115.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 123.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P910527  
CATALOG NUMBER: DFN2DIP-4P4F0-050D080US850-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P910527

CATALOG NUMBER: DFN2DIP-4P4F0-050D080US850-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	38				38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27				27
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28	23				23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20				20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13				13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12				12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1400	1400	1400
5°	1402	1381	1390
10°	1391	1363	1372
15°	1370	1341	1343
20°	1343	1310	1313
25°	1316	1273	1279
30°	1281	1239	1235
35°	1249	1198	1189
40°	1209	1157	1145
45°	1169	1117	1100
50°	1125	1074	1048
55°	1079	1024	1000
60°	1028	965	945
65°	971	904	880
70°	900	830	811
75°	800	741	748
80°	681	628	626
85°	493	432	422

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1543 cd/sqm



TEST NUMBER: P910527

CATALOG NUMBER: DFN2DIP-4P4F0-050D080US850-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.1	1.4
10°-20°	571.4	4.0
20°-30°	839.7	5.9
30°-40°	975.2	6.8
40°-50°	974.0	6.8
50°-60°	849.3	6.0
60°-70°	627.9	4.4
70°-80°	355.2	2.5
80°-90°	99.0	0.7
90°-100°	98.7	0.7
100°-110°	368.1	2.6
110°-120°	976.2	6.8
120°-130°	1619.0	11.3
130°-140°	1719.8	12.0
140°-150°	1598.3	11.2
150°-160°	1285.0	9.0
160°-170°	828.0	5.8
170°-180°	285.0	2.0
0°-30°	1614.1	11.3
0°-40°	2589.4	18.1
0°-60°	4412.7	30.9
0°-90°	5494.8	38.5
90°-120°	1442.9	10.1
90°-150°	6380.0	44.7
90°-180°	8778.0	61.5
0°-180°	14272.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2158	2158	2158	2158	2158	
5°	2158	2150	2126	2143	2139	205
15°	2054	2042	2014	2023	2012	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1001
45°	1305	1290	1259	1237	1228	1007
55°	988	975	950	925	915	883
65°	666	654	633	614	604	659
75°	348	344	334	322	326	372
85°	85	83	81	75	73	95
90°	2	26	43	54	58	13
95°	141	69	84	96	93	167
105°	659	724	132	156	165	704
115°	1246	1283	1337	334	178	1226
125°	1761	1790	1831	1846	1852	1571
135°	2180	2214	2234	2256	2251	1684
145°	2528	2526	2563	2578	2567	1581
155°	2784	2765	2791	2804	2786	1283
165°	2934	2921	2927	2942	2927	829
175°	3001	2985	2990	3005	2983	286
180°	2994	2994	2994	2994	2994	



TEST NUMBER: P910527

CATALOG NUMBER: DFN2DIP-4P4F0-050D080US850-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2157.6	2157.6	2157.6	2157.6	2157.6
2.5°	2170.1	2159.8	2136.9	2157.6	2153.7
5°	2157.6	2149.5	2126.5	2143.0	2139.2
7.5°	2143.0	2130.7	2107.9	2124.6	2120.4
10°	2120.4	2105.9	2081.0	2097.5	2091.4
12.5°	2089.1	2076.8	2052.0	2062.3	2058.1
15°	2053.9	2041.6	2014.5	2022.9	2012.5
17.5°	2010.3	1998.0	1970.9	1981.2	1970.9
20°	1962.6	1950.3	1921.2	1927.3	1919.2
22.5°	1915.0	1896.3	1869.2	1869.2	1865.0
25°	1858.9	1842.4	1807.1	1811.1	1807.1
27.5°	1796.6	1782.1	1755.2	1749.0	1738.7
30°	1734.5	1717.8	1686.8	1680.6	1672.3
32.5°	1668.0	1655.7	1622.5	1609.9	1601.6
35°	1603.7	1583.1	1549.8	1537.3	1527.0
37.5°	1531.1	1512.5	1479.2	1464.7	1454.3
40°	1456.6	1439.8	1406.5	1388.0	1379.7
42.5°	1383.9	1367.2	1334.1	1313.2	1300.9
45°	1305.1	1290.5	1259.3	1236.6	1228.2
47.5°	1228.2	1213.7	1180.5	1157.6	1145.3
50°	1147.3	1136.9	1107.9	1078.8	1068.4
52.5°	1068.4	1053.9	1027.0	1004.2	989.7
55°	987.7	975.1	950.2	925.3	915.0
57.5°	906.6	896.3	869.2	844.4	836.0
60°	825.7	817.6	788.5	765.5	759.4
62.5°	746.9	732.4	711.6	690.9	682.6
65°	666.1	653.5	632.8	614.2	603.7
67.5°	583.1	572.6	554.1	539.5	531.1
70°	506.3	497.9	479.2	464.7	456.6
72.5°	427.5	419.1	408.8	394.2	388.0
75°	348.4	344.5	333.9	321.6	325.8
77.5°	278.0	269.6	265.5	259.3	253.2
80°	207.6	205.4	201.2	195.1	190.9
82.5°	141.1	141.1	139.1	130.8	130.8
85°	84.9	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.8	20.7
90°	2.1	26.0	43.3	54.2	58.4
92.5°	54.2	45.6	52.0	56.3	58.4
95°	140.7	69.2	84.4	95.5	93.2
97.5°	253.4	75.9	110.3	117.1	119.1
100°	383.6	86.7	123.5	140.7	145.1
102.5°	526.4	522.2	127.9	151.5	158.3
105°	658.6	723.7	132.2	155.9	164.7
107.5°	812.5	866.5	136.6	160.3	169.0
110°	960.0	1005.2	379.3	162.6	171.1



TEST NUMBER: P910527

CATALOG NUMBER: DFN2DIP-4P4F0-050D080US850-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1098.6	1137.4	1100.7	166.7	173.4
115°	1245.7	1282.6	1336.8	333.7	177.8
117.5°	1373.6	1416.9	1453.9	1143.8	576.3
120°	1516.7	1549.1	1588.2	1614.1	1321.6
122.5°	1637.8	1672.6	1716.1	1728.9	1731.3
125°	1761.3	1789.6	1830.7	1845.9	1852.4
127.5°	1874.0	1904.4	1937.1	1958.6	1960.7
130°	1980.2	2014.9	2038.7	2062.6	2060.5
132.5°	2088.6	2116.9	2140.6	2160.1	2158.0
135°	2179.6	2214.3	2233.6	2255.6	2251.2
137.5°	2274.9	2300.8	2322.7	2344.3	2337.9
140°	2367.9	2385.5	2409.2	2428.7	2417.8
142.5°	2446.2	2461.3	2489.4	2506.7	2495.8
145°	2528.5	2526.2	2563.0	2578.2	2567.3
147.5°	2599.8	2593.4	2630.1	2641.0	2632.4
150°	2669.3	2654.1	2688.8	2701.6	2690.9
152.5°	2727.7	2710.4	2742.8	2756.0	2740.8
155°	2784.0	2764.7	2790.7	2803.6	2786.4
157.5°	2829.5	2812.3	2831.8	2847.0	2829.5
160°	2868.7	2855.6	2868.7	2881.5	2866.3
162.5°	2903.1	2890.3	2901.0	2916.2	2896.7
165°	2933.5	2920.7	2927.1	2942.2	2927.1
167.5°	2957.4	2944.3	2950.9	2966.1	2946.6
170°	2977.0	2963.8	2968.2	2983.4	2963.8
172.5°	2989.9	2977.0	2981.3	2996.5	2977.0
175°	3000.6	2985.4	2989.9	3004.9	2983.4
177.5°	3004.9	2989.9	2992.1	3007.3	2987.8
180°	2994.2	2994.2	2994.2	2994.2	2994.2



TEST NUMBER: P910527  
 CATALOG NUMBER: DFN2DIP-4P4F0-050D080US850-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.29	8.06	8.34	9.11	10.54	6.85	7.61	7.90	8.67	10.10
	3H	8.95	9.64	10.01	10.70	12.15	8.46	9.15	9.52	10.21	11.66
	4H	9.54	10.19	10.61	11.25	12.71	9.04	9.70	10.12	10.76	12.21
	6H	9.94	10.54	11.02	11.61	13.07	9.44	10.04	10.52	11.11	12.57
	8H	10.04	10.61	11.13	11.70	13.16	9.54	10.11	10.63	11.20	12.65
	12H	10.09	10.63	11.18	11.71	13.19	9.58	10.12	10.67	11.20	12.68
4H	2H	7.74	8.39	8.82	9.46	10.91	7.39	8.04	8.47	9.11	10.56
	3H	9.61	10.15	10.69	11.24	12.71	9.20	9.74	10.28	10.84	12.30
	4H	10.32	10.82	11.41	11.90	13.39	9.90	10.40	10.99	11.48	12.97
	6H	10.84	11.26	11.94	12.37	13.85	10.40	10.83	11.50	11.94	13.42
	8H	10.99	11.39	12.09	12.48	13.98	10.55	10.95	11.65	12.05	13.54
	12H	11.06	11.42	12.17	12.53	14.03	10.61	10.97	11.73	12.08	13.58
8H	4H	10.51	10.91	11.61	12.01	13.50	10.13	10.53	11.23	11.63	13.13
	6H	11.14	11.48	12.27	12.62	14.11	10.76	11.09	11.88	12.23	13.72
	8H	11.37	11.66	12.50	12.78	14.29	10.98	11.27	12.10	12.39	13.90
	12H	11.50	11.75	12.63	12.87	14.42	11.09	11.34	12.22	12.46	14.01
12H	4H	10.49	10.85	11.61	11.97	13.47	10.12	10.49	11.24	11.60	13.10
	6H	11.17	11.46	12.30	12.59	14.10	10.80	11.09	11.93	12.21	13.73
	8H	11.42	11.67	12.55	12.79	14.34	11.04	11.29	12.17	12.41	13.96