

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924249

Luminaire Tested: DFN2DIP-HX2F0-020D030US950-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P924249  
REPORT IS A COMBINATION OF REPORTS P900682 AND P897595  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-020D030US950-RLLONL  
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4455.2 lumens  
Efficiency: N/A  
Efficacy: 120.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 37  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P924249  
CATALOG NUMBER: DFN2DIP-HX2F0-020D030US950-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P924249

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US950-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36			36
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31			31
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32	27			27
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28	23			23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20			20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18			18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16			16
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14			14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13			13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12			12
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13	11			11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1858	1858	1858
5°	1858	1824	1837
10°	1837	1784	1774
15°	1808	1721	1678
20°	1772	1635	1562
25°	1735	1540	1450
30°	1686	1444	1309
35°	1637	1340	1186
40°	1588	1233	1044
45°	1531	1115	917
50°	1472	997	793
55°	1410	870	673
60°	1339	739	551
65°	1255	606	492
70°	1155	482	441
75°	1028	416	394
80°	847	337	332
85°	552	208	232

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1531 cd/sqm



TEST NUMBER: P924249

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US950-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.9	1.7
10°-20°	202.9	4.6
20°-30°	284.8	6.4
30°-40°	310.5	7.0
40°-50°	285.4	6.4
50°-60°	224.1	5.0
60°-70°	145.9	3.3
70°-80°	75.1	1.7
80°-90°	20.9	0.5
90°-100°	31.9	0.7
100°-110°	118.7	2.7
110°-120°	314.9	7.1
120°-130°	522.3	11.7
130°-140°	554.8	12.5
140°-150°	515.6	11.6
150°-160°	414.5	9.3
160°-170°	267.1	6.0
170°-180°	91.9	2.1
0°-30°	561.6	12.6
0°-40°	872.1	19.6
0°-60°	1381.7	31.0
0°-90°	1623.5	36.4
90°-120°	465.5	10.4
90°-150°	2058.1	46.2
90°-180°	2832.0	63.6
0°-180°	4455.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	789	789	789	789	789	
5°	789	785	776	782	780	75
15°	750	742	718	704	697	211
25°	681	658	611	582	571	313
35°	587	550	488	442	427	367
45°	480	432	357	306	289	370
55°	365	309	232	189	176	326
65°	246	188	124	100	98	244
75°	131	81	57	52	51	139
85°	31	16	14	14	14	35
90°	1	8	14	18	19	4
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	



TEST NUMBER: P924249

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US950-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	788.6	788.6	788.6	788.6	788.6
2.5°	792.1	788.6	780.7	787.9	786.5
5°	788.6	785.0	775.7	782.2	780.0
7.5°	782.2	777.9	767.9	770.7	767.1
10°	773.6	768.5	754.3	752.1	747.9
12.5°	762.9	756.4	737.2	733.0	725.0
15°	750.0	742.1	717.9	704.3	697.3
17.5°	735.1	723.6	693.7	677.9	666.6
20°	717.9	703.6	668.0	650.2	634.4
22.5°	699.4	683.0	641.6	617.3	606.6
25°	680.9	658.0	610.8	581.7	570.9
27.5°	658.7	634.4	582.3	548.7	532.3
30°	635.2	608.0	550.9	514.6	495.2
32.5°	612.3	579.5	521.0	478.1	460.3
35°	586.6	550.3	487.5	442.5	426.7
37.5°	561.6	522.3	456.0	406.8	388.9
40°	535.2	492.5	423.2	372.5	353.9
42.5°	508.1	462.5	390.4	337.5	319.8
45°	479.6	431.7	356.9	306.1	289.0
47.5°	452.5	401.8	324.7	274.0	258.3
50°	422.5	371.9	293.4	244.0	229.2
52.5°	393.1	339.6	263.3	216.3	202.7
55°	364.6	309.0	231.9	189.2	175.5
57.5°	335.4	278.3	204.2	164.2	152.7
60°	305.5	248.3	174.9	138.5	127.1
62.5°	276.2	219.1	149.9	115.6	109.9
65°	246.2	188.4	124.2	100.0	97.8
67.5°	217.7	159.8	100.0	87.8	85.7
70°	187.7	132.0	82.7	75.7	72.8
72.5°	159.1	106.3	69.2	63.5	62.1
75°	131.3	81.3	57.0	52.1	51.4
77.5°	103.5	57.8	44.9	42.1	40.6
80°	77.8	41.4	34.2	31.4	31.4
82.5°	54.2	27.9	23.6	22.1	22.1
85°	30.6	15.6	13.5	13.5	13.5
87.5°	11.4	5.7	5.7	5.0	5.0
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2



TEST NUMBER: P924249

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US950-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9



TEST NUMBER: P924249  
 CATALOG NUMBER: DFN2DIP-HX2F0-020D030US950-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.75	8.48	8.82	9.55	11.00	3.73	4.46	4.80	5.53	6.99
	3H	9.39	10.04	10.47	11.12	12.60	4.90	5.55	5.98	6.63	8.10
	4H	9.98	10.60	11.07	11.68	13.16	5.33	5.95	6.42	7.03	8.51
	6H	10.37	10.94	11.47	12.03	13.52	5.63	6.20	6.73	7.28	8.77
	8H	10.49	11.03	11.59	12.13	13.61	5.71	6.25	6.81	7.35	8.83
	12H	10.54	11.05	11.64	12.14	13.65	5.74	6.26	6.85	7.35	8.86
4H	2H	7.75	8.37	8.85	9.45	10.93	4.30	4.92	5.40	6.00	7.48
	3H	9.54	10.06	10.64	11.16	12.65	5.62	6.14	6.73	7.24	8.74
	4H	10.21	10.68	11.32	11.78	13.29	6.15	6.62	7.26	7.72	9.23
	6H	10.70	11.10	11.81	12.22	13.72	6.55	6.95	7.66	8.07	9.58
	8H	10.85	11.23	11.97	12.34	13.86	6.66	7.04	7.78	8.15	9.67
	12H	10.93	11.27	12.06	12.40	13.92	6.71	7.06	7.85	8.18	9.70
8H	4H	10.17	10.54	11.28	11.65	13.17	6.41	6.79	7.52	7.90	9.42
	6H	10.70	11.01	11.84	12.17	13.68	6.90	7.21	8.04	8.36	9.88
	8H	10.90	11.17	12.04	12.31	13.84	7.08	7.35	8.22	8.48	10.02
	12H	11.02	11.26	12.16	12.39	13.96	7.18	7.42	8.32	8.55	10.12
12H	4H	10.11	10.45	11.24	11.58	13.10	6.40	6.75	7.54	7.87	9.40
	6H	10.67	10.95	11.82	12.08	13.62	6.94	7.21	8.09	8.35	9.89
	8H	10.87	11.11	12.02	12.24	13.82	7.13	7.37	8.28	8.50	10.08