

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913230

Luminaire Tested: DFN2DIP-4P4F0-040D080US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913230
REPORT IS A COMBINATION OF REPORTS P899141 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-040D080US927-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8745.7 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 112.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913230

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913230

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36		
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36	30		
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31	25		
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21		
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22	18		
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20	16		
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	14		
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12		
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11		
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10		
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	800	800	800
5°	801	789	794
10°	795	779	784
15°	783	766	767
20°	767	749	750
25°	752	727	731
30°	732	708	706
35°	714	685	679
40°	691	661	654
45°	668	638	629
50°	643	614	599
55°	617	585	571
60°	587	551	540
65°	555	517	503
70°	514	474	464
75°	457	423	428
80°	389	359	358
85°	282	247	241

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1517 cd/sqm

TEST NUMBER: P913230

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	1.3
10°-20°	326.5	3.7
20°-30°	479.8	5.5
30°-40°	557.3	6.4
40°-50°	556.6	6.4
50°-60°	485.3	5.5
60°-70°	358.8	4.1
70°-80°	203.0	2.3
80°-90°	59.3	0.7
90°-100°	124.0	1.4
100°-110°	394.1	4.5
110°-120°	674.4	7.7
120°-130°	886.9	10.1
130°-140°	995.5	11.4
140°-150°	976.2	11.2
150°-160°	818.9	9.4
160°-170°	543.1	6.2
170°-180°	189.8	2.2
0°-30°	922.4	10.5
0°-40°	1479.7	16.9
0°-60°	2521.7	28.8
0°-90°	3142.7	35.9
90°-120°	1192.5	13.6
90°-150°	4051.1	46.3
90°-180°	5603.0	64.1
0°-180°	8745.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	2	22	59	56	57	9
95°	88	105	108	108	105	98
105°	364	369	372	375	375	384
115°	677	686	683	682	677	669
125°	984	999	995	989	987	880
135°	1273	1292	1296	1294	1289	984
145°	1546	1558	1567	1569	1563	966
155°	1767	1772	1778	1786	1781	813
165°	1923	1921	1921	1933	1924	542
175°	2001	1996	1992	2004	1994	190
180°	2004	2004	2004	2004	2004	

TEST NUMBER: P913230

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	1.8	21.8	59.3	55.6	57.4
92.5°	37.5	50.8	52.6	54.3	54.3
95°	88.2	105.1	108.1	108.1	105.1
97.5°	146.9	162.6	169.2	169.2	169.2
100°	214.5	228.4	233.2	233.2	231.4
102.5°	285.8	296.1	302.7	304.5	302.7
105°	363.8	368.6	372.2	375.3	375.3
107.5°	441.1	448.4	448.4	449.6	441.1
110°	516.0	525.7	525.7	525.7	520.9

TEST NUMBER: P913230

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	597.0	607.3	605.5	600.6	597.0
115°	676.8	686.4	683.4	681.6	676.8
117.5°	755.9	769.2	760.7	755.9	751.1
120°	835.7	849.0	835.7	835.7	830.2
122.5°	908.2	925.1	916.6	911.8	908.2
125°	984.3	999.4	994.6	989.1	987.4
127.5°	1058.7	1077.4	1070.7	1063.5	1058.7
130°	1128.1	1149.9	1146.8	1143.3	1136.6
132.5°	1206.1	1223.0	1224.2	1215.8	1210.9
135°	1273.1	1291.9	1295.5	1293.7	1288.9
137.5°	1348.1	1363.2	1366.2	1365.0	1357.7
140°	1414.0	1429.0	1437.5	1437.5	1430.8
142.5°	1481.6	1496.7	1501.6	1503.4	1496.7
145°	1545.7	1557.7	1567.4	1569.2	1562.6
147.5°	1603.1	1618.2	1625.4	1628.5	1621.8
150°	1662.3	1672.5	1679.2	1684.7	1679.2
152.5°	1714.8	1725.1	1733.6	1740.3	1733.6
155°	1767.4	1772.3	1777.7	1786.1	1780.7
157.5°	1812.7	1816.4	1819.4	1831.4	1823.0
160°	1853.2	1856.9	1858.7	1868.9	1861.7
162.5°	1890.7	1890.7	1892.5	1904.0	1895.5
165°	1922.7	1920.9	1920.9	1933.0	1924.5
167.5°	1951.7	1946.3	1946.3	1958.4	1949.9
170°	1973.5	1968.6	1966.8	1978.9	1968.6
172.5°	1988.6	1983.8	1982.0	1994.0	1983.8
175°	2000.7	1995.8	1992.2	2004.3	1994.0
177.5°	2007.3	2002.5	1998.8	2009.1	1998.8
180°	2004.3	2004.3	2004.3	2004.3	2004.3

TEST NUMBER: P913230

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.05	5.80	6.12	6.87	8.33	4.61	5.35	5.68	6.43	7.88
	3H	6.71	7.38	7.79	8.46	9.93	6.22	6.89	7.30	7.97	9.44
	4H	7.29	7.93	8.38	9.01	10.49	6.80	7.44	7.89	8.52	10.00
	6H	7.69	8.28	8.79	9.36	10.86	7.19	7.78	8.29	8.86	10.36
	8H	7.80	8.35	8.90	9.45	10.94	7.29	7.85	8.40	8.95	10.44
	12H	7.84	8.37	8.95	9.47	10.98	7.33	7.86	8.44	8.96	10.47
4H	2H	5.50	6.13	6.60	7.22	8.70	5.14	5.78	6.24	6.86	8.34
	3H	7.36	7.89	8.46	9.00	10.50	6.95	7.48	8.06	8.59	10.09
	4H	8.08	8.56	9.18	9.66	11.18	7.65	8.14	8.76	9.24	10.75
	6H	8.59	9.01	9.70	10.13	11.64	8.16	8.57	9.27	9.70	11.20
	8H	8.74	9.13	9.85	10.24	11.77	8.30	8.69	9.42	9.80	11.33
	12H	8.81	9.16	9.94	10.29	11.82	8.36	8.71	9.49	9.84	11.37
8H	4H	8.26	8.65	9.38	9.77	11.29	7.89	8.28	9.00	9.39	10.92
	6H	8.90	9.22	10.03	10.37	11.90	8.51	8.84	9.65	9.99	11.51
	8H	9.12	9.40	10.26	10.54	12.08	8.73	9.01	9.87	10.14	11.69
	12H	9.25	9.50	10.40	10.63	12.21	8.84	9.09	9.99	10.22	11.80
12H	4H	8.24	8.60	9.38	9.72	11.25	7.88	8.23	9.01	9.35	10.89
	6H	8.93	9.21	10.07	10.34	11.89	8.55	8.84	9.70	9.97	11.51
	8H	9.17	9.41	10.31	10.55	12.12	8.79	9.03	9.93	10.17	11.74

END OF REPORT