

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913314

Luminaire Tested: DFN2DIP-4P4F0-080D050US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913314
REPORT IS A COMBINATION OF REPORTS P899113 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D050US927-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9779.5 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 126
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913314

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913314

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91		80	80	80		69
1	101	97	93	89	95	91	87	84	80	77	75		70	68	66		61
2	92	84	78	73	86	79	74	69	70	66	62		62	58	56		54
3	84	74	67	61	79	70	63	58	62	57	52		55	50	47		48
4	77	66	58	51	72	62	55	49	55	49	45		49	44	40		43
5	71	59	50	44	66	55	48	42	49	43	39		44	39	35		38
6	65	53	44	38	61	50	42	37	45	38	34		40	35	31		35
7	60	48	40	34	56	45	38	32	40	34	30		36	31	27		32
8	56	43	35	30	53	41	34	29	37	31	27		33	28	24		29
9	52	40	32	27	49	38	31	26	34	28	24		30	26	22		27
10	49	37	29	24	46	35	28	23	31	26	22		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1600	1600	1600
5°	1602	1578	1589
10°	1590	1557	1568
15°	1566	1532	1535
20°	1535	1497	1501
25°	1504	1455	1462
30°	1464	1416	1412
35°	1427	1370	1359
40°	1381	1323	1308
45°	1336	1276	1257
50°	1286	1227	1197
55°	1233	1170	1143
60°	1174	1103	1080
65°	1110	1033	1006
70°	1028	948	927
75°	914	847	855
80°	778	718	715
85°	564	493	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1336 cd/sqm

TEST NUMBER: P913314

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.1	2.4
10°-20°	653.0	6.7
20°-30°	959.7	9.8
30°-40°	1114.6	11.4
40°-50°	1113.2	11.4
50°-60°	970.7	9.9
60°-70°	717.6	7.3
70°-80°	406.0	4.2
80°-90°	110.7	1.1
90°-100°	77.5	0.8
100°-110°	246.3	2.5
110°-120°	421.5	4.3
120°-130°	554.3	5.7
130°-140°	622.2	6.4
140°-150°	610.1	6.2
150°-160°	511.8	5.2
160°-170°	339.4	3.5
170°-180°	118.6	1.2
0°-30°	1844.8	18.9
0°-40°	2959.4	30.3
0°-60°	5043.4	51.6
0°-90°	6277.6	64.2
90°-120°	745.3	7.6
90°-150°	2532.0	25.9
90°-180°	3502.0	35.8
0°-180°	9779.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2466	2466	2466	2466	2466	
5°	2466	2457	2430	2449	2445	234
15°	2348	2333	2302	2312	2300	661
25°	2125	2106	2066	2070	2066	978
35°	1833	1809	1771	1757	1745	1145
45°	1492	1475	1439	1413	1404	1151
55°	1129	1114	1086	1058	1046	1009
65°	761	747	723	702	690	753
75°	398	394	382	368	372	425
85°	97	95	93	85	83	108
90°	1	14	37	35	36	9
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	

TEST NUMBER: P913314

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2465.9	2465.9	2465.9	2465.9	2465.9
2.5°	2480.2	2468.4	2442.3	2465.9	2461.4
5°	2465.9	2456.6	2430.5	2449.3	2444.8
7.5°	2449.3	2435.2	2409.1	2428.2	2423.4
10°	2423.4	2406.8	2378.4	2397.2	2390.2
12.5°	2387.7	2373.6	2345.2	2357.0	2352.2
15°	2347.5	2333.4	2302.4	2312.0	2300.2
17.5°	2297.6	2283.5	2252.6	2264.4	2252.6
20°	2243.1	2229.0	2195.8	2202.8	2193.5
22.5°	2188.7	2167.3	2136.4	2136.4	2131.6
25°	2124.6	2105.7	2065.5	2070.0	2065.5
27.5°	2053.3	2036.8	2006.0	1999.0	1987.2
30°	1982.4	1963.3	1927.9	1920.8	1911.2
32.5°	1906.5	1892.4	1854.3	1840.0	1830.5
35°	1832.9	1809.3	1771.3	1757.0	1745.2
37.5°	1749.9	1728.5	1690.6	1674.0	1662.2
40°	1664.7	1645.5	1607.6	1586.4	1576.8
42.5°	1581.7	1562.5	1524.8	1500.9	1486.8
45°	1491.6	1475.0	1439.2	1413.3	1403.8
47.5°	1403.8	1387.2	1349.2	1323.0	1308.9
50°	1311.2	1299.4	1266.1	1233.0	1221.1
52.5°	1221.1	1204.5	1173.9	1147.7	1131.1
55°	1128.8	1114.4	1086.1	1057.6	1045.8
57.5°	1036.3	1024.4	993.5	965.0	955.4
60°	943.6	934.4	901.1	875.0	867.9
62.5°	853.6	837.0	813.3	789.7	780.1
65°	761.3	746.9	723.3	701.9	690.1
67.5°	666.4	654.3	633.2	616.6	607.0
70°	578.6	569.0	547.7	531.1	521.7
72.5°	488.5	479.0	467.1	450.6	443.5
75°	398.2	393.7	381.7	367.6	372.3
77.5°	317.7	308.2	303.4	296.4	289.3
80°	237.3	234.7	230.0	222.9	218.1
82.5°	161.3	161.3	159.0	149.4	149.4
85°	97.1	94.8	92.6	85.3	83.0
87.5°	42.8	38.0	33.2	26.1	23.7
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5

TEST NUMBER: P913314

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7

TEST NUMBER: P913314

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.14	11.14	10.96	11.99	13.04	9.69	10.70	10.52	11.55	12.60
	3H	11.81	12.72	12.65	13.57	14.65	11.32	12.23	12.16	13.08	14.16
	4H	12.41	13.27	13.27	14.13	15.22	11.92	12.77	12.77	13.63	14.73
	6H	12.82	13.61	13.69	14.48	15.59	12.32	13.11	13.19	13.98	15.09
	8H	12.94	13.68	13.81	14.57	15.68	12.43	13.18	13.31	14.07	15.18
	12H	12.99	13.71	13.87	14.59	15.72	12.48	13.19	13.36	14.08	15.21
4H	2H	10.62	11.47	11.48	12.33	13.43	10.26	11.12	11.12	11.98	13.07
	3H	12.50	13.21	13.37	14.11	15.22	12.09	12.81	12.96	13.70	14.81
	4H	13.23	13.88	14.11	14.77	15.90	12.80	13.45	13.69	14.35	15.48
	6H	13.76	14.32	14.65	15.23	16.37	13.32	13.88	14.22	14.80	15.94
	8H	13.91	14.44	14.81	15.35	16.50	13.47	14.00	14.37	14.91	16.06
	12H	13.99	14.47	14.91	15.40	16.55	13.54	14.02	14.47	14.95	16.10
8H	4H	13.44	13.96	14.34	14.87	16.02	13.06	13.58	13.96	14.50	15.64
	6H	14.08	14.51	15.01	15.47	16.62	13.70	14.13	14.62	15.08	16.23
	8H	14.31	14.69	15.24	15.64	16.80	13.91	14.30	14.85	15.24	16.41
	12H	14.45	14.79	15.39	15.72	16.94	14.04	14.38	14.98	15.31	16.53
12H	4H	13.43	13.90	14.35	14.83	15.99	13.06	13.53	13.98	14.46	15.62
	6H	14.11	14.50	15.05	15.44	16.61	13.74	14.13	14.68	15.07	16.24
	8H	14.36	14.70	15.31	15.64	16.86	13.98	14.32	14.93	15.26	16.48