

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924308

Luminaire Tested: DFN2DIP-HX2F0-050D030US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924308
REPORT IS A COMBINATION OF REPORTS P899168 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-050D030US950-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6587.4 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 69.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924308

CATALOG NUMBER: DFN2DIP-HX2F0-050D030US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924308

CATALOG NUMBER: DFN2DIP-HX2F0-050D030US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	58
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	53	51	49
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	41	45	40	37	39	36	33
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4645	4645	4645
5°	4645	4560	4592
10°	4592	4460	4434
15°	4521	4302	4195
20°	4430	4088	3905
25°	4337	3851	3625
30°	4214	3609	3273
35°	4094	3349	2964
40°	3971	3082	2612
45°	3828	2788	2292
50°	3681	2491	1981
55°	3525	2175	1682
60°	3346	1847	1377
65°	3138	1515	1230
70°	2888	1206	1101
75°	2571	1041	985
80°	2115	844	829
85°	1384	521	582

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3828 cd/sqm

TEST NUMBER: P924308

CATALOG NUMBER: DFN2DIP-HX2F0-050D030US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.8
10°-20°	507.2	7.7
20°-30°	712.1	10.8
30°-40°	776.3	11.8
40°-50°	713.5	10.8
50°-60°	560.3	8.5
60°-70°	364.7	5.5
70°-80°	187.7	2.8
80°-90°	50.5	0.8
90°-100°	56.0	0.9
100°-110°	178.0	2.7
110°-120°	304.6	4.6
120°-130°	400.5	6.1
130°-140°	449.6	6.8
140°-150°	440.9	6.7
150°-160°	369.8	5.6
160°-170°	245.3	3.7
170°-180°	85.7	1.3
0°-30°	1404.1	21.3
0°-40°	2180.4	33.1
0°-60°	3454.1	52.4
0°-90°	4057.1	61.6
90°-120°	538.5	8.2
90°-150°	1829.5	27.8
90°-180°	2530.0	38.4
0°-180°	6587.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1971	1963	1939	1955	1950	187
15°	1875	1855	1795	1761	1743	528
25°	1702	1645	1527	1454	1427	783
35°	1467	1376	1219	1106	1067	918
45°	1199	1079	892	765	722	926
55°	912	772	580	473	439	815
65°	616	471	310	250	244	610
75°	328	203	143	130	128	347
85°	77	39	34	34	34	88
90°	1	10	27	25	26	6
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P924308

CATALOG NUMBER: DFN2DIP-HX2F0-050D030US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1971.4	1971.4	1971.4	1971.4	1971.4
2.5°	1980.3	1971.4	1951.8	1969.7	1966.1
5°	1971.4	1962.6	1939.3	1955.3	1950.1
7.5°	1955.3	1944.7	1919.7	1926.8	1917.8
10°	1933.9	1921.5	1885.9	1880.4	1869.7
12.5°	1907.2	1891.2	1842.9	1832.3	1812.6
15°	1875.1	1855.4	1794.9	1761.0	1743.1
17.5°	1837.6	1809.1	1734.1	1694.9	1666.3
20°	1794.9	1759.1	1669.9	1625.4	1586.0
22.5°	1748.5	1707.4	1603.9	1543.3	1516.6
25°	1702.0	1644.9	1527.2	1454.1	1427.2
27.5°	1646.8	1586.0	1455.8	1371.9	1330.9
30°	1587.9	1520.0	1377.3	1286.4	1238.1
32.5°	1530.8	1448.6	1302.5	1195.4	1150.7
35°	1466.6	1375.6	1218.6	1106.2	1066.9
37.5°	1404.1	1305.9	1140.1	1016.9	972.4
40°	1338.1	1231.1	1057.9	931.3	884.9
42.5°	1270.3	1156.2	975.9	843.8	799.4
45°	1199.0	1079.4	892.1	765.3	722.5
47.5°	1131.2	1004.6	811.9	685.1	645.9
50°	1056.3	929.6	733.3	610.1	572.8
52.5°	983.0	849.2	658.4	540.6	506.8
55°	911.6	772.5	579.7	472.8	438.9
57.5°	838.6	695.8	510.3	410.4	381.8
60°	763.6	620.9	437.0	346.2	317.6
62.5°	690.5	547.8	374.6	289.1	274.8
65°	615.5	471.0	310.4	249.9	244.4
67.5°	544.2	399.6	249.9	219.4	214.1
70°	469.3	330.1	206.9	189.1	181.9
72.5°	397.9	265.8	173.1	158.8	155.2
75°	328.3	203.3	142.7	130.2	128.5
77.5°	258.7	144.4	112.5	105.2	101.6
80°	194.4	103.5	85.6	78.5	78.5
82.5°	135.6	69.6	58.9	55.2	55.2
85°	76.7	39.2	33.9	33.9	33.9
87.5°	28.6	14.2	14.2	12.5	12.5
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P924308

CATALOG NUMBER: DFN2DIP-HX2F0-050D030US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P924308

CATALOG NUMBER: DFN2DIP-HX2F0-050D030US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.36	14.30	14.22	15.17	16.27	9.35	10.28	10.20	11.16	12.25
	3H	15.02	15.86	15.89	16.74	17.87	10.53	11.36	11.40	12.25	13.37
	4H	15.62	16.41	16.51	17.30	18.43	10.97	11.76	11.86	12.65	13.78
	6H	16.03	16.75	16.92	17.65	18.80	11.28	12.01	12.18	12.90	14.05
	8H	16.14	16.84	17.05	17.75	18.90	11.37	12.06	12.27	12.97	14.12
	12H	16.20	16.86	17.11	17.77	18.94	11.40	12.06	12.32	12.97	14.14
4H	2H	13.39	14.18	14.28	15.07	16.20	9.94	10.73	10.83	11.62	12.75
	3H	15.20	15.86	16.10	16.78	17.93	11.28	11.94	12.18	12.86	14.01
	4H	15.88	16.47	16.79	17.39	18.57	11.82	12.41	12.73	13.33	14.51
	6H	16.37	16.89	17.30	17.83	19.01	12.22	12.74	13.15	13.68	14.86
	8H	16.54	17.02	17.47	17.95	19.14	12.34	12.82	13.27	13.76	14.95
	12H	16.62	17.06	17.57	18.01	19.20	12.40	12.84	13.35	13.79	14.99
8H	4H	15.85	16.33	16.78	17.26	18.45	12.09	12.57	13.02	13.51	14.70
	6H	16.39	16.79	17.35	17.77	18.95	12.59	12.98	13.54	13.96	15.15
	8H	16.59	16.94	17.56	17.91	19.12	12.77	13.12	13.73	14.08	15.29
	12H	16.72	17.03	17.69	17.99	19.24	12.88	13.18	13.84	14.14	15.40
12H	4H	15.80	16.24	16.75	17.19	18.39	12.10	12.53	13.04	13.48	14.68
	6H	16.36	16.72	17.33	17.68	18.89	12.63	12.98	13.60	13.95	15.16
	8H	16.57	16.88	17.54	17.84	19.10	12.83	13.14	13.80	14.10	15.36