

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924312

Luminaire Tested: DFN2DIP-HX2F0-050D040US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924312
REPORT IS A COMBINATION OF REPORTS P899178 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-050D040US950-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7431.7 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924312
CATALOG NUMBER: DFN2DIP-HX2F0-050D040US950-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P924312
 CATALOG NUMBER: DFN2DIP-HX2F0-050D040US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55		
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	47		
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45	40		
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35		
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	30		
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30	27		
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24		
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21		
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	19		
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19	17		
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4645	4645	4645
5°	4645	4560	4592
10°	4592	4460	4434
15°	4521	4302	4195
20°	4430	4088	3905
25°	4337	3851	3625
30°	4214	3609	3273
35°	4094	3349	2964
40°	3971	3082	2612
45°	3828	2788	2292
50°	3681	2491	1981
55°	3525	2175	1682
60°	3346	1847	1377
65°	3138	1515	1230
70°	2888	1206	1101
75°	2571	1041	985
80°	2115	844	829
85°	1384	521	582

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3828 cd/sqm



TEST NUMBER: P924312

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.5
10°-20°	507.2	6.8
20°-30°	712.1	9.6
30°-40°	776.3	10.4
40°-50°	713.5	9.6
50°-60°	560.3	7.5
60°-70°	364.7	4.9
70°-80°	187.7	2.5
80°-90°	51.4	0.7
90°-100°	74.7	1.0
100°-110°	237.3	3.2
110°-120°	406.1	5.5
120°-130°	534.0	7.2
130°-140°	599.4	8.1
140°-150°	587.8	7.9
150°-160°	493.1	6.6
160°-170°	327.0	4.4
170°-180°	114.3	1.5
0°-30°	1404.1	18.9
0°-40°	2180.4	29.3
0°-60°	3454.1	46.5
0°-90°	4058.0	54.6
90°-120°	718.0	9.7
90°-150°	2439.3	32.8
90°-180°	3374.0	45.4
0°-180°	7431.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1971	1963	1939	1955	1950	187
15°	1875	1855	1795	1761	1743	528
25°	1702	1645	1527	1454	1427	783
35°	1467	1376	1219	1106	1067	918
45°	1199	1079	892	765	722	926
55°	912	772	580	473	439	815
65°	616	471	310	250	244	610
75°	328	203	143	130	128	347
85°	77	39	34	34	34	88
90°	1	13	36	34	34	7
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	



TEST NUMBER: P924312

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1971.4	1971.4	1971.4	1971.4	1971.4
2.5°	1980.3	1971.4	1951.8	1969.7	1966.1
5°	1971.4	1962.6	1939.3	1955.3	1950.1
7.5°	1955.3	1944.7	1919.7	1926.8	1917.8
10°	1933.9	1921.5	1885.9	1880.4	1869.7
12.5°	1907.2	1891.2	1842.9	1832.3	1812.6
15°	1875.1	1855.4	1794.9	1761.0	1743.1
17.5°	1837.6	1809.1	1734.1	1694.9	1666.3
20°	1794.9	1759.1	1669.9	1625.4	1586.0
22.5°	1748.5	1707.4	1603.9	1543.3	1516.6
25°	1702.0	1644.9	1527.2	1454.1	1427.2
27.5°	1646.8	1586.0	1455.8	1371.9	1330.9
30°	1587.9	1520.0	1377.3	1286.4	1238.1
32.5°	1530.8	1448.6	1302.5	1195.4	1150.7
35°	1466.6	1375.6	1218.6	1106.2	1066.9
37.5°	1404.1	1305.9	1140.1	1016.9	972.4
40°	1338.1	1231.1	1057.9	931.3	884.9
42.5°	1270.3	1156.2	975.9	843.8	799.4
45°	1199.0	1079.4	892.1	765.3	722.5
47.5°	1131.2	1004.6	811.9	685.1	645.9
50°	1056.3	929.6	733.3	610.1	572.8
52.5°	983.0	849.2	658.4	540.6	506.8
55°	911.6	772.5	579.7	472.8	438.9
57.5°	838.6	695.8	510.3	410.4	381.8
60°	763.6	620.9	437.0	346.2	317.6
62.5°	690.5	547.8	374.6	289.1	274.8
65°	615.5	471.0	310.4	249.9	244.4
67.5°	544.2	399.6	249.9	219.4	214.1
70°	469.3	330.1	206.9	189.1	181.9
72.5°	397.9	265.8	173.1	158.8	155.2
75°	328.3	203.3	142.7	130.2	128.5
77.5°	258.7	144.4	112.5	105.2	101.6
80°	194.4	103.5	85.6	78.5	78.5
82.5°	135.6	69.6	58.9	55.2	55.2
85°	76.7	39.2	33.9	33.9	33.9
87.5°	28.6	14.2	14.2	12.5	12.5
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7



TEST NUMBER: P924312

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US950-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8



TEST NUMBER: P924312
 CATALOG NUMBER: DFN2DIP-HX2F0-050D040US950-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.76	13.63	13.69	14.57	15.78	8.75	9.62	9.67	10.55	11.76
	3H	14.42	15.20	15.36	16.14	17.37	9.92	10.70	10.86	11.65	12.88
	4H	15.01	15.75	15.96	16.70	17.94	10.36	11.10	11.31	12.05	13.29
	6H	15.42	16.09	16.38	17.05	18.30	10.67	11.35	11.63	12.30	13.56
	8H	15.53	16.18	16.50	17.15	18.40	10.75	11.40	11.72	12.37	13.62
	12H	15.59	16.20	16.56	17.16	18.44	10.79	11.40	11.76	12.37	13.64
4H	2H	12.78	13.52	13.74	14.47	15.71	9.33	10.07	10.29	11.02	12.26
	3H	14.59	15.20	15.55	16.18	17.43	10.67	11.28	11.63	12.26	13.51
	4H	15.26	15.82	16.24	16.79	18.07	11.20	11.76	12.18	12.73	14.01
	6H	15.76	16.23	16.74	17.23	18.51	11.60	12.08	12.59	13.08	14.36
	8H	15.92	16.36	16.91	17.36	18.65	11.72	12.17	12.71	13.16	14.45
	12H	16.00	16.40	17.01	17.41	18.71	11.78	12.18	12.79	13.19	14.49
8H	4H	15.23	15.68	16.22	16.67	17.96	11.47	11.92	12.46	12.91	14.20
	6H	15.77	16.14	16.78	17.17	18.46	11.97	12.34	12.98	13.37	14.66
	8H	15.97	16.29	16.99	17.32	18.62	12.14	12.47	13.16	13.49	14.80
	12H	16.09	16.38	17.12	17.39	18.75	12.25	12.54	13.27	13.55	14.90
12H	4H	15.18	15.58	16.19	16.59	17.89	11.47	11.88	12.48	12.88	14.18
	6H	15.74	16.07	16.76	17.09	18.40	12.01	12.33	13.03	13.36	14.66
	8H	15.95	16.23	16.97	17.25	18.60	12.21	12.49	13.23	13.51	14.86