

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915956

Luminaire Tested: DFN2DIP-4P4F0-040D070US930-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915956
REPORT IS A COMBINATION OF REPORTS P899130 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-040D070US930-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect
Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7822.8 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915956

CATALOG NUMBER: DFN2DIP-4P4F0-040D070US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P915956

CATALOG NUMBER: DFN2DIP-4P4F0-040D070US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36		
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	31		
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26		
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27	23		
4	73	62	55	49	65	57	50	45	46	42	38	37	33	31	27	25	24	20		
5	67	56	48	42	60	51	44	39	42	37	33	33	29	27	25	23	21	17		
6	61	50	42	37	55	46	39	34	37	32	29	30	26	24	23	20	18	15		
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14		
8	53	41	33	28	48	38	31	26	31	26	23	25	21	19	19	17	15	12		
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11		
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	874	874	874
5°	876	861	866
10°	867	844	839
15°	855	817	795
20°	840	778	742
25°	824	735	691
30°	802	691	625
35°	781	644	568
40°	759	595	502
45°	734	541	442
50°	708	486	384
55°	681	427	328
60°	650	366	270
65°	614	303	244
70°	570	245	221
75°	515	217	202
80°	436	183	176
85°	305	124	135

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1366 cd/sqm

TEST NUMBER: P915956

CATALOG NUMBER: DFN2DIP-4P4F0-040D070US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.6
10°-20°	346.8	4.4
20°-30°	486.9	6.2
30°-40°	530.7	6.8
40°-50°	487.8	6.2
50°-60°	383.1	4.9
60°-70°	249.3	3.2
70°-80°	128.4	1.6
80°-90°	37.9	0.5
90°-100°	111.7	1.4
100°-110°	354.9	4.5
110°-120°	607.3	7.8
120°-130°	798.7	10.2
130°-140°	896.5	11.5
140°-150°	879.1	11.2
150°-160°	737.5	9.4
160°-170°	489.1	6.3
170°-180°	170.9	2.2
0°-30°	960.0	12.3
0°-40°	1490.7	19.1
0°-60°	2361.5	30.2
0°-90°	2777.1	35.5
90°-120°	1073.9	13.7
90°-150°	3648.2	46.6
90°-180°	5046.0	64.5
0°-180°	7822.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	2	20	53	50	52	8
95°	79	95	97	97	95	88
105°	328	332	335	338	338	346
115°	609	618	616	614	609	603
125°	886	900	896	891	889	792
135°	1147	1163	1167	1165	1161	886
145°	1392	1403	1412	1413	1407	870
155°	1592	1596	1601	1608	1604	733
165°	1731	1730	1730	1741	1733	488
175°	1802	1797	1794	1805	1796	171
180°	1805	1805	1805	1805	1805	

TEST NUMBER: P915956

CATALOG NUMBER: DFN2DIP-4P4F0-040D070US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	1.6	19.6	53.3	50.1	51.7
92.5°	33.8	45.7	47.4	49.0	49.0
95°	79.4	94.7	97.4	97.4	94.7
97.5°	132.2	146.3	152.4	152.4	152.4
100°	193.1	205.7	210.0	210.0	208.4
102.5°	257.4	266.6	272.6	274.3	272.6
105°	327.6	331.9	335.2	337.9	337.9
107.5°	397.2	403.7	403.7	404.9	397.2
110°	464.7	473.4	473.4	473.4	469.0

TEST NUMBER: P915956

CATALOG NUMBER: DFN2DIP-4P4F0-040D070US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	537.6	546.9	545.3	540.9	537.6
115°	609.4	618.2	615.5	613.8	609.4
117.5°	680.7	692.7	685.1	680.7	676.4
120°	752.5	764.5	752.5	752.5	747.6
122.5°	817.8	833.1	825.5	821.1	817.8
125°	886.4	900.0	895.7	890.8	889.2
127.5°	953.3	970.2	964.3	957.7	953.3
130°	1015.9	1035.5	1032.8	1029.6	1023.5
132.5°	1086.1	1101.4	1102.4	1094.9	1090.5
135°	1146.6	1163.3	1166.7	1165.0	1160.7
137.5°	1214.0	1227.6	1230.3	1229.2	1222.7
140°	1273.3	1286.9	1294.5	1294.5	1288.6
142.5°	1334.2	1347.9	1352.2	1353.8	1347.9
145°	1392.0	1402.8	1411.5	1413.2	1407.2
147.5°	1443.6	1457.3	1463.8	1466.5	1460.5
150°	1497.0	1506.2	1512.2	1517.1	1512.2
152.5°	1544.3	1553.6	1561.1	1567.2	1561.1
155°	1591.6	1595.9	1600.9	1608.5	1603.6
157.5°	1632.5	1635.7	1638.4	1649.3	1641.7
160°	1668.9	1672.2	1673.8	1683.0	1676.5
162.5°	1702.7	1702.7	1704.3	1714.6	1707.0
165°	1731.4	1729.8	1729.8	1740.7	1733.1
167.5°	1757.6	1752.7	1752.7	1763.6	1756.0
170°	1777.2	1772.9	1771.2	1782.1	1772.9
172.5°	1790.8	1786.4	1784.8	1795.7	1786.4
175°	1801.6	1797.3	1794.1	1804.9	1795.7
177.5°	1807.7	1803.3	1800.0	1809.3	1800.0
180°	1804.9	1804.9	1804.9	1804.9	1804.9

TEST NUMBER: P915956

CATALOG NUMBER: DFN2DIP-4P4F0-040D070US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.17	5.89	6.25	6.97	8.44	1.13	1.85	2.21	2.93	4.40
	3H	6.85	7.49	7.93	8.58	10.06	2.31	2.96	3.40	4.04	5.53
	4H	7.45	8.07	8.55	9.15	10.64	2.76	3.37	3.86	4.46	5.95
	6H	7.87	8.44	8.98	9.53	11.03	3.08	3.64	4.18	4.73	6.23
	8H	8.00	8.54	9.11	9.64	11.14	3.16	3.70	4.27	4.80	6.30
	12H	8.06	8.57	9.18	9.67	11.19	3.20	3.71	4.32	4.81	6.33
4H	2H	5.18	5.79	6.28	6.87	8.36	1.72	2.33	2.82	3.41	4.90
	3H	7.00	7.51	8.11	8.62	10.13	3.06	3.57	4.17	4.68	6.18
	4H	7.69	8.16	8.81	9.26	10.79	3.60	4.07	4.72	5.17	6.70
	6H	8.21	8.61	9.33	9.73	11.25	4.02	4.42	5.14	5.55	7.06
	8H	8.39	8.76	9.51	9.88	11.41	4.15	4.52	5.27	5.64	7.17
	12H	8.48	8.82	9.62	9.95	11.48	4.21	4.55	5.35	5.68	7.21
8H	4H	7.65	8.03	8.78	9.15	10.68	3.88	4.25	5.00	5.37	6.90
	6H	8.22	8.53	9.37	9.69	11.22	4.40	4.71	5.54	5.86	7.39
	8H	8.44	8.71	9.59	9.85	11.40	4.59	4.86	5.74	6.00	7.55
	12H	8.58	8.82	9.73	9.95	11.54	4.70	4.94	5.86	6.08	7.66
12H	4H	7.60	7.94	8.74	9.07	10.61	3.88	4.22	5.02	5.35	6.89
	6H	8.20	8.47	9.35	9.61	11.16	4.45	4.72	5.60	5.86	7.41
	8H	8.42	8.66	9.57	9.79	11.38	4.65	4.89	5.81	6.03	7.61

END OF REPORT