

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902523

Luminaire Tested: DFN2DIP-HX3F0-030D040US830-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P902523  
REPORT IS A COMBINATION OF REPORTS P900735 AND P897645  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-030D040US830-FLONL  
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6531.8 lumens  
Efficiency: N/A  
Efficacy: 122.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 53.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.983  
Total Harmonic Distortion (THDi): 0.073  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P902523  
CATALOG NUMBER: DFN2DIP-HX3F0-030D040US830-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P902523

CATALOG NUMBER: DFN2DIP-HX3F0-030D040US830-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43				43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36				36
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35	30				30
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30	26				26
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	31	28	26	22				22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19				19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17				17
7	57	45	37	32	52	41	34	29	35	29	25	29	25	22	23	20	18	15				15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11				11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1274	1274	1274
5°	1276	1256	1264
10°	1265	1238	1247
15°	1246	1217	1219
20°	1220	1188	1191
25°	1195	1153	1159
30°	1163	1120	1118
35°	1132	1082	1074
40°	1095	1044	1033
45°	1058	1005	991
50°	1017	965	942
55°	975	918	897
60°	926	862	846
65°	874	804	785
70°	807	734	719
75°	714	649	657
80°	602	541	541
85°	428	358	351

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1058 cd/sqm



TEST NUMBER: P902523

CATALOG NUMBER: DFN2DIP-HX3F0-030D040US830-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.6	1.6
10°-20°	291.4	4.5
20°-30°	428.2	6.6
30°-40°	497.3	7.6
40°-50°	496.7	7.6
50°-60°	433.1	6.6
60°-70°	320.2	4.9
70°-80°	181.1	2.8
80°-90°	50.0	0.8
90°-100°	41.9	0.6
100°-110°	156.4	2.4
110°-120°	414.8	6.4
120°-130°	688.0	10.5
130°-140°	730.8	11.2
140°-150°	679.2	10.4
150°-160°	546.1	8.4
160°-170°	351.9	5.4
170°-180°	121.1	1.9
0°-30°	823.1	12.6
0°-40°	1320.4	20.2
0°-60°	2250.3	34.5
0°-90°	2801.6	42.9
90°-120°	613.2	9.4
90°-150°	2711.2	41.5
90°-180°	3730.0	57.1
0°-180°	6531.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1100	1096	1084	1093	1091	104
15°	1047	1041	1027	1032	1026	295
25°	948	940	922	924	922	436
35°	818	807	790	784	779	511
45°	666	658	642	631	626	514
55°	504	497	485	472	467	450
65°	340	333	323	313	308	336
75°	178	176	170	164	166	190
85°	43	42	41	38	37	48
90°	1	11	18	23	25	6
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	668
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	



TEST NUMBER: P902523

CATALOG NUMBER: DFN2DIP-HX3F0-030D040US830-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1100.2	1100.2	1100.2	1100.2	1100.2
2.5°	1106.6	1101.4	1089.7	1100.2	1098.3
5°	1100.2	1096.1	1084.4	1092.9	1090.8
7.5°	1092.9	1086.6	1074.9	1083.5	1081.3
10°	1081.3	1073.8	1061.2	1069.6	1066.5
12.5°	1065.4	1059.0	1046.4	1051.6	1049.5
15°	1047.4	1041.1	1027.3	1031.5	1026.2
17.5°	1025.1	1018.9	1005.0	1010.3	1005.0
20°	1000.8	994.5	979.7	982.8	978.6
22.5°	976.6	967.0	953.2	953.2	951.0
25°	947.9	939.5	921.5	923.6	921.5
27.5°	916.2	908.7	895.0	891.9	886.6
30°	884.5	876.0	860.2	857.0	852.7
32.5°	850.6	844.3	827.4	821.0	816.7
35°	817.8	807.3	790.3	783.9	778.6
37.5°	780.8	771.3	754.3	746.9	741.6
40°	742.7	734.2	717.3	707.8	703.6
42.5°	705.7	697.2	680.3	669.7	663.4
45°	665.5	658.1	642.2	630.6	626.3
47.5°	626.3	619.0	602.0	590.3	584.0
50°	585.0	579.8	565.0	550.2	544.9
52.5°	544.9	537.4	523.8	512.1	504.6
55°	503.7	497.3	484.6	471.9	466.7
57.5°	462.3	457.0	443.3	430.6	426.3
60°	421.0	416.9	402.1	390.4	387.3
62.5°	380.9	373.4	362.9	352.3	348.1
65°	339.7	333.3	322.7	313.2	307.9
67.5°	297.4	292.0	282.5	275.1	270.9
70°	258.2	253.9	244.4	237.0	232.8
72.5°	218.0	213.7	208.4	201.0	197.9
75°	177.7	175.7	170.3	164.0	166.2
77.5°	141.8	137.5	135.3	132.2	129.1
80°	105.8	104.7	102.5	99.4	97.4
82.5°	71.9	71.9	71.0	66.6	66.6
85°	43.4	42.3	41.3	38.1	37.0
87.5°	19.0	17.0	14.8	11.7	10.6
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.6	56.2	66.3	69.9
107.5°	345.3	368.3	58.1	68.1	71.8
110°	407.9	427.2	161.2	69.1	72.7



TEST NUMBER: P902523

CATALOG NUMBER: DFN2DIP-HX3F0-030D040US830-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.1	141.8	75.6
117.5°	583.7	602.1	617.8	486.1	244.9
120°	644.5	658.3	674.9	686.0	561.7
122.5°	696.0	710.8	729.2	734.7	735.7
125°	748.5	760.5	778.0	784.5	787.2
127.5°	796.4	809.3	823.1	832.4	833.2
130°	841.5	856.3	866.3	876.5	875.6
132.5°	887.5	899.6	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.5	956.7
137.5°	966.7	977.7	987.0	996.2	993.4
140°	1006.3	1013.7	1023.8	1032.1	1027.5
142.5°	1039.5	1045.9	1057.9	1065.2	1060.6
145°	1074.5	1073.6	1089.1	1095.6	1091.0
147.5°	1104.8	1102.0	1117.7	1122.3	1118.7
150°	1134.3	1127.8	1142.6	1148.1	1143.5
152.5°	1159.1	1151.8	1165.5	1171.1	1164.7
155°	1183.1	1174.9	1185.9	1191.4	1184.0
157.5°	1202.4	1195.0	1203.4	1209.8	1202.4
160°	1219.0	1213.4	1219.0	1224.5	1218.0
162.5°	1233.7	1228.2	1232.8	1239.3	1231.0
165°	1246.6	1241.1	1243.9	1250.3	1243.9
167.5°	1256.8	1251.1	1254.1	1260.5	1252.2
170°	1265.1	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.1	1267.0	1273.4	1265.1
175°	1275.1	1268.7	1270.5	1277.0	1267.8
177.5°	1277.0	1270.5	1271.5	1278.0	1269.7
180°	1272.4	1272.4	1272.4	1272.4	1272.4



TEST NUMBER: P902523  
 CATALOG NUMBER: DFN2DIP-HX3F0-030D040US830-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.38	8.18	8.39	9.20	10.57	6.95	7.75	7.96	8.77	10.14
	3H	9.02	9.74	10.05	10.78	12.17	8.56	9.27	9.58	10.31	11.70
	4H	9.60	10.28	10.64	11.32	12.72	9.14	9.82	10.17	10.85	12.25
	6H	9.99	10.62	11.04	11.66	13.07	9.53	10.15	10.57	11.19	12.60
	8H	10.09	10.69	11.15	11.75	13.15	9.63	10.22	10.68	11.28	12.68
	12H	10.14	10.70	11.20	11.76	13.18	9.66	10.23	10.72	11.28	12.71
4H	2H	7.83	8.51	8.87	9.54	10.94	7.49	8.17	8.53	9.20	10.60
	3H	9.68	10.25	10.73	11.31	12.72	9.29	9.86	10.34	10.92	12.33
	4H	10.39	10.91	11.44	11.96	13.39	9.98	10.50	11.04	11.56	12.99
	6H	10.89	11.34	11.96	12.42	13.84	10.48	10.93	11.55	12.01	13.44
	8H	11.03	11.45	12.10	12.52	13.96	10.63	11.04	11.70	12.12	13.56
	12H	11.10	11.48	12.19	12.56	14.01	10.68	11.06	11.77	12.15	13.59
8H	4H	10.57	10.99	11.64	12.06	13.50	10.22	10.63	11.29	11.71	13.15
	6H	11.19	11.54	12.29	12.65	14.09	10.83	11.18	11.93	12.29	13.73
	8H	11.41	11.71	12.51	12.81	14.27	11.04	11.35	12.14	12.44	13.90
	12H	11.53	11.80	12.63	12.89	14.39	11.15	11.42	12.25	12.51	14.01
12H	4H	10.56	10.93	11.64	12.02	13.47	10.21	10.58	11.29	11.67	13.12
	6H	11.22	11.52	12.32	12.62	14.08	10.87	11.18	11.97	12.27	13.73
	8H	11.45	11.72	12.56	12.81	14.31	11.10	11.37	12.20	12.46	13.96