

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915989

Luminaire Tested: DFN2DIP-4P4F0-060D030US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915989
REPORT IS A COMBINATION OF REPORTS P900606 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-060D030US930-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6579.4 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915989
CATALOG NUMBER: DFN2DIP-4P4F0-060D030US930-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P915989

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	61	60	59	54
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51	55	52	51	47
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44	49	46	44	40
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38	44	41	38	35
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34	40	37	34	31
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30	37	33	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27	34	30	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	31	27	24	22
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22	29	25	22	20
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1312	1312	1312
5°	1314	1291	1300
10°	1301	1266	1258
15°	1283	1225	1193
20°	1259	1168	1113
25°	1235	1103	1036
30°	1203	1037	938
35°	1171	966	852
40°	1139	893	753
45°	1101	811	663
50°	1062	729	576
55°	1022	641	492
60°	975	549	405
65°	921	455	365
70°	855	367	331
75°	773	325	303
80°	654	274	264
85°	457	185	202

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1101 cd/sqm



TEST NUMBER: P915989

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	2.9
10°-20°	520.2	7.9
20°-30°	730.3	11.1
30°-40°	796.1	12.1
40°-50°	731.7	11.1
50°-60°	574.6	8.7
60°-70°	374.0	5.7
70°-80°	192.5	2.9
80°-90°	50.6	0.8
90°-100°	27.2	0.4
100°-110°	101.5	1.5
110°-120°	269.1	4.1
120°-130°	446.3	6.8
130°-140°	474.1	7.2
140°-150°	440.6	6.7
150°-160°	354.3	5.4
160°-170°	228.3	3.5
170°-180°	78.6	1.2
0°-30°	1439.9	21.9
0°-40°	2236.0	34.0
0°-60°	3542.3	53.8
0°-90°	4159.4	63.2
90°-120°	397.8	6.0
90°-150°	1758.9	26.7
90°-180°	2420.0	36.8
0°-180°	6579.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	1	7	12	15	16	6
95°	39	19	23	26	26	46
105°	182	200	36	43	45	194
115°	343	354	368	92	49	338
125°	486	493	505	509	511	433
135°	601	610	616	622	621	464
145°	697	696	707	711	708	436
155°	768	762	769	773	768	354
165°	809	805	807	811	807	228
175°	827	823	824	828	822	79
180°	826	826	826	826	826	



TEST NUMBER: P915989

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	0.6	7.2	11.9	15.0	16.1
92.5°	15.0	12.6	14.3	15.6	16.1
95°	38.8	19.1	23.2	26.3	25.7
97.5°	69.9	21.0	30.4	32.3	32.9
100°	105.7	23.9	34.1	38.8	40.0
102.5°	145.1	144.0	35.2	41.7	43.6
105°	181.6	199.5	36.4	43.0	45.4
107.5°	224.0	238.9	37.7	44.2	46.6
110°	264.6	277.1	104.5	44.8	47.2



TEST NUMBER: P915989

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	302.9	313.6	303.5	46.0	47.8
115°	343.4	353.6	368.5	92.0	49.0
117.5°	378.7	390.6	400.8	315.4	158.9
120°	418.1	427.1	437.8	445.0	364.4
122.5°	451.5	461.1	473.1	476.6	477.3
125°	485.6	493.3	504.8	508.9	510.7
127.5°	516.7	525.0	534.0	540.0	540.5
130°	545.9	555.5	562.1	568.6	568.1
132.5°	575.8	583.6	590.1	595.5	594.9
135°	600.9	610.5	615.8	621.8	620.6
137.5°	627.1	634.3	640.3	646.3	644.5
140°	652.8	657.6	664.1	669.5	666.6
142.5°	674.4	678.6	686.3	691.0	688.1
145°	697.1	696.4	706.6	710.8	707.8
147.5°	716.7	714.9	725.1	728.1	725.7
150°	735.9	731.7	741.3	744.8	741.8
152.5°	751.9	747.2	756.2	759.8	755.6
155°	767.5	762.2	769.3	772.9	768.2
157.5°	780.1	775.3	780.7	784.9	780.1
160°	790.8	787.3	790.8	794.4	790.2
162.5°	800.4	796.8	799.8	804.0	798.6
165°	808.7	805.2	807.0	811.1	807.0
167.5°	815.3	811.7	813.5	817.7	812.4
170°	820.7	817.1	818.3	822.5	817.1
172.5°	824.3	820.7	821.9	826.1	820.7
175°	827.2	823.0	824.3	828.4	822.5
177.5°	828.4	824.3	824.9	829.1	823.7
180°	825.5	825.5	825.5	825.5	825.5



TEST NUMBER: P915989
 CATALOG NUMBER: DFN2DIP-4P4F0-060D030US930-RLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.26	10.21	10.10	11.07	12.14	5.22	6.17	6.06	7.03	8.10
	3H	10.95	11.80	11.81	12.67	13.77	6.42	7.27	7.28	8.14	9.24
	4H	11.57	12.37	12.44	13.25	14.36	6.88	7.68	7.75	8.56	9.67
	6H	12.00	12.74	12.89	13.62	14.75	7.21	7.95	8.09	8.83	9.95
	8H	12.14	12.84	13.03	13.74	14.86	7.30	8.01	8.19	8.91	10.03
	12H	12.20	12.87	13.10	13.77	14.91	7.35	8.02	8.25	8.91	10.06
4H	2H	9.29	10.10	10.17	10.97	12.08	5.84	6.64	6.71	7.51	8.62
	3H	11.14	11.81	12.03	12.71	13.84	7.20	7.87	8.09	8.77	9.90
	4H	11.84	12.45	12.74	13.35	14.50	7.75	8.36	8.65	9.26	10.41
	6H	12.37	12.89	13.28	13.82	14.97	8.18	8.70	9.09	9.63	10.78
	8H	12.55	13.04	13.47	13.96	15.13	8.31	8.80	9.23	9.72	10.89
	12H	12.65	13.09	13.59	14.03	15.20	8.38	8.82	9.32	9.76	10.94
8H	4H	11.82	12.31	12.73	13.23	14.39	8.04	8.53	8.96	9.45	10.62
	6H	12.40	12.80	13.34	13.76	14.93	8.57	8.97	9.51	9.94	11.10
	8H	12.62	12.97	13.57	13.93	15.11	8.76	9.12	9.72	10.08	11.26
	12H	12.76	13.08	13.72	14.03	15.26	8.89	9.20	9.84	10.15	11.38
12H	4H	11.78	12.22	12.71	13.16	14.33	8.06	8.49	8.99	9.44	10.61
	6H	12.37	12.73	13.32	13.68	14.87	8.62	8.98	9.57	9.93	11.12
	8H	12.60	12.92	13.55	13.86	15.10	8.84	9.15	9.79	10.10	11.33