

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902533

Luminaire Tested: DFN2DIP-HX3F0-030D060US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902533
REPORT IS A COMBINATION OF REPORTS P900764 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-030D060US830-RLONL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8002.2 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902533
CATALOG NUMBER: DFN2DIP-HX3F0-030D060US830-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P902533

CATALOG NUMBER: DFN2DIP-HX3F0-030D060US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32	34	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	18	16	15	12
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1354	1354	1354
5°	1355	1331	1340
10°	1341	1304	1296
15°	1322	1260	1228
20°	1297	1200	1144
25°	1272	1132	1064
30°	1237	1063	962
35°	1204	989	873
40°	1169	913	770
45°	1130	828	678
50°	1089	742	587
55°	1046	651	500
60°	996	556	411
65°	939	459	369
70°	869	368	333
75°	781	323	301
80°	656	268	259
85°	447	174	190

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1222 cd/sqm



TEST NUMBER: P902533

CATALOG NUMBER: DFN2DIP-HX3F0-030D060US830-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	1.4
10°-20°	300.7	3.8
20°-30°	422.1	5.3
30°-40°	460.2	5.8
40°-50°	422.9	5.3
50°-60°	332.2	4.2
60°-70°	216.2	2.7
70°-80°	111.3	1.4
80°-90°	31.8	0.4
90°-100°	62.9	0.8
100°-110°	234.6	2.9
110°-120°	622.2	7.8
120°-130°	1032.0	12.9
130°-140°	1096.2	13.7
140°-150°	1018.8	12.7
150°-160°	819.1	10.2
160°-170°	527.8	6.6
170°-180°	181.7	2.3
0°-30°	832.3	10.4
0°-40°	1292.5	16.2
0°-60°	2047.6	25.6
0°-90°	2406.8	30.1
90°-120°	919.8	11.5
90°-150°	4066.8	50.8
90°-180°	5595.0	69.9
0°-180°	8002.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	1	17	28	35	37	7
95°	90	44	54	61	59	106
105°	420	461	84	99	105	449
115°	794	818	852	213	113	782
125°	1123	1141	1167	1177	1181	1001
135°	1389	1412	1424	1438	1435	1073
145°	1612	1610	1634	1643	1636	1008
155°	1775	1762	1779	1787	1776	818
165°	1870	1862	1866	1876	1866	528
175°	1913	1903	1906	1915	1902	182
180°	1909	1909	1909	1909	1909	



TEST NUMBER: P902533

CATALOG NUMBER: DFN2DIP-HX3F0-030D060US830-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	1.3	16.6	27.5	34.6	37.2
92.5°	34.6	29.0	33.1	35.9	37.2
95°	89.7	44.1	53.8	60.9	59.4
97.5°	161.6	48.4	70.3	74.6	76.0
100°	244.5	55.2	78.7	89.7	92.5
102.5°	335.5	332.9	81.5	96.6	100.9
105°	419.8	461.3	84.3	99.3	105.0
107.5°	517.9	552.3	87.1	102.2	107.7
110°	611.9	640.7	241.8	103.7	109.1



TEST NUMBER: P902533

CATALOG NUMBER: DFN2DIP-HX3F0-030D060US830-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	700.2	725.0	701.5	106.2	110.6
115°	794.1	817.6	852.2	212.7	113.3
117.5°	875.5	903.1	926.7	729.2	367.3
120°	966.8	987.4	1012.4	1028.9	842.4
122.5°	1044.0	1066.1	1093.8	1102.0	1103.5
125°	1122.8	1140.8	1167.0	1176.7	1180.7
127.5°	1194.6	1213.9	1234.7	1248.5	1249.8
130°	1262.3	1284.4	1299.5	1314.8	1313.4
132.5°	1331.3	1349.3	1364.4	1376.9	1375.5
135°	1389.4	1411.6	1423.8	1437.8	1434.9
137.5°	1450.0	1466.6	1480.5	1494.3	1490.3
140°	1509.4	1520.6	1535.7	1548.1	1541.2
142.5°	1559.2	1569.0	1586.9	1597.8	1590.9
145°	1611.7	1610.2	1633.7	1643.4	1636.5
147.5°	1657.2	1653.0	1676.5	1683.4	1678.0
150°	1701.5	1691.8	1713.9	1722.1	1715.2
152.5°	1738.7	1727.7	1748.3	1756.7	1747.0
155°	1774.6	1762.3	1778.9	1787.1	1776.0
157.5°	1803.6	1792.6	1805.1	1814.8	1803.6
160°	1828.5	1820.1	1828.5	1836.7	1827.1
162.5°	1850.5	1842.3	1849.2	1858.9	1846.4
165°	1869.9	1861.7	1865.8	1875.5	1865.8
167.5°	1885.1	1876.8	1881.0	1890.7	1878.2
170°	1897.6	1889.2	1892.1	1901.7	1889.2
172.5°	1905.8	1897.6	1900.4	1910.1	1897.6
175°	1912.7	1903.0	1905.8	1915.4	1901.7
177.5°	1915.4	1905.8	1907.2	1916.9	1904.5
180°	1908.6	1908.6	1908.6	1908.6	1908.6



TEST NUMBER: P902533
 CATALOG NUMBER: DFN2DIP-HX3F0-030D060US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.94	6.63	7.05	7.73	9.26	1.91	2.60	3.03	3.71	5.24
	3H	7.59	8.21	8.72	9.33	10.87	3.08	3.70	4.21	4.82	6.37
	4H	8.19	8.78	9.32	9.89	11.45	3.53	4.11	4.66	5.23	6.78
	6H	8.60	9.14	9.74	10.26	11.82	3.84	4.37	4.98	5.49	7.06
	8H	8.72	9.23	9.86	10.36	11.92	3.92	4.43	5.07	5.57	7.12
	12H	8.77	9.26	9.92	10.38	11.97	3.96	4.44	5.11	5.57	7.15
4H	2H	5.93	6.52	7.08	7.64	9.19	2.48	3.07	3.63	4.19	5.74
	3H	7.74	8.23	8.89	9.37	10.94	3.82	4.30	4.96	5.45	7.01
	4H	8.42	8.87	9.57	10.00	11.59	4.36	4.80	5.50	5.93	7.52
	6H	8.92	9.31	10.08	10.46	12.04	4.76	5.15	5.92	6.30	7.88
	8H	9.09	9.45	10.25	10.59	12.19	4.89	5.24	6.04	6.39	7.98
	12H	9.17	9.50	10.35	10.66	12.25	4.94	5.27	6.11	6.42	8.02
8H	4H	8.38	8.74	9.53	9.88	11.47	4.62	4.98	5.77	6.12	7.72
	6H	8.93	9.23	10.11	10.41	12.00	5.13	5.42	6.30	6.61	8.20
	8H	9.14	9.40	10.32	10.57	12.18	5.31	5.57	6.49	6.74	8.35
	12H	9.27	9.49	10.45	10.66	12.30	5.42	5.65	6.61	6.81	8.46
12H	4H	8.32	8.65	9.49	9.81	11.40	4.62	4.94	5.79	6.10	7.70
	6H	8.91	9.16	10.09	10.33	11.94	5.17	5.43	6.35	6.60	8.21
	8H	9.11	9.34	10.30	10.50	12.15	5.37	5.60	6.56	6.76	8.41