

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916003

Luminaire Tested: DFN2DIP-4P4F0-060D070US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916003
REPORT IS A COMBINATION OF REPORTS P900653 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-060D070US930-FLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10492.9 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 122.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916003
CATALOG NUMBER: DFN2DIP-4P4F0-060D070US930-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P916003
 CATALOG NUMBER: DFN2DIP-4P4F0-060D070US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46		
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	46	45	44	39		
2	88	81	75	70	81	74	69	65	62	59	55	51	48	46	41	39	37	33		
3	81	71	64	58	74	66	59	54	55	50	46	45	42	39	36	34	32	28		
4	74	63	55	49	67	58	51	46	49	44	40	40	37	33	32	30	27	24		
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	21		
6	62	50	42	36	57	46	39	34	39	34	30	33	29	25	26	23	21	18		
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16		
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	14		
9	50	38	30	25	46	35	28	24	30	24	21	25	21	18	21	17	15	13		
10	46	34	27	22	43	32	26	21	27	22	19	23	19	16	19	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1235	1235	1235
5°	1237	1218	1226
10°	1227	1202	1210
15°	1209	1183	1185
20°	1185	1155	1159
25°	1161	1123	1128
30°	1130	1093	1090
35°	1102	1057	1049
40°	1066	1021	1010
45°	1031	985	970
50°	992	947	924
55°	952	903	882
60°	907	851	834
65°	857	798	777
70°	794	732	716
75°	706	654	660
80°	600	554	552
85°	435	380	373

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1031 cd/sqm



TEST NUMBER: P916003

CATALOG NUMBER: DFN2DIP-4P4F0-060D070US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	1.7
10°-20°	504.1	4.8
20°-30°	740.8	7.1
30°-40°	860.4	8.2
40°-50°	859.3	8.2
50°-60°	749.3	7.1
60°-70°	553.9	5.3
70°-80°	313.4	3.0
80°-90°	86.1	0.8
90°-100°	63.5	0.6
100°-110°	236.8	2.3
110°-120°	627.9	6.0
120°-130°	1041.5	9.9
130°-140°	1106.3	10.5
140°-150°	1028.1	9.8
150°-160°	826.6	7.9
160°-170°	532.6	5.1
170°-180°	183.3	1.7
0°-30°	1424.0	13.6
0°-40°	2284.3	21.8
0°-60°	3892.9	37.1
0°-90°	4846.3	46.2
90°-120°	928.2	8.8
90°-150°	4104.1	39.1
90°-180°	5647.0	53.8
0°-180°	10492.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1876	1891	1887	181
15°	1812	1801	1777	1785	1776	510
25°	1640	1625	1594	1598	1594	755
35°	1415	1397	1367	1356	1347	884
45°	1151	1138	1111	1091	1084	889
55°	871	860	838	816	807	779
65°	588	577	558	542	533	581
75°	307	304	295	284	287	328
85°	75	73	71	66	64	84
90°	1	17	28	35	38	10
95°	90	44	54	61	60	107
105°	424	466	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1178	1188	1192	1010
135°	1402	1424	1437	1451	1448	1083
145°	1626	1625	1649	1658	1652	1017
155°	1791	1778	1795	1803	1792	825
165°	1887	1879	1883	1893	1883	533
175°	1930	1920	1923	1933	1919	184
180°	1926	1926	1926	1926	1926	



TEST NUMBER: P916003

CATALOG NUMBER: DFN2DIP-4P4F0-060D070US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1903.4	1903.4	1903.4	1903.4	1903.4
2.5°	1914.5	1905.4	1885.1	1903.4	1899.9
5°	1903.4	1896.2	1876.0	1890.6	1887.1
7.5°	1890.6	1879.8	1859.5	1874.3	1870.6
10°	1870.6	1857.8	1835.8	1850.4	1844.9
12.5°	1843.1	1832.1	1810.2	1819.3	1815.7
15°	1811.9	1801.1	1777.2	1784.6	1775.5
17.5°	1773.5	1762.7	1738.8	1747.8	1738.8
20°	1731.4	1720.5	1694.8	1700.3	1693.1
22.5°	1689.5	1672.9	1649.0	1649.0	1645.4
25°	1639.9	1625.4	1594.2	1597.7	1594.2
27.5°	1584.9	1572.1	1548.4	1543.0	1533.9
30°	1530.2	1515.4	1488.1	1482.6	1475.2
32.5°	1471.5	1460.7	1431.3	1420.2	1412.9
35°	1414.9	1396.6	1367.3	1356.2	1347.0
37.5°	1350.8	1334.2	1305.0	1292.1	1283.0
40°	1284.9	1270.2	1240.9	1224.6	1217.2
42.5°	1220.8	1206.1	1177.0	1158.5	1147.6
45°	1151.4	1138.5	1110.9	1091.0	1083.5
47.5°	1083.5	1070.7	1041.5	1021.2	1010.3
50°	1012.1	1003.0	977.4	951.7	942.6
52.5°	942.6	929.8	906.0	885.9	873.1
55°	871.3	860.2	838.3	816.4	807.2
57.5°	799.9	790.8	766.9	744.9	737.5
60°	728.4	721.2	695.6	675.4	669.9
62.5°	658.8	646.0	627.8	609.5	602.2
65°	587.6	576.6	558.3	541.8	532.6
67.5°	514.4	505.1	488.8	476.0	468.6
70°	446.6	439.3	422.7	409.9	402.8
72.5°	377.1	369.7	360.6	347.8	342.3
75°	307.4	303.9	294.6	283.7	287.4
77.5°	245.2	237.9	234.2	228.8	223.3
80°	183.1	181.2	177.5	172.0	168.4
82.5°	124.5	124.5	122.7	115.4	115.4
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.4	25.6	20.2	18.3
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	163.0	48.8	71.0	75.3	76.6
100°	246.8	55.8	79.4	90.5	93.4
102.5°	338.6	336.0	82.3	97.5	101.7
105°	423.7	465.5	85.0	100.3	105.9
107.5°	522.6	557.4	87.9	103.1	108.8
110°	617.5	646.6	243.9	104.6	110.1



TEST NUMBER: P916003

CATALOG NUMBER: DFN2DIP-4P4F0-060D070US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	706.7	731.6	708.0	107.2	111.5
115°	801.4	825.0	859.9	214.7	114.4
117.5°	883.6	911.4	935.2	735.8	370.7
120°	975.6	996.5	1021.7	1038.4	850.2
122.5°	1053.5	1075.9	1103.9	1112.1	1113.6
125°	1133.0	1151.2	1177.7	1187.5	1191.6
127.5°	1205.5	1225.0	1246.0	1260.0	1261.3
130°	1273.8	1296.2	1311.4	1326.8	1325.5
132.5°	1343.5	1361.7	1377.0	1389.5	1388.2
135°	1402.1	1424.4	1436.9	1450.9	1448.1
137.5°	1463.3	1480.1	1494.1	1508.1	1503.9
140°	1523.2	1534.5	1549.7	1562.3	1555.3
142.5°	1573.5	1583.3	1601.3	1612.4	1605.5
145°	1626.5	1625.1	1648.7	1658.5	1651.5
147.5°	1672.3	1668.3	1691.9	1698.8	1693.4
150°	1717.0	1707.3	1729.7	1737.9	1731.0
152.5°	1754.6	1743.5	1764.4	1772.8	1763.1
155°	1790.9	1778.4	1795.1	1803.4	1792.4
157.5°	1820.2	1809.1	1821.6	1831.4	1820.2
160°	1845.3	1836.9	1845.3	1853.6	1843.8
162.5°	1867.5	1859.2	1866.1	1875.9	1863.4
165°	1887.0	1878.8	1882.8	1892.6	1882.8
167.5°	1902.4	1893.9	1898.3	1908.0	1895.5
170°	1915.0	1906.6	1909.3	1919.1	1906.6
172.5°	1923.3	1915.0	1917.8	1927.5	1915.0
175°	1930.2	1920.4	1923.3	1933.0	1919.1
177.5°	1933.0	1923.3	1924.8	1934.5	1921.9
180°	1926.1	1926.1	1926.1	1926.1	1926.1



TEST NUMBER: P916003
 CATALOG NUMBER: DFN2DIP-4P4F0-060D070US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.66	8.49	8.65	9.49	10.82	7.22	8.04	8.21	9.05	10.37
	3H	9.32	10.07	10.32	11.08	12.42	8.83	9.58	9.83	10.59	11.93
	4H	9.91	10.62	10.93	11.63	12.98	9.42	10.12	10.43	11.14	12.49
	6H	10.32	10.96	11.34	11.98	13.35	9.82	10.46	10.84	11.48	12.85
	8H	10.42	11.04	11.45	12.07	13.44	9.92	10.54	10.95	11.57	12.93
	12H	10.47	11.06	11.51	12.09	13.47	9.96	10.55	11.00	11.58	12.96
4H	2H	8.12	8.82	9.14	9.84	11.19	7.76	8.47	8.78	9.48	10.83
	3H	9.99	10.57	11.02	11.62	12.98	9.58	10.17	10.61	11.21	12.58
	4H	10.71	11.24	11.74	12.28	13.67	10.28	10.82	11.32	11.85	13.24
	6H	11.22	11.69	12.27	12.74	14.13	10.79	11.25	11.84	12.31	13.70
	8H	11.38	11.81	12.42	12.86	14.26	10.94	11.37	11.98	12.42	13.82
	12H	11.45	11.84	12.51	12.90	14.31	11.00	11.39	12.06	12.46	13.86
8H	4H	10.90	11.33	11.95	12.38	13.78	10.52	10.96	11.57	12.01	13.41
	6H	11.54	11.89	12.61	12.99	14.38	11.15	11.51	12.22	12.60	14.00
	8H	11.76	12.07	12.84	13.15	14.57	11.37	11.68	12.45	12.76	14.18
	12H	11.89	12.17	12.98	13.24	14.70	11.48	11.76	12.56	12.83	14.29
12H	4H	10.88	11.27	11.95	12.34	13.75	10.52	10.91	11.58	11.97	13.38
	6H	11.57	11.88	12.64	12.96	14.37	11.19	11.51	12.27	12.58	14.00
	8H	11.81	12.09	12.89	13.16	14.62	11.43	11.71	12.51	12.78	14.24