

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916030

Luminaire Tested: DFN2DIP-4P4F0-070D080US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916030
REPORT IS A COMBINATION OF REPORTS P899147 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D080US930-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11422.4 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 147.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916030
CATALOG NUMBER: DFN2DIP-4P4F0-070D080US930-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P916030

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	47	47	47	42
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40	40	40	40	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	34	34	34	30
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29	29	29	29	25
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	25	25	25	22
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	22	22	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	20	20	20	17
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	18	18	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	16	16	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1441	1441	1441
5°	1443	1421	1431
10°	1431	1402	1412
15°	1411	1380	1382
20°	1382	1348	1352
25°	1354	1310	1316
30°	1319	1275	1271
35°	1285	1233	1224
40°	1244	1191	1178
45°	1203	1149	1132
50°	1158	1105	1078
55°	1111	1054	1029
60°	1058	993	973
65°	1000	930	906
70°	926	854	835
75°	823	762	770
80°	700	646	644
85°	509	444	435

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1562 cd/sqm



TEST NUMBER: P916030

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.0	1.8
10°-20°	588.1	5.1
20°-30°	864.2	7.6
30°-40°	1003.7	8.8
40°-50°	1002.5	8.8
50°-60°	874.2	7.7
60°-70°	646.2	5.7
70°-80°	365.6	3.2
80°-90°	102.4	0.9
90°-100°	127.6	1.1
100°-110°	405.6	3.6
110°-120°	694.1	6.1
120°-130°	912.8	8.0
130°-140°	1024.6	9.0
140°-150°	1004.7	8.8
150°-160°	842.8	7.4
160°-170°	558.9	4.9
170°-180°	195.4	1.7
0°-30°	1661.3	14.5
0°-40°	2665.1	23.3
0°-60°	4541.7	39.8
0°-90°	5655.9	49.5
90°-120°	1227.3	10.7
90°-150°	4169.4	36.5
90°-180°	5766.0	50.5
0°-180°	11422.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2221	2221	2221	2221	2221	
5°	2221	2212	2189	2206	2202	211
15°	2114	2101	2073	2082	2071	595
25°	1913	1896	1860	1864	1860	880
35°	1651	1629	1595	1582	1572	1031
45°	1343	1328	1296	1273	1264	1037
55°	1016	1004	978	952	942	909
65°	686	673	651	632	621	678
75°	359	355	344	331	335	383
85°	88	85	83	77	75	98
90°	2	22	61	57	59	11
95°	91	108	111	111	108	101
105°	374	379	383	386	386	395
115°	696	706	703	702	696	689
125°	1013	1029	1024	1018	1016	905
135°	1310	1330	1333	1332	1326	1013
145°	1591	1603	1613	1615	1608	994
155°	1819	1824	1830	1838	1833	837
165°	1979	1977	1977	1989	1981	558
175°	2059	2054	2050	2063	2052	196
180°	2063	2063	2063	2063	2063	



TEST NUMBER: P916030

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US930-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2220.6	2220.6	2220.6	2220.6	2220.6
2.5°	2233.6	2222.9	2199.3	2220.6	2216.6
5°	2220.6	2212.3	2188.7	2205.7	2201.6
7.5°	2205.7	2193.0	2169.4	2186.7	2182.4
10°	2182.4	2167.4	2141.8	2158.8	2152.5
12.5°	2150.2	2137.5	2111.9	2122.5	2118.2
15°	2114.0	2101.3	2073.4	2082.0	2071.3
17.5°	2069.1	2056.4	2028.5	2039.2	2028.5
20°	2019.9	2007.3	1977.3	1983.7	1975.3
22.5°	1971.0	1951.7	1923.9	1923.9	1919.5
25°	1913.3	1896.2	1860.0	1864.1	1860.0
27.5°	1849.1	1834.2	1806.5	1800.2	1789.5
30°	1785.3	1768.0	1736.1	1729.7	1721.1
32.5°	1716.8	1704.1	1669.9	1657.0	1648.4
35°	1650.7	1629.4	1595.1	1582.2	1571.6
37.5°	1575.9	1556.6	1522.4	1507.5	1496.8
40°	1499.1	1481.9	1447.6	1428.6	1420.0
42.5°	1424.3	1407.1	1373.1	1351.6	1338.9
45°	1343.2	1328.3	1296.1	1272.8	1264.1
47.5°	1264.1	1249.2	1215.0	1191.4	1178.8
50°	1180.8	1170.1	1140.2	1110.4	1099.7
52.5°	1099.7	1084.8	1057.1	1033.6	1018.6
55°	1016.5	1003.6	978.0	952.4	941.8
57.5°	933.2	922.5	894.6	869.0	860.5
60°	849.8	841.4	811.5	788.0	781.6
62.5°	768.7	753.7	732.5	711.2	702.5
65°	685.6	672.6	651.3	632.1	621.4
67.5°	600.1	589.3	570.2	555.3	546.7
70°	521.1	512.5	493.2	478.3	469.9
72.5°	439.9	431.4	420.7	405.8	399.4
75°	358.6	354.6	343.6	331.0	335.3
77.5°	286.2	277.5	273.2	266.8	260.6
80°	213.6	211.4	207.1	200.7	196.4
82.5°	145.2	145.2	143.2	134.6	134.6
85°	87.5	85.4	83.4	76.8	74.8
87.5°	38.5	34.2	29.9	23.6	21.3
90°	1.9	22.4	61.0	57.2	59.1
92.5°	38.6	52.3	54.1	55.9	55.9
95°	90.8	108.2	111.3	111.3	108.2
97.5°	151.2	167.3	174.1	174.1	174.1
100°	220.8	235.1	240.0	240.0	238.1
102.5°	294.2	304.8	311.5	313.4	311.5
105°	374.4	379.4	383.1	386.2	386.2
107.5°	454.0	461.5	461.5	462.7	454.0
110°	531.1	541.0	541.0	541.0	536.1



TEST NUMBER: P916030

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	614.4	625.0	623.1	618.2	614.4
115°	696.5	706.5	703.4	701.5	696.5
117.5°	778.0	791.7	782.9	778.0	773.0
120°	860.1	873.8	860.1	860.1	854.4
122.5°	934.7	952.1	943.4	938.4	934.7
125°	1013.0	1028.6	1023.6	1018.0	1016.2
127.5°	1089.6	1108.8	1102.0	1094.5	1089.6
130°	1161.1	1183.4	1180.3	1176.6	1169.8
132.5°	1241.3	1258.7	1260.0	1251.2	1246.3
135°	1310.3	1329.6	1333.3	1331.5	1326.5
137.5°	1387.4	1403.0	1406.1	1404.8	1397.3
140°	1455.2	1470.7	1479.4	1479.4	1472.6
142.5°	1524.9	1540.4	1545.4	1547.3	1540.4
145°	1590.8	1603.2	1613.1	1615.0	1608.2
147.5°	1649.8	1665.4	1672.8	1676.0	1669.2
150°	1710.8	1721.3	1728.2	1733.8	1728.2
152.5°	1764.9	1775.5	1784.2	1791.0	1784.2
155°	1819.0	1824.0	1829.6	1838.3	1832.7
157.5°	1865.6	1869.4	1872.5	1884.9	1876.2
160°	1907.3	1911.1	1912.9	1923.5	1916.0
162.5°	1945.9	1945.9	1947.7	1959.6	1950.8
165°	1978.8	1976.9	1976.9	1989.4	1980.7
167.5°	2008.7	2003.1	2003.1	2015.5	2006.8
170°	2031.1	2026.1	2024.2	2036.7	2026.1
172.5°	2046.6	2041.7	2039.8	2052.2	2041.7
175°	2059.0	2054.1	2050.3	2062.8	2052.2
177.5°	2065.9	2060.9	2057.2	2067.8	2057.2
180°	2062.8	2062.8	2062.8	2062.8	2062.8



TEST NUMBER: P916030
 CATALOG NUMBER: DFN2DIP-4P4F0-070D080US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.51	9.37	9.47	10.35	11.62	8.07	8.93	9.03	9.90	11.18
	3H	10.18	10.95	11.15	11.93	13.23	9.69	10.46	10.66	11.44	12.74
	4H	10.77	11.50	11.76	12.49	13.80	10.28	11.00	11.26	11.99	13.30
	6H	11.17	11.84	12.17	12.84	14.16	10.67	11.34	11.67	12.34	13.66
	8H	11.28	11.92	12.28	12.93	14.25	10.78	11.42	11.78	12.43	13.75
	12H	11.33	11.94	12.34	12.94	14.29	10.82	11.43	11.83	12.43	13.78
4H	2H	8.97	9.70	9.97	10.69	12.00	8.62	9.35	9.61	10.34	11.65
	3H	10.85	11.45	11.85	12.47	13.79	10.44	11.05	11.44	12.06	13.39
	4H	11.56	12.12	12.57	13.13	14.48	11.14	11.70	12.15	12.71	14.05
	6H	12.09	12.56	13.11	13.60	14.94	11.65	12.13	12.67	13.17	14.51
	8H	12.24	12.68	13.26	13.71	15.07	11.80	12.25	12.82	13.27	14.63
	12H	12.31	12.72	13.35	13.76	15.12	11.86	12.27	12.90	13.31	14.67
8H	4H	11.76	12.21	12.78	13.24	14.59	11.39	11.83	12.41	12.86	14.22
	6H	12.40	12.77	13.45	13.84	15.19	12.02	12.39	13.06	13.45	14.81
	8H	12.62	12.95	13.68	14.00	15.38	12.23	12.56	13.29	13.61	14.99
	12H	12.76	13.05	13.82	14.10	15.51	12.35	12.63	13.41	13.68	15.10
12H	4H	11.75	12.15	12.79	13.19	14.56	11.38	11.78	12.42	12.83	14.19
	6H	12.43	12.76	13.48	13.81	15.18	12.06	12.38	13.11	13.44	14.81
	8H	12.68	12.96	13.73	14.01	15.43	12.30	12.58	13.35	13.63	15.05