

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902559

Luminaire Tested: DFN2DIP-HX3F0-040D070US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902559
REPORT IS A COMBINATION OF REPORTS P900779 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-040D070US830-FLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10264.3 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 87.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902559
CATALOG NUMBER: DFN2DIP-HX3F0-040D070US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P902559

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31				31
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31	26				26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22				22
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23	19				19
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20	16				16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14				14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13				13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11				11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12	10				10
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1699	1699	1699
5°	1701	1674	1686
10°	1687	1651	1662
15°	1661	1622	1626
20°	1627	1583	1588
25°	1593	1537	1545
30°	1550	1494	1490
35°	1510	1443	1433
40°	1460	1392	1378
45°	1410	1340	1321
50°	1356	1286	1256
55°	1300	1224	1196
60°	1235	1149	1127
65°	1165	1072	1046
70°	1076	978	958
75°	952	866	876
80°	802	722	722
85°	569	477	468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1429 cd/sqm



TEST NUMBER: P902559

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	1.3
10°-20°	388.5	3.8
20°-30°	570.9	5.6
30°-40°	663.1	6.5
40°-50°	662.3	6.5
50°-60°	577.5	5.6
60°-70°	426.9	4.2
70°-80°	241.5	2.4
80°-90°	67.7	0.7
90°-100°	73.4	0.7
100°-110°	273.7	2.7
110°-120°	725.9	7.1
120°-130°	1204.0	11.7
130°-140°	1278.9	12.5
140°-150°	1188.6	11.6
150°-160°	955.6	9.3
160°-170°	615.8	6.0
170°-180°	211.9	2.1
0°-30°	1097.5	10.7
0°-40°	1760.6	17.2
0°-60°	3000.3	29.2
0°-90°	3736.4	36.4
90°-120°	1073.0	10.5
90°-150°	4744.6	46.2
90°-180°	6528.0	63.6
0°-180°	10264.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	2	19	32	40	44	9
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1362	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2182	2172	2177	2188	2177	616
175°	2232	2220	2224	2235	2219	212
180°	2227	2227	2227	2227	2227	



TEST NUMBER: P902559

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1475.5	1468.5	1452.9	1467.0	1464.3
5°	1467.0	1461.4	1445.9	1457.1	1454.4
7.5°	1457.1	1448.7	1433.1	1444.5	1441.7
10°	1441.7	1431.8	1414.9	1426.2	1421.9
12.5°	1420.4	1412.0	1395.2	1402.2	1399.3
15°	1396.5	1388.1	1369.7	1375.4	1368.4
17.5°	1366.9	1358.5	1340.1	1347.1	1340.1
20°	1334.4	1326.0	1306.3	1310.4	1304.9
22.5°	1302.0	1289.3	1270.9	1270.9	1268.1
25°	1263.9	1252.6	1228.7	1231.4	1228.7
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1168.0	1146.9	1142.6	1137.0
32.5°	1134.2	1125.8	1103.2	1094.7	1088.9
35°	1090.4	1076.4	1053.8	1045.3	1038.2
37.5°	1041.0	1028.3	1005.7	995.9	988.8
40°	990.3	978.9	956.3	943.8	938.1
42.5°	940.9	929.5	907.1	892.9	884.5
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.7	787.1	778.7
50°	780.0	773.0	753.3	733.5	726.4
52.5°	726.4	716.6	698.3	682.8	672.9
55°	671.6	663.0	646.1	629.1	622.2
57.5°	616.4	609.4	591.0	574.1	568.4
60°	561.4	555.8	536.1	520.6	516.3
62.5°	507.8	497.9	483.9	469.8	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.6	325.8	315.9	310.4
72.5°	290.7	284.9	278.0	268.1	263.8
75°	237.0	234.2	227.1	218.7	221.5
77.5°	189.0	183.3	180.5	176.3	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	96.0	96.0	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	1.5	19.3	32.1	40.3	43.5
92.5°	40.3	33.8	38.6	41.9	43.5
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.2	644.4	101.6	119.2	125.7
110°	713.9	747.5	282.0	120.9	127.2



TEST NUMBER: P902559

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.8	994.1	248.2	132.2
117.5°	1021.5	1053.7	1081.2	850.6	428.6
120°	1127.8	1152.0	1181.1	1200.4	982.9
122.5°	1218.0	1243.8	1276.2	1285.7	1287.4
125°	1309.9	1330.9	1361.5	1372.8	1377.5
127.5°	1393.6	1416.2	1440.5	1456.6	1458.1
130°	1472.6	1498.5	1516.1	1533.9	1532.4
132.5°	1553.2	1574.2	1591.9	1606.4	1604.9
135°	1620.9	1646.7	1661.1	1677.3	1674.1
137.5°	1691.7	1711.1	1727.3	1743.4	1738.6
140°	1761.0	1774.0	1791.6	1806.1	1798.1
142.5°	1819.1	1830.4	1851.2	1864.1	1856.1
145°	1880.4	1878.7	1906.0	1917.3	1909.3
147.5°	1933.3	1928.6	1956.0	1964.0	1957.7
150°	1985.0	1973.8	1999.6	2009.1	2001.1
152.5°	2028.4	2015.6	2039.8	2049.5	2038.2
155°	2070.4	2056.0	2075.3	2084.9	2072.1
157.5°	2104.2	2091.4	2105.9	2117.2	2104.2
160°	2133.4	2123.5	2133.4	2142.9	2131.6
162.5°	2159.0	2149.4	2157.4	2168.7	2154.2
165°	2181.5	2172.0	2176.7	2188.0	2176.7
167.5°	2199.3	2189.5	2194.5	2205.8	2191.3
170°	2213.8	2204.1	2207.3	2218.7	2204.1
172.5°	2223.5	2213.8	2217.1	2228.4	2213.8
175°	2231.5	2220.2	2223.5	2234.7	2218.7
177.5°	2234.7	2223.5	2225.2	2236.5	2221.9
180°	2226.7	2226.7	2226.7	2226.7	2226.7



TEST NUMBER: P902559
 CATALOG NUMBER: DFN2DIP-HX3F0-040D070US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.66	8.41	8.73	9.48	10.94	7.23	7.99	8.30	9.05	10.51
	3H	9.31	9.98	10.38	11.06	12.53	8.84	9.51	9.91	10.59	12.06
	4H	9.89	10.52	10.97	11.60	13.08	9.42	10.06	10.50	11.13	12.61
	6H	10.27	10.86	11.37	11.94	13.43	9.80	10.39	10.90	11.47	12.96
	8H	10.37	10.93	11.47	12.03	13.51	9.90	10.46	11.00	11.56	13.04
	12H	10.41	10.94	11.52	12.04	13.54	9.94	10.47	11.04	11.56	13.07
4H	2H	8.11	8.75	9.20	9.83	11.30	7.77	8.40	8.86	9.48	10.96
	3H	9.96	10.49	11.06	11.59	13.08	9.57	10.10	10.67	11.20	12.69
	4H	10.66	11.15	11.76	12.24	13.76	10.26	10.75	11.36	11.84	13.35
	6H	11.16	11.58	12.27	12.70	14.20	10.76	11.18	11.87	12.29	13.80
	8H	11.30	11.70	12.42	12.81	14.33	10.90	11.29	12.01	12.40	13.92
	12H	11.37	11.72	12.50	12.85	14.37	10.95	11.31	12.08	12.43	13.96
8H	4H	10.84	11.24	11.96	12.35	13.87	10.49	10.88	11.60	11.99	13.51
	6H	11.46	11.79	12.60	12.94	14.45	11.10	11.43	12.24	12.58	14.10
	8H	11.68	11.96	12.82	13.09	14.63	11.31	11.59	12.45	12.73	14.26
	12H	11.80	12.05	12.94	13.18	14.75	11.42	11.67	12.56	12.80	14.37
12H	4H	10.82	11.18	11.95	12.30	13.83	10.47	10.83	11.60	11.95	13.48
	6H	11.49	11.77	12.63	12.91	14.44	11.14	11.42	12.28	12.56	14.09
	8H	11.72	11.97	12.86	13.10	14.67	11.37	11.62	12.51	12.75	14.32