

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916042

Luminaire Tested: DFN2DIP-4P4F0-080D050US930-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P916042  
REPORT IS A COMBINATION OF REPORTS P899113 AND P895967  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P4F0-080D050US930-FLLFLL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10064.9 lumens  
Efficiency: N/A  
Efficacy: 79.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 126  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P916042  
CATALOG NUMBER: DFN2DIP-4P4F0-080D050US930-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P916042

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US930-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	69	69	69	64
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	61	60	58	61	60	58	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	54	51	49	45
3	84	74	67	61	79	70	63	58	62	57	52	55	50	47	48	45	42	48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	32	38	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	35	31	28	25
7	60	48	40	34	56	45	38	32	40	34	30	36	31	27	32	28	25	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1646	1646	1646
5°	1649	1624	1635
10°	1636	1603	1614
15°	1612	1577	1580
20°	1580	1541	1545
25°	1547	1497	1504
30°	1507	1457	1453
35°	1469	1409	1398
40°	1422	1361	1347
45°	1375	1313	1294
50°	1323	1263	1232
55°	1269	1205	1176
60°	1209	1135	1112
65°	1143	1064	1036
70°	1058	976	954
75°	941	872	880
80°	801	739	736
85°	581	508	496

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1375 cd/sqm



TEST NUMBER: P916042

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US930-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	238.9	2.4
10°-20°	672.1	6.7
20°-30°	987.7	9.8
30°-40°	1147.1	11.4
40°-50°	1145.7	11.4
50°-60°	999.0	9.9
60°-70°	738.5	7.3
70°-80°	417.8	4.2
80°-90°	114.0	1.1
90°-100°	79.8	0.8
100°-110°	253.5	2.5
110°-120°	433.8	4.3
120°-130°	570.5	5.7
130°-140°	640.4	6.4
140°-150°	627.9	6.2
150°-160°	526.8	5.2
160°-170°	349.3	3.5
170°-180°	122.1	1.2
0°-30°	1898.6	18.9
0°-40°	3045.8	30.3
0°-60°	5190.5	51.6
0°-90°	6460.8	64.2
90°-120°	767.0	7.6
90°-150°	2605.8	25.9
90°-180°	3604.0	35.8
0°-180°	10064.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2538	2538	2538	2538	2538	
5°	2538	2528	2501	2521	2516	241
15°	2416	2402	2370	2379	2367	680
25°	2186	2167	2126	2130	2126	1006
35°	1886	1862	1823	1808	1796	1178
45°	1535	1518	1481	1455	1445	1185
55°	1162	1147	1118	1088	1076	1039
65°	784	769	744	722	710	775
75°	410	405	393	378	383	438
85°	100	98	95	88	85	112
90°	1	14	38	36	37	10
95°	57	68	70	70	68	63
105°	234	237	240	241	241	247
115°	435	442	440	438	435	431
125°	633	643	640	636	635	566
135°	819	831	833	832	829	633
145°	994	1002	1008	1009	1005	621
155°	1137	1140	1144	1149	1145	523
165°	1237	1236	1236	1243	1238	349
175°	1287	1284	1282	1289	1283	122
180°	1289	1289	1289	1289	1289	



TEST NUMBER: P916042

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US930-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2537.9	2537.9	2537.9	2537.9	2537.9
2.5°	2552.6	2540.5	2513.6	2537.9	2533.2
5°	2537.9	2528.3	2501.4	2520.8	2516.2
7.5°	2520.8	2506.3	2479.4	2499.1	2494.2
10°	2494.2	2477.0	2447.8	2467.2	2460.0
12.5°	2457.4	2442.9	2413.6	2425.8	2420.9
15°	2416.0	2401.5	2369.6	2379.4	2367.3
17.5°	2364.7	2350.2	2318.3	2330.5	2318.3
20°	2308.5	2294.0	2259.8	2267.1	2257.5
22.5°	2252.6	2230.6	2198.7	2198.7	2193.8
25°	2186.5	2167.1	2125.7	2130.4	2125.7
27.5°	2113.3	2096.2	2064.6	2057.3	2045.2
30°	2040.3	2020.6	1984.1	1976.9	1967.0
32.5°	1962.1	1947.6	1908.5	1893.7	1883.9
35°	1886.4	1862.1	1823.0	1808.2	1796.1
37.5°	1801.0	1779.0	1739.9	1722.8	1710.7
40°	1713.3	1693.5	1654.5	1632.7	1622.9
42.5°	1627.8	1608.1	1569.3	1544.7	1530.2
45°	1535.1	1518.0	1481.2	1454.6	1444.8
47.5°	1444.8	1427.7	1388.5	1361.6	1347.1
50°	1349.5	1337.3	1303.1	1268.9	1256.8
52.5°	1256.8	1239.7	1208.1	1181.2	1164.1
55°	1161.7	1147.0	1117.8	1088.5	1076.3
57.5°	1066.5	1054.3	1022.5	993.2	983.3
60°	971.2	961.6	927.4	900.5	893.2
62.5°	878.5	861.4	837.1	812.8	802.9
65°	783.5	768.7	744.4	722.4	710.2
67.5°	685.8	673.4	651.7	634.6	624.8
70°	595.5	585.6	563.7	546.6	537.0
72.5°	502.8	493.0	480.8	463.7	456.5
75°	409.9	405.2	392.8	378.3	383.2
77.5°	327.0	317.2	312.3	305.0	297.7
80°	244.2	241.6	236.7	229.4	224.5
82.5°	166.0	166.0	163.6	153.8	153.8
85°	100.0	97.6	95.3	87.8	85.4
87.5°	44.0	39.1	34.2	26.9	24.4
90°	1.1	14.0	38.1	35.8	36.9
92.5°	24.1	32.6	33.8	35.0	35.0
95°	56.7	67.7	69.5	69.5	67.7
97.5°	94.4	104.5	108.8	108.8	108.8
100°	137.9	146.9	150.0	150.0	148.9
102.5°	183.8	190.5	194.7	195.9	194.7
105°	234.0	237.1	239.5	241.3	241.3
107.5°	283.7	288.4	288.4	289.2	283.7
110°	331.9	338.2	338.2	338.2	335.0



TEST NUMBER: P916042

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US930-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	384.0	390.6	389.5	386.4	384.0
115°	435.3	441.6	439.6	438.5	435.3
117.5°	486.2	494.8	489.3	486.2	483.1
120°	537.5	546.1	537.5	537.5	534.0
122.5°	584.2	595.1	589.6	586.5	584.2
125°	633.2	642.9	639.8	636.3	635.1
127.5°	680.9	693.0	688.8	684.0	680.9
130°	725.7	739.6	737.7	735.4	731.1
132.5°	775.8	786.7	787.5	782.0	778.9
135°	819.0	831.0	833.3	832.2	829.1
137.5°	867.2	876.9	878.8	878.0	873.3
140°	909.5	919.2	924.6	924.6	920.4
142.5°	953.0	962.8	965.9	967.0	962.8
145°	994.3	1002.0	1008.2	1009.4	1005.1
147.5°	1031.2	1040.9	1045.5	1047.5	1043.2
150°	1069.3	1075.9	1080.1	1083.6	1080.1
152.5°	1103.1	1109.7	1115.1	1119.4	1115.1
155°	1136.9	1140.0	1143.5	1148.9	1145.4
157.5°	1166.0	1168.3	1170.3	1178.1	1172.6
160°	1192.0	1194.4	1195.6	1202.2	1197.5
162.5°	1216.2	1216.2	1217.3	1224.7	1219.3
165°	1236.8	1235.6	1235.6	1243.4	1237.9
167.5°	1255.4	1251.9	1251.9	1259.7	1254.3
170°	1269.4	1266.3	1265.2	1272.9	1266.3
172.5°	1279.1	1276.0	1274.9	1282.6	1276.0
175°	1286.9	1283.8	1281.5	1289.2	1282.6
177.5°	1291.2	1288.1	1285.7	1292.3	1285.7
180°	1289.2	1289.2	1289.2	1289.2	1289.2



TEST NUMBER: P916042  
 CATALOG NUMBER: DFN2DIP-4P4F0-080D050US930-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.24	11.24	11.06	12.09	13.14	9.79	10.80	10.62	11.65	12.70
	3H	11.91	12.82	12.75	13.67	14.75	11.42	12.33	12.26	13.18	14.26
	4H	12.51	13.37	13.37	14.23	15.32	12.02	12.87	12.87	13.74	14.83
	6H	12.92	13.71	13.79	14.58	15.69	12.42	13.21	13.29	14.08	15.19
	8H	13.04	13.79	13.91	14.67	15.78	12.53	13.28	13.41	14.17	15.28
	12H	13.09	13.81	13.97	14.69	15.82	12.58	13.30	13.46	14.18	15.31
4H	2H	10.72	11.57	11.58	12.43	13.53	10.36	11.22	11.22	12.08	13.17
	3H	12.60	13.31	13.47	14.21	15.32	12.19	12.91	13.07	13.80	14.91
	4H	13.33	13.98	14.21	14.87	16.00	12.90	13.55	13.79	14.45	15.58
	6H	13.86	14.42	14.75	15.33	16.47	13.42	13.98	14.32	14.90	16.04
	8H	14.01	14.54	14.91	15.45	16.60	13.57	14.10	14.47	15.01	16.16
	12H	14.09	14.57	15.02	15.50	16.65	13.64	14.12	14.57	15.05	16.20
8H	4H	13.54	14.06	14.44	14.97	16.12	13.16	13.68	14.06	14.60	15.74
	6H	14.18	14.61	15.11	15.57	16.72	13.80	14.23	14.72	15.18	16.33
	8H	14.41	14.79	15.34	15.74	16.90	14.01	14.40	14.95	15.34	16.51
	12H	14.55	14.89	15.49	15.82	17.04	14.14	14.48	15.08	15.41	16.63
12H	4H	13.53	14.00	14.45	14.93	16.09	13.16	13.63	14.08	14.56	15.72
	6H	14.21	14.60	15.15	15.54	16.71	13.84	14.23	14.78	15.17	16.34
	8H	14.46	14.80	15.41	15.74	16.96	14.08	14.42	15.03	15.36	16.58