

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902586

Luminaire Tested: DFN2DIP-HX3F0-050D080US830-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P902586  
REPORT IS A COMBINATION OF REPORTS P899275 AND P896089  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-050D080US830-FLLFLL  
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11338.8 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 106.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P902586  
CATALOG NUMBER: DFN2DIP-HX3F0-050D080US830-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P902586

CATALOG NUMBER: DFN2DIP-HX3F0-050D080US830-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	41	41	41	41	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	34	34	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	29	29	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	25	25	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	22	22	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	19	19	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	15	15	15	13
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	14	14	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	13	13	13	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2124	2124	2124
5°	2127	2093	2108
10°	2108	2063	2078
15°	2076	2028	2032
20°	2034	1979	1985
25°	1991	1921	1931
30°	1938	1867	1863
35°	1887	1804	1791
40°	1825	1740	1722
45°	1763	1675	1652
50°	1696	1608	1570
55°	1624	1529	1495
60°	1544	1437	1409
65°	1456	1340	1308
70°	1345	1223	1198
75°	1190	1082	1095
80°	1003	903	902
85°	711	597	585

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2244 cd/sqm



TEST NUMBER: P902586

CATALOG NUMBER: DFN2DIP-HX3F0-050D080US830-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.6	1.5
10°-20°	485.6	4.3
20°-30°	713.7	6.3
30°-40°	828.9	7.3
40°-50°	827.8	7.3
50°-60°	721.8	6.4
60°-70°	533.6	4.7
70°-80°	301.9	2.7
80°-90°	86.5	0.8
90°-100°	147.6	1.3
100°-110°	468.9	4.1
110°-120°	802.4	7.1
120°-130°	1055.3	9.3
130°-140°	1184.5	10.4
140°-150°	1161.5	10.2
150°-160°	974.4	8.6
160°-170°	646.2	5.7
170°-180°	225.9	2.0
0°-30°	1371.9	12.1
0°-40°	2200.7	19.4
0°-60°	3750.4	33.1
0°-90°	4672.4	41.2
90°-120°	1418.8	12.5
90°-150°	4820.1	42.5
90°-180°	6666.0	58.8
0°-180°	11338.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1834	1834	1834	1834	1834	
5°	1834	1827	1807	1821	1818	174
15°	1746	1735	1712	1719	1710	492
25°	1580	1566	1536	1539	1536	727
35°	1363	1346	1317	1307	1298	851
45°	1109	1097	1070	1051	1044	856
55°	839	829	808	786	778	750
65°	566	555	538	522	513	560
75°	296	293	284	273	277	316
85°	72	70	69	63	62	81
90°	2	26	70	66	68	11
95°	105	125	129	129	125	117
105°	433	439	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1534	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2286	2286	2300	2290	645
175°	2380	2375	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	



TEST NUMBER: P902586

CATALOG NUMBER: DFN2DIP-HX3F0-050D080US830-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1833.7	1833.7	1833.7	1833.7	1833.7
2.5°	1844.4	1835.6	1816.2	1833.7	1830.4
5°	1833.7	1826.8	1807.3	1821.4	1818.1
7.5°	1821.4	1810.9	1791.5	1805.7	1802.1
10°	1802.1	1789.8	1768.7	1782.6	1777.4
12.5°	1775.6	1765.1	1744.0	1752.8	1749.2
15°	1745.6	1735.1	1712.1	1719.3	1710.4
17.5°	1708.5	1698.1	1675.1	1683.9	1675.1
20°	1668.0	1657.6	1632.9	1638.0	1631.2
22.5°	1627.6	1611.7	1588.7	1588.7	1585.1
25°	1579.9	1565.8	1535.9	1539.3	1535.9
27.5°	1526.9	1514.6	1491.8	1486.5	1477.7
30°	1474.1	1460.0	1433.6	1428.3	1421.3
32.5°	1417.7	1407.2	1378.9	1368.3	1361.2
35°	1363.0	1345.5	1317.2	1306.6	1297.8
37.5°	1301.3	1285.4	1257.2	1244.8	1236.0
40°	1237.9	1223.7	1195.4	1179.7	1172.6
42.5°	1176.2	1162.0	1133.9	1116.1	1105.6
45°	1109.2	1096.8	1070.3	1051.0	1043.9
47.5°	1043.9	1031.5	1003.3	983.8	973.4
50°	975.1	966.3	941.6	916.9	908.0
52.5°	908.0	895.7	872.9	853.5	841.1
55°	839.4	828.8	807.6	786.5	777.7
57.5°	770.5	761.8	738.8	717.7	710.5
60°	701.7	694.8	670.1	650.6	645.5
62.5°	634.8	622.5	604.8	587.2	580.1
65°	566.1	555.4	537.8	522.0	513.1
67.5°	495.6	486.6	470.9	458.5	451.4
70°	430.3	423.2	407.3	394.9	388.0
72.5°	363.4	356.2	347.4	335.1	329.8
75°	296.1	292.8	283.8	273.3	276.9
77.5°	236.3	229.1	225.6	220.4	215.2
80°	176.4	174.6	171.0	165.8	162.2
82.5°	119.9	119.9	118.2	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.8	28.3	24.7	19.4	17.6
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.6	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	614.0	625.5	625.5	625.5	619.7



TEST NUMBER: P902586

CATALOG NUMBER: DFN2DIP-HX3F0-050D080US830-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.6	720.4	714.6	710.3
115°	805.2	816.7	813.1	811.0	805.2
117.5°	899.4	915.2	905.1	899.4	893.6
120°	994.3	1010.1	994.3	994.3	987.8
122.5°	1080.5	1100.7	1090.6	1084.9	1080.5
125°	1171.1	1189.1	1183.4	1176.9	1174.8
127.5°	1259.6	1281.9	1273.9	1265.4	1259.6
130°	1342.3	1368.1	1364.5	1360.3	1352.4
132.5°	1435.0	1455.1	1456.6	1446.5	1440.8
135°	1514.8	1537.1	1541.4	1539.3	1533.5
137.5°	1603.9	1621.9	1625.5	1624.1	1615.4
140°	1682.3	1700.3	1710.3	1710.3	1702.4
142.5°	1762.8	1780.8	1786.6	1788.8	1780.8
145°	1839.1	1853.4	1864.9	1867.1	1859.2
147.5°	1907.3	1925.3	1933.9	1937.6	1929.7
150°	1977.8	1990.0	1997.9	2004.4	1997.9
152.5°	2040.3	2052.6	2062.7	2070.6	2062.7
155°	2102.9	2108.7	2115.2	2125.2	2118.7
157.5°	2156.8	2161.2	2164.7	2179.1	2169.1
160°	2205.0	2209.3	2211.5	2223.6	2215.1
162.5°	2249.6	2249.6	2251.7	2265.4	2255.3
165°	2287.6	2285.5	2285.5	2299.9	2289.8
167.5°	2322.1	2315.7	2315.7	2330.1	2320.0
170°	2348.1	2342.3	2340.1	2354.6	2342.3
172.5°	2366.1	2360.3	2358.1	2372.5	2360.3
175°	2380.4	2374.6	2370.3	2384.7	2372.5
177.5°	2388.3	2382.6	2378.2	2390.5	2378.2
180°	2384.7	2384.7	2384.7	2384.7	2384.7



TEST NUMBER: P902586  
 CATALOG NUMBER: DFN2DIP-HX3F0-050D080US830-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.97	9.76	10.00	10.80	12.19	8.54	9.33	9.57	10.37	11.76
	3H	10.62	11.33	11.66	12.37	13.78	10.15	10.86	11.19	11.90	13.31
	4H	11.20	11.87	12.25	12.92	14.33	10.73	11.40	11.78	12.45	13.86
	6H	11.59	12.20	12.65	13.26	14.69	11.12	11.73	12.18	12.79	14.22
	8H	11.69	12.27	12.75	13.34	14.77	11.22	11.81	12.28	12.87	14.30
	12H	11.73	12.29	12.80	13.35	14.80	11.26	11.81	12.33	12.87	14.32
4H	2H	9.42	10.09	10.48	11.14	12.56	9.08	9.75	10.14	10.80	12.21
	3H	11.27	11.83	12.34	12.91	14.34	10.88	11.44	11.95	12.52	13.95
	4H	11.98	12.49	13.05	13.56	15.01	11.58	12.09	12.65	13.15	14.61
	6H	12.48	12.92	13.56	14.01	15.46	12.08	12.52	13.16	13.61	15.05
	8H	12.63	13.04	13.71	14.12	15.58	12.22	12.63	13.30	13.71	15.17
	12H	12.69	13.06	13.79	14.16	15.63	12.27	12.65	13.37	13.74	15.21
8H	4H	12.16	12.58	13.25	13.66	15.12	11.81	12.22	12.89	13.30	14.76
	6H	12.78	13.12	13.89	14.25	15.71	12.42	12.76	13.53	13.89	15.35
	8H	13.00	13.30	14.11	14.40	15.88	12.63	12.93	13.74	14.04	15.52
	12H	13.12	13.38	14.24	14.49	16.00	12.74	13.00	13.86	14.11	15.62
12H	4H	12.15	12.52	13.24	13.61	15.08	11.80	12.17	12.90	13.26	14.73
	6H	12.81	13.11	13.92	14.22	15.70	12.46	12.76	13.57	13.87	15.35
	8H	13.04	13.31	14.16	14.41	15.93	12.69	12.95	13.80	14.05	15.57