

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918660

Luminaire Tested: DFN2DIP-4P4F0-030D070US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918660
REPORT IS A COMBINATION OF REPORTS P899128 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-030D070US935-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7529.4 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918660

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918660

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	32	32
2	85	78	72	68	76	70	66	61	56	52	49	42	40	38	29	28	27
3	78	69	62	57	70	62	56	52	49	45	42	37	35	32	26	25	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	24	22	20
5	65	54	47	41	59	49	43	38	39	35	31	30	27	24	21	19	18
6	60	49	41	36	54	44	38	33	35	31	27	27	24	21	20	17	16
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14
8	52	40	33	27	46	36	30	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	693	693	693
5°	694	682	686
10°	687	669	664
15°	678	647	630
20°	665	616	588
25°	652	583	547
30°	635	548	495
35°	618	510	450
40°	601	471	398
45°	581	428	350
50°	561	385	304
55°	539	338	260
60°	515	290	214
65°	486	240	193
70°	452	194	175
75°	408	172	160
80°	345	145	139
85°	241	98	106

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1443 cd/sqm

TEST NUMBER: P918660

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	1.3
10°-20°	274.7	3.6
20°-30°	385.6	5.1
30°-40°	420.3	5.6
40°-50°	386.3	5.1
50°-60°	303.4	4.0
60°-70°	197.5	2.6
70°-80°	101.7	1.4
80°-90°	31.4	0.4
90°-100°	117.9	1.6
100°-110°	374.8	5.0
110°-120°	641.3	8.5
120°-130°	843.5	11.2
130°-140°	946.7	12.6
140°-150°	928.4	12.3
150°-160°	778.8	10.3
160°-170°	516.5	6.9
170°-180°	180.5	2.4
0°-30°	760.3	10.1
0°-40°	1180.7	15.7
0°-60°	1870.4	24.8
0°-90°	2200.9	29.2
90°-120°	1134.1	15.1
90°-150°	3852.7	51.2
90°-180°	5328.0	70.8
0°-180°	7529.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1068	1063	1050	1059	1056	101
15°	1015	1005	972	954	944	286
25°	922	891	827	787	773	424
35°	794	745	660	599	578	497
45°	649	584	483	414	391	501
55°	494	418	314	256	238	441
65°	333	255	168	135	132	330
75°	178	110	77	70	70	188
85°	42	21	18	18	18	48
90°	2	21	56	53	55	7
95°	84	100	103	103	100	93
105°	346	350	354	357	357	365
115°	644	653	650	648	644	637
125°	936	950	946	941	939	837
135°	1211	1229	1232	1230	1226	936
145°	1470	1481	1491	1492	1486	918
155°	1681	1685	1691	1699	1694	774
165°	1828	1827	1827	1838	1830	516
175°	1903	1898	1895	1906	1896	181
180°	1906	1906	1906	1906	1906	

TEST NUMBER: P918660

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.6	1067.6	1067.6	1067.6	1067.6
2.5°	1072.4	1067.6	1056.9	1066.6	1064.7
5°	1067.6	1062.7	1050.2	1058.9	1055.9
7.5°	1058.9	1053.1	1039.6	1043.4	1038.5
10°	1047.2	1040.5	1021.2	1018.2	1012.5
12.5°	1032.8	1024.1	998.0	992.2	981.5
15°	1015.4	1004.7	971.9	953.6	943.9
17.5°	995.1	979.6	939.0	917.8	902.3
20°	971.9	952.5	904.2	880.2	858.8
22.5°	946.8	924.5	868.5	835.7	821.2
25°	921.7	890.7	827.0	787.4	772.8
27.5°	891.7	858.8	788.3	743.0	720.7
30°	859.9	823.1	745.8	696.6	670.5
32.5°	828.9	784.5	705.3	647.3	623.1
35°	794.2	744.8	659.9	599.0	577.7
37.5°	760.3	707.1	617.3	550.6	526.6
40°	724.6	666.7	572.9	504.3	479.2
42.5°	687.9	626.1	528.5	456.9	432.8
45°	649.3	584.4	483.1	414.4	391.2
47.5°	612.5	544.0	439.6	370.9	349.7
50°	572.0	503.3	397.1	330.4	310.1
52.5°	532.3	459.9	356.5	292.7	274.4
55°	493.6	418.3	313.9	256.1	237.7
57.5°	454.1	376.8	276.4	222.2	206.7
60°	413.5	336.2	236.7	187.4	172.0
62.5°	373.9	296.6	202.9	156.5	148.9
65°	333.3	255.0	168.1	135.3	132.3
67.5°	294.7	216.4	135.3	118.8	115.9
70°	254.1	178.7	112.0	102.4	98.5
72.5°	215.4	143.9	93.7	86.0	84.0
75°	177.7	110.1	77.3	70.5	69.6
77.5°	140.1	78.2	60.9	57.0	55.0
80°	105.3	56.1	46.3	42.5	42.5
82.5°	73.4	37.7	31.9	30.0	30.0
85°	41.5	21.2	18.3	18.3	18.3
87.5°	15.5	7.7	7.7	6.8	6.8
90°	1.7	20.7	56.3	52.9	54.6
92.5°	35.6	48.3	50.0	51.7	51.7
95°	83.9	100.0	102.9	102.9	100.0
97.5°	139.7	154.5	160.9	160.9	160.9
100°	204.0	217.2	221.8	221.8	220.1
102.5°	271.8	281.5	287.9	289.6	287.9
105°	345.9	350.5	354.0	356.9	356.9
107.5°	419.5	426.4	426.4	427.6	419.5
110°	490.8	500.0	500.0	500.0	495.3



TEST NUMBER: P918660

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	567.7	577.6	575.8	571.2	567.7
115°	643.6	652.8	650.0	648.2	643.6
117.5°	718.8	731.5	723.5	718.8	714.3
120°	794.7	807.4	794.7	794.7	789.5
122.5°	863.7	879.8	871.8	867.1	863.7
125°	936.1	950.5	945.9	940.7	939.0
127.5°	1006.8	1024.6	1018.3	1011.4	1006.8
130°	1072.9	1093.6	1090.7	1087.3	1080.9
132.5°	1147.0	1163.1	1164.2	1156.2	1151.6
135°	1210.8	1228.6	1232.1	1230.3	1225.7
137.5°	1282.0	1296.4	1299.2	1298.1	1291.2
140°	1344.7	1359.1	1367.1	1367.1	1360.8
142.5°	1409.0	1423.4	1428.0	1429.7	1423.4
145°	1470.0	1481.4	1490.6	1492.4	1486.1
147.5°	1524.6	1538.9	1545.8	1548.7	1542.4
150°	1580.9	1590.6	1597.0	1602.1	1597.0
152.5°	1630.8	1640.6	1648.6	1655.0	1648.6
155°	1680.8	1685.4	1690.7	1698.7	1693.5
157.5°	1724.0	1727.4	1730.3	1741.8	1733.7
160°	1762.5	1765.9	1767.6	1777.4	1770.5
162.5°	1798.1	1798.1	1799.8	1810.7	1802.7
165°	1828.5	1826.8	1826.8	1838.3	1830.2
167.5°	1856.1	1851.0	1851.0	1862.4	1854.4
170°	1876.8	1872.2	1870.5	1882.0	1872.2
172.5°	1891.2	1886.5	1884.8	1896.3	1886.5
175°	1902.6	1898.1	1894.6	1906.1	1896.3
177.5°	1909.0	1904.4	1900.9	1910.7	1900.9
180°	1906.1	1906.1	1906.1	1906.1	1906.1

TEST NUMBER: P918660

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.55	4.23	4.67	5.34	6.89	0.00	0.19	0.63	1.30	2.85
	3H	5.22	5.83	6.35	6.95	8.51	0.69	1.30	1.82	2.42	3.98
	4H	5.82	6.41	6.96	7.53	9.09	1.13	1.71	2.27	2.83	4.40
	6H	6.24	6.78	7.39	7.90	9.48	1.45	1.98	2.59	3.10	4.68
	8H	6.37	6.88	7.52	8.02	9.58	1.53	2.04	2.68	3.18	4.75
	12H	6.43	6.91	7.58	8.04	9.63	1.57	2.06	2.73	3.19	4.78
4H	2H	3.55	4.13	4.70	5.25	6.81	0.09	0.67	1.24	1.79	3.35
	3H	5.37	5.85	6.52	7.00	8.58	1.43	1.91	2.58	3.06	4.63
	4H	6.06	6.51	7.22	7.64	9.24	1.97	2.42	3.13	3.55	5.15
	6H	6.57	6.95	7.73	8.11	9.70	2.38	2.76	3.54	3.92	5.51
	8H	6.75	7.10	7.91	8.25	9.86	2.51	2.87	3.67	4.02	5.62
	12H	6.84	7.16	8.02	8.32	9.93	2.57	2.89	3.75	4.05	5.66
8H	4H	6.02	6.37	7.18	7.52	9.13	2.24	2.60	3.40	3.75	5.35
	6H	6.59	6.88	7.76	8.07	9.67	2.76	3.05	3.94	4.24	5.84
	8H	6.81	7.06	7.99	8.23	9.85	2.95	3.21	4.14	4.38	6.00
	12H	6.94	7.17	8.13	8.33	9.99	3.07	3.29	4.25	4.46	6.11
12H	4H	5.96	6.29	7.14	7.45	9.05	2.24	2.56	3.42	3.73	5.33
	6H	6.56	6.82	7.74	7.99	9.61	2.81	3.06	3.99	4.24	5.85
	8H	6.78	7.00	7.97	8.17	9.82	3.02	3.24	4.20	4.41	6.06

END OF REPORT