

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918695

Luminaire Tested: DFN2DIP-4P4F0-050D040US935-FLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918695
REPORT IS A COMBINATION OF REPORTS P900615 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-050D040US935-FLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7671.5 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 80.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918695
CATALOG NUMBER: DFN2DIP-4P4F0-050D040US935-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P918695
 CATALOG NUMBER: DFN2DIP-4P4F0-050D040US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	54	53	52	47
2	90	83	76	71	84	77	72	67	66	62	59	57	54	51	48	46	44	39
3	82	73	65	59	76	68	61	56	59	54	50	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	48	52	47	42	45	40	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1087	1087	1087
5°	1089	1072	1079
10°	1080	1058	1065
15°	1064	1041	1043
20°	1043	1017	1020
25°	1021	988	993
30°	995	962	959
35°	969	930	923
40°	938	899	889
45°	907	867	854
50°	873	834	813
55°	838	795	776
60°	798	749	734
65°	754	702	683
70°	698	644	630
75°	621	575	581
80°	529	488	486
85°	384	335	328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 907 cd/sqm



TEST NUMBER: P918695

CATALOG NUMBER: DFN2DIP-4P4F0-050D040US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.1
10°-20°	443.6	5.8
20°-30°	651.9	8.5
30°-40°	757.2	9.9
40°-50°	756.2	9.9
50°-60°	659.4	8.6
60°-70°	487.4	6.4
70°-80°	275.8	3.6
80°-90°	74.8	1.0
90°-100°	38.3	0.5
100°-110°	142.9	1.9
110°-120°	378.9	4.9
120°-130°	628.5	8.2
130°-140°	667.6	8.7
140°-150°	620.4	8.1
150°-160°	498.8	6.5
160°-170°	321.4	4.2
170°-180°	110.6	1.4
0°-30°	1253.2	16.3
0°-40°	2010.3	26.2
0°-60°	3425.9	44.7
0°-90°	4264.0	55.6
90°-120°	560.1	7.3
90°-150°	2476.6	32.3
90°-180°	3407.0	44.4
0°-180°	7671.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1651	1664	1661	159
15°	1595	1585	1564	1570	1562	449
25°	1443	1430	1403	1406	1403	664
35°	1245	1229	1203	1194	1186	778
45°	1013	1002	978	960	954	782
55°	767	757	738	718	710	686
65°	517	507	491	477	469	511
75°	270	267	259	250	253	289
85°	66	64	63	58	56	74
90°	1	10	17	21	23	7
95°	55	27	33	37	36	65
105°	256	281	51	60	64	273
115°	484	498	519	130	69	476
125°	684	695	711	717	719	610
135°	846	860	867	876	874	654
145°	982	981	995	1001	997	614
155°	1081	1073	1083	1088	1082	498
165°	1139	1134	1136	1142	1136	322
175°	1165	1159	1161	1166	1158	111
180°	1162	1162	1162	1162	1162	



TEST NUMBER: P918695

CATALOG NUMBER: DFN2DIP-4P4F0-050D040US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.1	1675.1	1675.1	1675.1	1675.1
2.5°	1684.8	1676.8	1659.1	1675.1	1672.1
5°	1675.1	1668.8	1651.0	1663.8	1660.8
7.5°	1663.8	1654.2	1636.5	1649.5	1646.2
10°	1646.2	1634.9	1615.7	1628.4	1623.7
12.5°	1621.9	1612.4	1593.1	1601.1	1597.8
15°	1594.6	1585.0	1564.0	1570.5	1562.5
17.5°	1560.7	1551.2	1530.2	1538.2	1530.2
20°	1523.7	1514.2	1491.6	1496.3	1490.0
22.5°	1486.8	1472.2	1451.2	1451.2	1447.9
25°	1443.2	1430.4	1403.0	1406.1	1403.0
27.5°	1394.8	1383.5	1362.7	1357.9	1349.9
30°	1346.6	1333.7	1309.6	1304.8	1298.3
32.5°	1295.0	1285.5	1259.6	1249.9	1243.5
35°	1245.1	1229.1	1203.2	1193.5	1185.5
37.5°	1188.7	1174.2	1148.4	1137.1	1129.1
40°	1130.8	1117.8	1092.0	1077.6	1071.2
42.5°	1074.4	1061.4	1035.8	1019.5	1010.0
45°	1013.2	1001.9	977.7	960.1	953.6
47.5°	953.6	942.3	916.5	898.7	889.2
50°	890.7	882.7	860.1	837.6	829.5
52.5°	829.5	818.2	797.4	779.6	768.4
55°	766.8	757.1	737.7	718.4	710.4
57.5°	703.9	695.9	674.9	655.6	649.0
60°	641.0	634.7	612.2	594.3	589.6
62.5°	579.9	568.6	552.5	536.4	529.9
65°	517.1	507.4	491.3	476.8	468.7
67.5°	452.7	444.5	430.2	418.9	412.3
70°	393.0	386.6	372.0	360.8	354.5
72.5°	331.9	325.4	317.4	306.1	301.3
75°	270.5	267.4	259.2	249.7	253.0
77.5°	215.9	209.3	206.1	201.3	196.6
80°	161.2	159.5	156.2	151.4	148.2
82.5°	109.5	109.5	108.0	101.5	101.5
85°	66.0	64.4	62.9	57.9	56.4
87.5°	29.0	25.8	22.6	17.7	16.1
90°	0.8	10.1	16.8	21.1	22.6
92.5°	21.1	17.7	20.1	21.9	22.6
95°	54.6	26.9	32.7	37.0	36.2
97.5°	98.4	29.4	42.9	45.5	46.2
100°	148.9	33.7	48.0	54.6	56.3
102.5°	204.3	202.8	49.6	58.8	61.4
105°	255.6	280.9	51.3	60.5	63.9
107.5°	315.4	336.4	53.0	62.3	65.6
110°	372.6	390.2	147.2	63.1	66.4



TEST NUMBER: P918695

CATALOG NUMBER: DFN2DIP-4P4F0-050D040US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	426.5	441.5	427.2	64.7	67.3
115°	483.5	497.8	518.9	129.5	69.1
117.5°	533.2	550.0	564.4	444.0	223.7
120°	588.8	601.3	616.5	626.6	513.1
122.5°	635.8	649.3	666.2	671.1	672.0
125°	683.7	694.7	710.7	716.6	719.1
127.5°	727.5	739.3	751.9	760.3	761.1
130°	768.7	782.2	791.3	800.6	799.9
132.5°	810.7	821.7	830.9	838.5	837.8
135°	846.1	859.6	867.1	875.5	873.9
137.5°	883.0	893.1	901.6	910.0	907.5
140°	919.2	926.0	935.2	942.8	938.6
142.5°	949.6	955.4	966.4	973.0	968.9
145°	981.5	980.7	994.9	1000.8	996.6
147.5°	1009.2	1006.7	1021.0	1025.2	1021.9
150°	1036.1	1030.3	1043.8	1048.8	1044.6
152.5°	1058.9	1052.1	1064.7	1069.8	1063.9
155°	1080.7	1073.2	1083.3	1088.3	1081.6
157.5°	1098.4	1091.7	1099.3	1105.2	1098.4
160°	1113.5	1108.4	1113.5	1118.5	1112.7
162.5°	1127.0	1122.0	1126.2	1132.0	1124.5
165°	1138.8	1133.8	1136.3	1142.1	1136.3
167.5°	1148.1	1142.9	1145.6	1151.4	1143.8
170°	1155.6	1150.6	1152.2	1158.1	1150.6
172.5°	1160.6	1155.6	1157.4	1163.2	1155.6
175°	1164.8	1158.9	1160.6	1166.5	1158.1
177.5°	1166.5	1160.6	1161.5	1167.4	1159.9
180°	1162.3	1162.3	1162.3	1162.3	1162.3



TEST NUMBER: P918695
 CATALOG NUMBER: DFN2DIP-4P4F0-050D040US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.08	8.99	8.99	9.92	11.11	7.64	8.55	8.54	9.48	10.67
	3H	9.75	10.57	10.67	11.51	12.72	9.26	10.08	10.18	11.02	12.23
	4H	10.34	11.12	11.28	12.06	13.28	9.85	10.63	10.78	11.57	12.79
	6H	10.75	11.47	11.70	12.41	13.65	10.25	10.97	11.20	11.91	13.15
	8H	10.86	11.54	11.81	12.51	13.74	10.36	11.04	11.31	12.00	13.24
	12H	10.91	11.56	11.87	12.52	13.78	10.40	11.05	11.36	12.01	13.27
4H	2H	8.55	9.32	9.49	10.27	11.49	8.19	8.97	9.13	9.91	11.13
	3H	10.43	11.07	11.38	12.04	13.28	10.02	10.67	10.97	11.64	12.87
	4H	11.15	11.74	12.11	12.70	13.97	10.72	11.31	11.68	12.28	13.54
	6H	11.67	12.18	12.64	13.17	14.43	11.24	11.75	12.21	12.74	14.00
	8H	11.82	12.30	12.80	13.28	14.56	11.39	11.86	12.36	12.85	14.12
	12H	11.90	12.33	12.90	13.33	14.61	11.45	11.88	12.45	12.88	14.16
8H	4H	11.35	11.82	12.32	12.81	14.08	10.97	11.45	11.95	12.43	13.71
	6H	11.99	12.38	12.99	13.41	14.68	11.61	12.00	12.61	13.02	14.30
	8H	12.21	12.56	13.22	13.57	14.87	11.82	12.17	12.83	13.18	14.47
	12H	12.35	12.66	13.36	13.66	15.00	11.94	12.25	12.95	13.25	14.59
12H	4H	11.34	11.77	12.33	12.77	14.05	10.97	11.40	11.96	12.40	13.68
	6H	12.02	12.37	13.03	13.38	14.67	11.65	12.00	12.66	13.01	14.30
	8H	12.27	12.57	13.28	13.58	14.92	11.89	12.19	12.90	13.20	14.54