

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902684

Luminaire Tested: DFN2DIP-HX3F0-090D090US830-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P902684  
REPORT IS A COMBINATION OF REPORTS P899297 AND P896089  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-090D090US830-FLLFLL  
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15905.4 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 163.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P902684  
CATALOG NUMBER: DFN2DIP-HX3F0-090D090US830-FLLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P902684

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US830-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3823	3823	3823
5°	3828	3768	3793
10°	3795	3714	3740
15°	3738	3650	3658
20°	3660	3563	3573
25°	3584	3459	3476
30°	3488	3361	3353
35°	3397	3247	3224
40°	3285	3131	3100
45°	3174	3016	2973
50°	3052	2894	2827
55°	2924	2753	2692
60°	2779	2586	2537
65°	2621	2413	2354
70°	2420	2202	2156
75°	2142	1948	1971
80°	1805	1624	1623
85°	1281	1075	1052

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3174 cd/sqm



TEST NUMBER: P902684

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US830-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	310.7	2.0
10°-20°	874.1	5.5
20°-30°	1284.6	8.1
30°-40°	1492.0	9.4
40°-50°	1490.1	9.4
50°-60°	1299.3	8.2
60°-70°	960.5	6.0
70°-80°	543.4	3.4
80°-90°	151.0	0.9
90°-100°	166.0	1.0
100°-110°	527.5	3.3
110°-120°	902.7	5.7
120°-130°	1187.2	7.5
130°-140°	1332.5	8.4
140°-150°	1306.7	8.2
150°-160°	1096.1	6.9
160°-170°	726.9	4.6
170°-180°	254.1	1.6
0°-30°	2469.3	15.5
0°-40°	3961.3	24.9
0°-60°	6750.7	42.4
0°-90°	8405.7	52.8
90°-120°	1596.2	10.0
90°-150°	5422.6	34.1
90°-180°	7500.0	47.2
0°-180°	15905.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3301	3301	3301	3301	3301	
5°	3301	3288	3253	3278	3272	313
15°	3142	3123	3082	3095	3079	885
25°	2844	2818	2765	2771	2765	1309
35°	2454	2422	2371	2352	2336	1532
45°	1996	1974	1926	1892	1879	1541
55°	1511	1492	1454	1416	1400	1351
65°	1019	1000	968	940	924	1007
75°	533	527	511	492	498	569
85°	130	127	124	114	111	145
90°	2	29	79	74	77	15
95°	118	141	145	145	141	131
105°	487	493	498	502	502	514
115°	906	919	915	912	906	896
125°	1318	1338	1331	1324	1322	1177
135°	1704	1729	1734	1732	1725	1317
145°	2069	2085	2098	2100	2092	1293
155°	2366	2372	2380	2391	2384	1089
165°	2574	2571	2571	2587	2576	726
175°	2678	2671	2667	2683	2669	254
180°	2683	2683	2683	2683	2683	



TEST NUMBER: P902684

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US830-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3300.7	3300.7	3300.7	3300.7	3300.7
2.5°	3319.9	3304.1	3269.1	3300.7	3294.7
5°	3300.7	3288.2	3253.3	3278.5	3272.4
7.5°	3278.5	3259.7	3224.6	3250.3	3243.9
10°	3243.9	3221.6	3183.5	3208.8	3199.4
12.5°	3196.0	3177.1	3139.1	3154.9	3148.6
15°	3142.2	3123.3	3081.8	3094.6	3078.8
17.5°	3075.4	3056.6	3015.2	3031.0	3015.2
20°	3002.4	2983.5	2939.0	2948.5	2936.0
22.5°	2929.6	2901.1	2859.6	2859.6	2853.2
25°	2843.7	2818.5	2764.7	2770.7	2764.7
27.5°	2748.5	2726.2	2685.2	2675.8	2659.9
30°	2653.5	2627.9	2580.4	2571.0	2558.2
32.5°	2551.8	2533.0	2482.1	2463.0	2450.1
35°	2453.5	2421.9	2371.0	2351.8	2336.0
37.5°	2342.4	2313.8	2262.9	2240.7	2224.9
40°	2228.2	2202.6	2151.7	2123.5	2110.7
42.5°	2117.0	2091.5	2041.0	2009.0	1990.2
45°	1996.5	1974.3	1926.5	1891.8	1879.1
47.5°	1879.1	1856.8	1805.9	1770.9	1752.1
50°	1755.1	1739.3	1694.8	1650.4	1634.6
52.5°	1634.6	1612.3	1571.2	1536.2	1514.0
55°	1511.0	1491.8	1453.7	1415.7	1399.9
57.5°	1387.0	1371.2	1329.8	1291.8	1278.9
60°	1263.1	1250.7	1206.2	1171.2	1161.8
62.5°	1142.5	1120.3	1088.6	1057.1	1044.2
65°	1019.0	999.8	968.1	939.5	923.7
67.5°	892.0	875.9	847.5	825.4	812.6
70°	774.5	761.7	733.1	710.9	698.4
72.5°	653.9	641.1	625.3	603.1	593.7
75°	533.1	527.0	510.9	492.0	498.4
77.5°	425.3	412.6	406.1	396.7	387.3
80°	317.5	314.1	307.7	298.3	292.0
82.5°	215.8	215.8	212.8	200.0	200.0
85°	130.0	127.0	123.9	114.1	111.1
87.5°	57.2	50.8	44.5	35.1	31.7
90°	2.5	29.1	79.3	74.4	76.8
92.5°	50.1	68.0	70.4	72.8	72.8
95°	118.1	140.7	144.8	144.8	140.7
97.5°	196.5	217.5	226.5	226.5	226.5
100°	287.1	305.8	312.2	312.2	309.8
102.5°	382.6	396.3	405.2	407.6	405.2
105°	486.9	493.3	498.2	502.3	502.3
107.5°	590.4	600.1	600.1	601.7	590.4
110°	690.7	703.7	703.7	703.7	697.2



TEST NUMBER: P902684

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US830-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	799.1	812.8	810.4	804.0	799.1
115°	905.9	918.8	914.7	912.4	905.9
117.5°	1011.8	1029.6	1018.3	1011.8	1005.3
120°	1118.6	1136.3	1118.6	1118.6	1111.3
122.5°	1215.6	1238.3	1227.0	1220.5	1215.6
125°	1317.6	1337.8	1331.3	1324.0	1321.6
127.5°	1417.0	1442.1	1433.2	1423.5	1417.0
130°	1510.0	1539.2	1535.1	1530.2	1521.4
132.5°	1614.4	1637.0	1638.6	1627.3	1620.9
135°	1704.1	1729.2	1734.1	1731.6	1725.2
137.5°	1804.4	1824.7	1828.7	1827.1	1817.4
140°	1892.6	1912.8	1924.1	1924.1	1915.2
142.5°	1983.2	2003.4	2009.9	2012.3	2003.4
145°	2069.0	2085.1	2098.0	2100.5	2091.6
147.5°	2145.8	2166.0	2175.7	2179.7	2170.9
150°	2225.1	2238.8	2247.7	2254.9	2247.7
152.5°	2295.4	2309.1	2320.4	2329.4	2320.4
155°	2365.8	2372.2	2379.5	2390.9	2383.6
157.5°	2426.4	2431.3	2435.3	2451.5	2440.1
160°	2480.6	2485.5	2487.9	2501.6	2491.9
162.5°	2530.7	2530.7	2533.2	2548.5	2537.2
165°	2573.6	2571.2	2571.2	2587.4	2576.1
167.5°	2612.4	2605.2	2605.2	2621.3	2610.0
170°	2641.6	2635.1	2632.7	2648.8	2635.1
172.5°	2661.7	2655.3	2652.9	2669.1	2655.3
175°	2678.0	2671.4	2666.6	2682.9	2669.1
177.5°	2686.8	2680.4	2675.5	2689.3	2675.5
180°	2682.9	2682.9	2682.9	2682.9	2682.9



TEST NUMBER: P902684  
 CATALOG NUMBER: DFN2DIP-HX3F0-090D090US830-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.15	13.03	13.08	13.98	15.21	11.72	12.61	12.65	13.55	14.78
	3H	13.80	14.60	14.74	15.56	16.81	13.33	14.13	14.28	15.09	16.34
	4H	14.38	15.14	15.34	16.10	17.36	13.92	14.67	14.87	15.63	16.89
	6H	14.78	15.47	15.75	16.44	17.72	14.31	15.00	15.28	15.97	17.25
	8H	14.88	15.54	15.86	16.53	17.80	14.41	15.07	15.39	16.06	17.33
	12H	14.93	15.56	15.91	16.54	17.83	14.45	15.08	15.44	16.06	17.36
4H	2H	12.61	13.36	13.57	14.33	15.59	12.27	13.02	13.23	13.98	15.24
	3H	14.47	15.10	15.44	16.09	17.37	14.08	14.71	15.05	15.70	16.98
	4H	15.18	15.75	16.16	16.74	18.04	14.78	15.35	15.76	16.34	17.64
	6H	15.69	16.18	16.68	17.19	18.49	15.28	15.78	16.28	16.79	18.09
	8H	15.83	16.30	16.83	17.30	18.61	15.43	15.89	16.42	16.89	18.21
	12H	15.90	16.32	16.92	17.34	18.66	15.49	15.91	16.50	16.92	18.24
8H	4H	15.37	15.84	16.37	16.84	18.15	15.02	15.48	16.01	16.48	17.79
	6H	16.00	16.38	17.02	17.42	18.73	15.64	16.02	16.66	17.06	18.38
	8H	16.21	16.55	17.24	17.58	18.91	15.85	16.18	16.88	17.22	18.55
	12H	16.34	16.64	17.37	17.66	19.04	15.96	16.26	16.99	17.28	18.66
12H	4H	15.36	15.78	16.37	16.80	18.11	15.01	15.43	16.02	16.45	17.77
	6H	16.02	16.36	17.05	17.39	18.72	15.68	16.01	16.71	17.05	18.38
	8H	16.26	16.56	17.29	17.58	18.96	15.91	16.21	16.94	17.23	18.61