

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905264

Luminaire Tested: DFN2DIP-HX3F0-030D070US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905264
REPORT IS A COMBINATION OF REPORTS P899258 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-030D070US835-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8745.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 77.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905264

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905264

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	32	32
2	85	78	72	68	76	70	66	61	56	52	49	42	40	38	29	28	27
3	78	69	62	57	70	62	56	52	49	45	42	37	35	32	26	25	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	24	22	20
5	65	54	47	41	59	49	43	38	39	35	31	30	27	24	21	19	18
6	60	49	41	36	54	44	38	33	35	31	27	27	24	21	20	17	16
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14
8	52	40	33	27	46	36	30	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1436	1436	1436
5°	1438	1412	1422
10°	1423	1384	1375
15°	1403	1337	1302
20°	1376	1273	1214
25°	1349	1202	1129
30°	1313	1128	1021
35°	1277	1050	926
40°	1241	968	817
45°	1199	878	719
50°	1155	787	623
55°	1109	690	531
60°	1057	589	436
65°	996	486	392
70°	922	391	353
75°	829	342	320
80°	695	284	275
85°	475	185	202

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2083 cd/sqm

TEST NUMBER: P905264

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	1.3
10°-20°	319.0	3.6
20°-30°	447.9	5.1
30°-40°	488.2	5.6
40°-50°	448.7	5.1
50°-60°	352.4	4.0
60°-70°	229.4	2.6
70°-80°	118.1	1.4
80°-90°	36.4	0.4
90°-100°	137.0	1.6
100°-110°	435.3	5.0
110°-120°	744.9	8.5
120°-130°	979.6	11.2
130°-140°	1099.6	12.6
140°-150°	1078.3	12.3
150°-160°	904.5	10.3
160°-170°	599.9	6.9
170°-180°	209.7	2.4
0°-30°	883.1	10.1
0°-40°	1371.3	15.7
0°-60°	2172.4	24.8
0°-90°	2556.3	29.2
90°-120°	1317.2	15.1
90°-150°	4474.7	51.2
90°-180°	6189.0	70.8
0°-180°	8745.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	2	24	65	61	63	9
95°	97	116	120	120	116	108
105°	402	407	411	414	414	424
115°	748	758	755	753	748	739
125°	1087	1104	1099	1093	1091	972
135°	1406	1427	1431	1429	1424	1087
145°	1707	1721	1731	1733	1726	1067
155°	1952	1958	1964	1973	1967	899
165°	2124	2122	2122	2135	2126	599
175°	2210	2204	2200	2214	2202	210
180°	2214	2214	2214	2214	2214	

TEST NUMBER: P905264

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	2.0	24.0	65.4	61.4	63.4
92.5°	41.4	56.1	58.1	60.1	60.1
95°	97.4	116.1	119.5	119.5	116.1
97.5°	162.2	179.5	186.9	186.9	186.9
100°	236.9	252.3	257.6	257.6	255.6
102.5°	315.7	327.0	334.4	336.4	334.4
105°	401.8	407.1	411.1	414.5	414.5
107.5°	487.2	495.2	495.2	496.6	487.2
110°	570.0	580.7	580.7	580.7	575.3

TEST NUMBER: P905264

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.4	670.8	668.8	663.4	659.4
115°	747.5	758.2	754.9	752.9	747.5
117.5°	834.9	849.6	840.3	834.9	829.6
120°	923.0	937.7	923.0	923.0	917.0
122.5°	1003.1	1021.8	1012.5	1007.1	1003.1
125°	1087.2	1103.9	1098.6	1092.6	1090.6
127.5°	1169.3	1190.0	1182.7	1174.7	1169.3
130°	1246.1	1270.1	1266.8	1262.8	1255.4
132.5°	1332.2	1350.9	1352.2	1342.9	1337.5
135°	1406.3	1426.9	1431.0	1428.9	1423.6
137.5°	1489.0	1505.7	1509.0	1507.7	1499.7
140°	1561.8	1578.5	1587.8	1587.8	1580.5
142.5°	1636.5	1653.2	1658.5	1660.5	1653.2
145°	1707.3	1720.6	1731.3	1733.3	1726.0
147.5°	1770.7	1787.4	1795.4	1798.7	1791.4
150°	1836.1	1847.4	1854.8	1860.8	1854.8
152.5°	1894.1	1905.5	1914.8	1922.2	1914.8
155°	1952.2	1957.5	1963.6	1972.9	1966.9
157.5°	2002.3	2006.3	2009.6	2023.0	2013.6
160°	2047.0	2051.0	2053.0	2064.3	2056.3
162.5°	2088.4	2088.4	2090.4	2103.0	2093.7
165°	2123.7	2121.7	2121.7	2135.1	2125.7
167.5°	2155.8	2149.8	2149.8	2163.1	2153.8
170°	2179.8	2174.5	2172.5	2185.8	2174.5
172.5°	2196.5	2191.1	2189.1	2202.5	2191.1
175°	2209.8	2204.5	2200.5	2213.8	2202.5
177.5°	2217.2	2211.8	2207.8	2219.2	2207.8
180°	2213.8	2213.8	2213.8	2213.8	2213.8

TEST NUMBER: P905264

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US835-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.02	6.70	7.14	7.82	9.36	2.00	2.68	3.12	3.79	5.33
	3H	7.68	8.29	8.81	9.41	10.97	3.17	3.78	4.30	4.90	6.46
	4H	8.27	8.86	9.41	9.98	11.54	3.61	4.19	4.75	5.31	6.87
	6H	8.68	9.22	9.83	10.34	11.91	3.92	4.45	5.07	5.58	7.15
	8H	8.80	9.31	9.95	10.45	12.01	4.00	4.51	5.15	5.65	7.22
	12H	8.85	9.34	10.01	10.47	12.06	4.04	4.52	5.19	5.65	7.24
4H	2H	6.02	6.60	7.16	7.72	9.28	2.57	3.15	3.72	4.27	5.83
	3H	7.83	8.31	8.98	9.46	11.03	3.90	4.38	5.05	5.53	7.11
	4H	8.51	8.95	9.66	10.09	11.68	4.44	4.88	5.59	6.02	7.61
	6H	9.01	9.39	10.17	10.54	12.13	4.84	5.22	6.00	6.38	7.97
	8H	9.17	9.53	10.33	10.68	12.28	4.97	5.32	6.13	6.47	8.08
	12H	9.26	9.58	10.43	10.74	12.35	5.02	5.35	6.20	6.51	8.11
8H	4H	8.46	8.82	9.62	9.97	11.57	4.70	5.06	5.86	6.21	7.81
	6H	9.01	9.31	10.19	10.50	12.10	5.21	5.50	6.39	6.69	8.29
	8H	9.22	9.48	10.41	10.65	12.27	5.40	5.65	6.58	6.82	8.44
	12H	9.35	9.58	10.54	10.74	12.40	5.51	5.73	6.69	6.90	8.55
12H	4H	8.41	8.73	9.58	9.89	11.50	4.70	5.02	5.87	6.18	7.79
	6H	8.99	9.24	10.17	10.41	12.03	5.26	5.51	6.44	6.68	8.30
	8H	9.20	9.42	10.38	10.59	12.24	5.46	5.68	6.64	6.85	8.50

END OF REPORT