

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918717

Luminaire Tested: DFN2DIP-4P4F0-060D030US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918717
REPORT IS A COMBINATION OF REPORTS P900606 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-060D030US935-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6948.3 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918717
CATALOG NUMBER: DFN2DIP-4P4F0-060D030US935-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P918717

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	59	59	59	54
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51	51	51	51	47
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44	44	44	44	40
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38	38	38	38	35
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34	34	34	34	31
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30	30	30	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27	27	27	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	24	24	24	22
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22	22	22	22	20
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1385	1385	1385
5°	1387	1364	1372
10°	1374	1337	1328
15°	1355	1293	1260
20°	1330	1233	1175
25°	1305	1165	1094
30°	1270	1095	990
35°	1237	1020	900
40°	1202	943	795
45°	1163	857	701
50°	1122	770	608
55°	1079	677	519
60°	1029	579	428
65°	972	480	386
70°	903	388	350
75°	816	343	320
80°	690	289	279
85°	482	196	213

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1163 cd/sqm



TEST NUMBER: P918717

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	2.9
10°-20°	549.3	7.9
20°-30°	771.2	11.1
30°-40°	840.7	12.1
40°-50°	772.7	11.1
50°-60°	606.8	8.7
60°-70°	395.0	5.7
70°-80°	203.3	2.9
80°-90°	53.4	0.8
90°-100°	28.7	0.4
100°-110°	107.2	1.5
110°-120°	284.2	4.1
120°-130°	471.3	6.8
130°-140°	500.7	7.2
140°-150°	465.3	6.7
150°-160°	374.1	5.4
160°-170°	241.1	3.5
170°-180°	83.0	1.2
0°-30°	1520.7	21.9
0°-40°	2361.4	34.0
0°-60°	3740.9	53.8
0°-90°	4392.6	63.2
90°-120°	420.1	6.0
90°-150°	1857.5	26.7
90°-180°	2556.0	36.8
0°-180°	6948.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	1	8	13	16	17	7
95°	41	20	24	28	27	49
105°	192	211	38	45	48	205
115°	363	373	389	97	52	357
125°	513	521	533	537	539	457
135°	635	645	650	657	655	490
145°	736	736	746	751	747	460
155°	810	805	812	816	811	373
165°	854	850	852	857	852	241
175°	874	869	870	875	869	83
180°	872	872	872	872	872	



TEST NUMBER: P918717

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.6	7.6	12.6	15.8	17.0
92.5°	15.8	13.3	15.2	16.4	17.0
95°	41.0	20.1	24.5	27.8	27.1
97.5°	73.8	22.1	32.1	34.1	34.7
100°	111.7	25.2	36.0	41.0	42.3
102.5°	153.3	152.1	37.2	44.1	46.1
105°	191.7	210.7	38.5	45.4	48.0
107.5°	236.5	252.3	39.8	46.7	49.2
110°	279.5	292.7	110.4	47.4	49.9



TEST NUMBER: P918717

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	319.9	331.1	320.5	48.6	50.5
115°	362.7	373.4	389.2	97.1	51.7
117.5°	399.9	412.5	423.3	333.0	167.8
120°	441.5	451.0	462.4	469.9	384.8
122.5°	476.8	487.0	499.6	503.3	504.0
125°	512.8	521.0	533.0	537.4	539.3
127.5°	545.6	554.4	564.0	570.2	570.8
130°	576.5	586.7	593.6	600.5	599.9
132.5°	608.0	616.3	623.2	628.9	628.3
135°	634.6	644.7	650.3	656.7	655.4
137.5°	662.3	669.9	676.2	682.5	680.6
140°	689.4	694.5	701.4	707.1	704.0
142.5°	712.2	716.6	724.8	729.8	726.7
145°	736.2	735.5	746.2	750.6	747.4
147.5°	756.9	755.0	765.8	768.9	766.4
150°	777.1	772.7	782.8	786.5	783.4
152.5°	794.1	789.1	798.6	802.4	798.0
155°	810.5	804.9	812.4	816.2	811.2
157.5°	823.8	818.8	824.5	828.9	823.8
160°	835.2	831.4	835.2	839.0	834.5
162.5°	845.2	841.5	844.6	849.0	843.3
165°	854.0	850.3	852.2	856.6	852.2
167.5°	861.0	857.2	859.1	863.6	857.9
170°	866.7	862.9	864.2	868.6	862.9
172.5°	870.5	866.7	868.0	872.4	866.7
175°	873.6	869.2	870.5	874.9	868.6
177.5°	874.9	870.5	871.2	875.5	869.9
180°	871.8	871.8	871.8	871.8	871.8



TEST NUMBER: P918717
 CATALOG NUMBER: DFN2DIP-4P4F0-060D030US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.45	10.40	10.29	11.26	12.33	5.41	6.36	6.25	7.22	8.29
	3H	11.14	11.99	12.00	12.86	13.96	6.61	7.46	7.47	8.33	9.43
	4H	11.76	12.56	12.63	13.44	14.55	7.07	7.87	7.94	8.74	9.86
	6H	12.19	12.93	13.08	13.81	14.94	7.40	8.14	8.28	9.02	10.14
	8H	12.33	13.03	13.22	13.93	15.05	7.49	8.19	8.38	9.09	10.22
	12H	12.39	13.06	13.29	13.96	15.10	7.54	8.21	8.44	9.10	10.25
4H	2H	9.48	10.29	10.36	11.16	12.27	6.02	6.83	6.90	7.70	8.81
	3H	11.33	12.00	12.22	12.90	14.03	7.39	8.05	8.27	8.96	10.09
	4H	12.03	12.64	12.93	13.54	14.69	7.94	8.55	8.84	9.45	10.60
	6H	12.56	13.08	13.47	14.01	15.16	8.37	8.89	9.28	9.82	10.97
	8H	12.74	13.23	13.65	14.15	15.32	8.50	8.99	9.42	9.91	11.08
	12H	12.84	13.28	13.78	14.22	15.39	8.57	9.01	9.51	9.95	11.12
8H	4H	12.01	12.50	12.92	13.42	14.58	8.23	8.72	9.15	9.64	10.81
	6H	12.58	12.99	13.53	13.95	15.12	8.76	9.16	9.70	10.13	11.29
	8H	12.81	13.16	13.76	14.12	15.30	8.95	9.31	9.90	10.26	11.45
	12H	12.95	13.27	13.91	14.21	15.45	9.08	9.39	10.03	10.34	11.57
12H	4H	11.97	12.40	12.90	13.34	14.52	8.25	8.68	9.18	9.62	10.80
	6H	12.56	12.92	13.51	13.87	15.06	8.81	9.17	9.76	10.12	11.31
	8H	12.79	13.10	13.74	14.05	15.29	9.03	9.34	9.98	10.29	11.52