

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918747

Luminaire Tested: DFN2DIP-4P4F0-070D050US935-FLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P918747  
REPORT IS A COMBINATION OF REPORTS P900631 AND P897523  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P4F0-070D050US935-FLLONL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10228.7 lumens  
Efficiency: N/A  
Efficacy: 89.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 114.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P918747  
CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P918747  
 CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58			58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49			49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	47	45	41			41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39	35			35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30			30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29	26			26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23			23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20			20
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	18			18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16			16
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	19	17	15			15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1521	1521	1521
5°	1524	1501	1511
10°	1512	1481	1491
15°	1490	1457	1460
20°	1460	1424	1427
25°	1430	1384	1390
30°	1393	1346	1343
35°	1357	1302	1292
40°	1314	1258	1244
45°	1270	1214	1195
50°	1223	1167	1139
55°	1173	1113	1087
60°	1117	1049	1027
65°	1056	983	957
70°	978	902	882
75°	870	805	813
80°	740	683	680
85°	537	469	459

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1270 cd/sqm



TEST NUMBER: P918747

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	220.7	2.2
10°-20°	621.0	6.1
20°-30°	912.7	8.9
30°-40°	1060.0	10.4
40°-50°	1058.7	10.4
50°-60°	923.2	9.0
60°-70°	682.4	6.7
70°-80°	386.1	3.8
80°-90°	104.5	1.0
90°-100°	47.9	0.5
100°-110°	178.6	1.7
110°-120°	473.7	4.6
120°-130°	785.6	7.7
130°-140°	834.5	8.2
140°-150°	775.6	7.6
150°-160°	623.5	6.1
160°-170°	401.8	3.9
170°-180°	138.3	1.4
0°-30°	1754.4	17.2
0°-40°	2814.4	27.5
0°-60°	4796.3	46.9
0°-90°	5969.3	58.4
90°-120°	700.2	6.8
90°-150°	3095.8	30.3
90°-180°	4259.0	41.6
0°-180°	10228.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	1	13	21	26	28	9
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	



TEST NUMBER: P918747

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.0	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.2	2153.5	2142.2
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1564.9	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.5	857.0	832.2	825.4
62.5°	811.7	796.0	773.5	751.0	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0



TEST NUMBER: P918747

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8



TEST NUMBER: P918747  
 CATALOG NUMBER: DFN2DIP-4P4F0-070D050US935-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.49	10.43	10.37	11.33	12.48	9.04	9.98	9.92	10.89	12.03
	3H	11.16	12.00	12.05	12.92	14.09	10.67	11.51	11.56	12.43	13.60
	4H	11.75	12.55	12.66	13.47	14.65	11.26	12.06	12.17	12.98	14.16
	6H	12.16	12.90	13.08	13.82	15.02	11.66	12.40	12.58	13.32	14.52
	8H	12.27	12.97	13.20	13.91	15.11	11.77	12.47	12.70	13.41	14.61
	12H	12.32	12.99	13.26	13.93	15.15	11.82	12.48	12.75	13.42	14.64
4H	2H	9.96	10.76	10.87	11.68	12.86	9.60	10.40	10.52	11.32	12.50
	3H	11.84	12.50	12.76	13.45	14.65	11.43	12.10	12.36	13.05	14.24
	4H	12.56	13.17	13.50	14.11	15.33	12.14	12.74	13.07	13.69	14.91
	6H	13.09	13.61	14.03	14.58	15.80	12.65	13.18	13.60	14.15	15.37
	8H	13.24	13.73	14.19	14.69	15.93	12.80	13.29	13.75	14.25	15.49
	12H	13.32	13.76	14.29	14.74	15.98	12.87	13.31	13.84	14.29	15.53
8H	4H	12.76	13.25	13.72	14.22	15.45	12.39	12.88	13.34	13.84	15.08
	6H	13.41	13.81	14.38	14.81	16.05	13.02	13.43	14.00	14.43	15.67
	8H	13.63	13.99	14.62	14.98	16.23	13.24	13.60	14.22	14.59	15.84
	12H	13.77	14.09	14.76	15.07	16.37	13.36	13.68	14.35	14.66	15.96
12H	4H	12.75	13.20	13.72	14.18	15.42	12.39	12.83	13.36	13.81	15.05
	6H	13.44	13.80	14.42	14.79	16.04	13.06	13.42	14.05	14.42	15.67
	8H	13.69	14.00	14.68	14.99	16.29	13.31	13.62	14.30	14.61	15.91