

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905350

Luminaire Tested: DFN2DIP-HX3F0-070D050US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905350
REPORT IS A COMBINATION OF REPORTS P899237 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D050US835-FLLFL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11355.0 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 105.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905350

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905350

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89		77	77	77		66
1	100	96	92	88	94	90	86	83	79	76	74		68	66	65		59
2	91	84	77	72	85	79	73	68	69	65	61		60	57	54		52
3	83	74	66	60	78	69	63	57	61	56	51		53	49	46		46
4	76	65	57	51	71	61	54	49	54	48	44		47	43	39		41
5	70	58	50	44	65	55	47	42	48	42	38		42	38	34		37
6	65	52	44	38	60	49	42	36	44	38	33		38	34	30		33
7	60	47	39	33	56	45	37	32	40	34	29		35	30	26		31
8	56	43	35	30	52	41	33	28	36	30	26		32	27	24		28
9	52	39	32	27	48	37	30	25	33	27	23		30	25	21		26
10	48	36	29	24	45	34	28	23	31	25	21		27	23	19		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3155	3155	3155
5°	3159	3109	3130
10°	3132	3065	3086
15°	3084	3012	3018
20°	3020	2940	2949
25°	2957	2854	2869
30°	2878	2774	2767
35°	2803	2679	2660
40°	2711	2584	2558
45°	2619	2488	2453
50°	2518	2388	2333
55°	2413	2272	2221
60°	2293	2134	2093
65°	2163	1991	1942
70°	1997	1817	1779
75°	1767	1607	1627
80°	1490	1341	1339
85°	1057	888	869

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2619 cd/sqm

TEST NUMBER: P905350

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	2.3
10°-20°	721.3	6.4
20°-30°	1060.0	9.3
30°-40°	1231.1	10.8
40°-50°	1229.6	10.8
50°-60°	1072.2	9.4
60°-70°	792.6	7.0
70°-80°	448.4	3.9
80°-90°	122.9	1.1
90°-100°	97.8	0.9
100°-110°	310.9	2.7
110°-120°	532.1	4.7
120°-130°	699.7	6.2
130°-140°	785.4	6.9
140°-150°	770.2	6.8
150°-160°	646.1	5.7
160°-170°	428.5	3.8
170°-180°	149.8	1.3
0°-30°	2037.7	17.9
0°-40°	3268.8	28.8
0°-60°	5570.6	49.1
0°-90°	6934.5	61.1
90°-120°	940.8	8.3
90°-150°	3196.2	28.1
90°-180°	4421.0	38.9
0°-180°	11355.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	120
90°	1	17	47	44	45	11
95°	70	83	85	85	83	77
105°	287	291	294	296	296	303
115°	534	542	539	538	534	528
125°	777	788	785	780	779	694
135°	1004	1019	1022	1021	1017	776
145°	1220	1229	1237	1238	1233	762
155°	1394	1398	1402	1409	1405	642
165°	1517	1516	1516	1525	1518	428
175°	1578	1575	1572	1581	1573	150
180°	1581	1581	1581	1581	1581	

TEST NUMBER: P905350

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	1.4	17.2	46.7	43.9	45.3
92.5°	29.6	40.0	41.5	42.9	42.9
95°	69.6	83.0	85.3	85.3	83.0
97.5°	115.8	128.2	133.5	133.5	133.5
100°	169.2	180.2	184.0	184.0	182.6
102.5°	225.5	233.6	238.8	240.3	238.8
105°	287.0	290.8	293.7	296.0	296.0
107.5°	348.0	353.7	353.7	354.7	348.0
110°	407.1	414.8	414.8	414.8	410.9



TEST NUMBER: P905350

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.0	479.1	477.7	473.9	471.0
115°	533.9	541.6	539.2	537.8	533.9
117.5°	596.4	606.9	600.2	596.4	592.6
120°	659.3	669.8	659.3	659.3	655.0
122.5°	716.5	729.9	723.2	719.4	716.5
125°	776.6	788.5	784.7	780.4	779.0
127.5°	835.2	850.0	844.8	839.0	835.2
130°	890.1	907.2	904.8	902.0	896.7
132.5°	951.6	964.9	965.9	959.2	955.4
135°	1004.5	1019.2	1022.1	1020.7	1016.9
137.5°	1063.6	1075.5	1077.9	1076.9	1071.2
140°	1115.5	1127.5	1134.1	1134.1	1128.9
142.5°	1168.9	1180.9	1184.7	1186.1	1180.9
145°	1219.5	1229.0	1236.6	1238.1	1232.8
147.5°	1264.8	1276.7	1282.4	1284.8	1279.5
150°	1311.5	1319.6	1324.8	1329.1	1324.8
152.5°	1353.0	1361.1	1367.7	1373.0	1367.7
155°	1394.4	1398.2	1402.5	1409.2	1404.9
157.5°	1430.2	1433.0	1435.4	1445.0	1438.3
160°	1462.1	1465.0	1466.4	1474.5	1468.8
162.5°	1491.7	1491.7	1493.1	1502.2	1495.5
165°	1517.0	1515.5	1515.5	1525.1	1518.4
167.5°	1539.8	1535.5	1535.5	1545.1	1538.4
170°	1557.0	1553.2	1551.8	1561.3	1553.2
172.5°	1568.9	1565.1	1563.7	1573.2	1565.1
175°	1578.5	1574.6	1571.8	1581.3	1573.2
177.5°	1583.7	1579.9	1577.0	1585.1	1577.0
180°	1581.3	1581.3	1581.3	1581.3	1581.3

TEST NUMBER: P905350

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.18	13.15	13.04	14.03	15.13	11.75	12.72	12.61	13.60	14.71
	3H	13.84	14.71	14.71	15.60	16.73	13.37	14.25	14.24	15.13	16.26
	4H	14.43	15.25	15.31	16.15	17.29	13.96	14.79	14.85	15.68	16.82
	6H	14.83	15.59	15.73	16.49	17.64	14.36	15.12	15.26	16.02	17.17
	8H	14.93	15.66	15.84	16.58	17.73	14.47	15.19	15.37	16.11	17.26
	12H	14.98	15.67	15.89	16.58	17.76	14.51	15.20	15.42	16.11	17.29
4H	2H	12.65	13.48	13.54	14.37	15.51	12.31	13.13	13.20	14.03	15.17
	3H	14.52	15.21	15.42	16.13	17.29	14.13	14.82	15.03	15.74	16.90
	4H	15.23	15.86	16.15	16.78	17.96	14.83	15.46	15.74	16.38	17.56
	6H	15.75	16.29	16.67	17.23	18.42	15.34	15.88	16.27	16.83	18.01
	8H	15.90	16.40	16.82	17.34	18.54	15.49	16.00	16.42	16.93	18.13
	12H	15.97	16.43	16.92	17.38	18.59	15.55	16.01	16.50	16.97	18.17
8H	4H	15.44	15.94	16.36	16.88	18.08	15.08	15.58	16.01	16.52	17.72
	6H	16.06	16.48	17.02	17.46	18.66	15.70	16.12	16.66	17.10	18.30
	8H	16.28	16.65	17.24	17.62	18.83	15.91	16.29	16.88	17.26	18.47
	12H	16.41	16.74	17.38	17.70	18.96	16.03	16.36	17.00	17.32	18.58
12H	4H	15.43	15.88	16.37	16.84	18.04	15.08	15.53	16.02	16.49	17.69
	6H	16.09	16.46	17.06	17.43	18.65	15.74	16.11	16.71	17.09	18.30
	8H	16.33	16.66	17.30	17.62	18.89	15.98	16.31	16.95	17.27	18.53