

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905373

Luminaire Tested: DFN2DIP-HX3F0-080D040US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905373
REPORT IS A COMBINATION OF REPORTS P900746 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-080D040US835-RLLONL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10760.0 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 109.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905373

CATALOG NUMBER: DFN2DIP-HX3F0-080D040US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905373

CATALOG NUMBER: DFN2DIP-HX3F0-080D040US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3830	3830	3830
5°	3834	3766	3791
10°	3795	3690	3666
15°	3741	3565	3473
20°	3670	3395	3237
25°	3597	3204	3010
30°	3500	3009	2722
35°	3405	2799	2469
40°	3309	2582	2180
45°	3196	2342	1918
50°	3080	2100	1661
55°	2959	1841	1416
60°	2818	1572	1163
65°	2656	1297	1044
70°	2459	1042	942
75°	2212	913	853
80°	1854	757	732
85°	1267	493	538

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3196 cd/sqm

TEST NUMBER: P905373

CATALOG NUMBER: DFN2DIP-HX3F0-080D040US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.9	2.9
10°-20°	850.7	7.9
20°-30°	1194.3	11.1
30°-40°	1301.9	12.1
40°-50°	1196.6	11.1
50°-60°	939.7	8.7
60°-70°	611.7	5.7
70°-80°	314.9	2.9
80°-90°	82.8	0.8
90°-100°	44.5	0.4
100°-110°	165.9	1.5
110°-120°	440.1	4.1
120°-130°	729.9	6.8
130°-140°	775.4	7.2
140°-150°	720.6	6.7
150°-160°	579.4	5.4
160°-170°	373.3	3.5
170°-180°	128.5	1.2
0°-30°	2354.9	21.9
0°-40°	3656.8	34.0
0°-60°	5793.1	53.8
0°-90°	6802.4	63.2
90°-120°	650.5	6.0
90°-150°	2876.4	26.7
90°-180°	3958.0	36.8
0°-180°	10760.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3306	3306	3306	3306	3306	
5°	3306	3292	3252	3279	3270	314
15°	3145	3112	3010	2953	2924	886
25°	2855	2759	2561	2439	2394	1313
35°	2460	2307	2044	1855	1789	1540
45°	2011	1810	1496	1284	1212	1553
55°	1529	1296	972	793	736	1366
65°	1032	790	521	419	410	1024
75°	550	341	239	218	216	582
85°	129	66	57	57	57	148
90°	1	12	20	24	26	10
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P905373

CATALOG NUMBER: DFN2DIP-HX3F0-080D040US835-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3306.4	3306.4	3306.4	3306.4	3306.4
2.5°	3321.3	3306.4	3273.4	3303.5	3297.5
5°	3306.4	3291.5	3252.4	3279.4	3270.5
7.5°	3279.4	3261.6	3219.7	3231.5	3216.5
10°	3243.5	3222.6	3162.9	3153.7	3135.9
12.5°	3198.8	3171.8	3090.8	3073.0	3040.0
15°	3144.8	3111.8	3010.2	2953.4	2923.5
17.5°	3081.9	3034.0	2908.3	2842.6	2794.6
20°	3010.2	2950.2	2800.7	2726.1	2660.0
22.5°	2932.4	2863.5	2689.9	2588.3	2543.5
25°	2854.6	2758.8	2561.3	2438.8	2393.7
27.5°	2761.9	2660.0	2441.6	2301.0	2232.1
30°	2663.2	2549.2	2309.9	2157.5	2076.5
32.5°	2567.3	2429.6	2184.5	2004.8	1929.9
35°	2459.7	2307.0	2043.8	1855.3	1789.2
37.5°	2354.9	2190.2	1912.1	1705.4	1630.8
40°	2244.2	2064.8	1774.3	1561.9	1484.1
42.5°	2130.5	1939.1	1636.8	1415.3	1340.6
45°	2010.8	1810.2	1496.2	1283.5	1211.8
47.5°	1897.2	1684.8	1361.6	1148.9	1083.2
50°	1771.4	1559.1	1229.9	1023.2	960.6
52.5°	1648.6	1424.1	1104.1	906.7	849.9
55°	1528.9	1295.6	972.4	793.0	736.2
57.5°	1406.4	1167.0	855.9	688.3	640.3
60°	1280.6	1041.3	733.0	580.6	532.7
62.5°	1158.1	918.7	628.3	484.8	461.0
65°	1032.4	789.8	520.6	419.1	409.8
67.5°	912.7	670.2	419.1	367.9	359.1
70°	787.0	553.7	347.0	317.1	305.1
72.5°	667.3	445.7	290.2	266.4	260.3
75°	550.5	341.0	239.4	218.4	215.6
77.5°	434.0	242.2	188.6	176.5	170.5
80°	326.0	173.7	143.5	131.7	131.7
82.5°	227.3	116.8	98.7	92.7	92.7
85°	128.6	65.7	56.8	56.8	56.8
87.5°	47.9	23.8	23.8	21.0	21.0
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1

TEST NUMBER: P905373

CATALOG NUMBER: DFN2DIP-HX3F0-080D040US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P905373

CATALOG NUMBER: DFN2DIP-HX3F0-080D040US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.92	13.87	13.76	14.73	15.80	8.90	9.85	9.74	10.71	11.78
	3H	14.60	15.45	15.46	16.32	17.42	10.09	10.94	10.95	11.81	12.91
	4H	15.21	16.01	16.08	16.89	18.00	10.54	11.35	11.42	12.22	13.33
	6H	15.63	16.37	16.51	17.25	18.37	10.87	11.61	11.75	12.49	13.61
	8H	15.76	16.46	16.65	17.36	18.48	10.96	11.66	11.85	12.56	13.68
	12H	15.82	16.49	16.72	17.38	18.53	11.00	11.67	11.90	12.57	13.71
4H	2H	12.95	13.76	13.83	14.63	15.74	9.50	10.31	10.38	11.18	12.29
	3H	14.79	15.45	15.67	16.36	17.48	10.86	11.53	11.75	12.43	13.56
	4H	15.48	16.08	16.37	16.99	18.14	11.41	12.01	12.31	12.92	14.07
	6H	15.99	16.51	16.90	17.44	18.59	11.83	12.35	12.74	13.28	14.43
	8H	16.16	16.65	17.08	17.57	18.74	11.96	12.45	12.87	13.37	14.53
	12H	16.26	16.70	17.19	17.64	18.81	12.03	12.46	12.96	13.40	14.58
8H	4H	15.45	15.94	16.37	16.86	18.03	11.69	12.18	12.61	13.10	14.27
	6H	16.01	16.42	16.96	17.38	18.55	12.21	12.61	13.15	13.58	14.74
	8H	16.23	16.58	17.18	17.54	18.72	12.40	12.75	13.35	13.71	14.89
	12H	16.36	16.68	17.32	17.62	18.86	12.52	12.83	13.47	13.78	15.01
12H	4H	15.41	15.85	16.34	16.79	17.96	11.70	12.14	12.64	13.08	14.25
	6H	15.99	16.35	16.94	17.30	18.48	12.26	12.61	13.21	13.57	14.75
	8H	16.21	16.52	17.16	17.47	18.70	12.47	12.78	13.42	13.73	14.96

END OF REPORT