

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921372

Luminaire Tested: DFN2DIP-4P4F0-030D030US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921372
REPORT IS A COMBINATION OF REPORTS P899080 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-030D030US940-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4641.3 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 50.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921372
CATALOG NUMBER: DFN2DIP-4P4F0-030D030US940-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P921372

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31				31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	717	717	717
5°	718	706	711
10°	711	693	688
15°	702	670	652
20°	689	638	609
25°	676	603	566
30°	658	567	513
35°	640	528	466
40°	623	488	412
45°	602	444	363
50°	581	399	315
55°	559	350	269
60°	533	300	222
65°	503	249	200
70°	468	201	181
75°	422	178	166
80°	358	150	145
85°	250	101	110

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 642 cd/sqm



TEST NUMBER: P921372

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	2.2
10°-20°	284.5	6.1
20°-30°	399.4	8.6
30°-40°	435.3	9.4
40°-50°	400.1	8.6
50°-60°	314.2	6.8
60°-70°	204.5	4.4
70°-80°	105.3	2.3
80°-90°	29.3	0.6
90°-100°	52.3	1.1
100°-110°	166.3	3.6
110°-120°	284.7	6.1
120°-130°	374.4	8.1
130°-140°	420.2	9.1
140°-150°	412.1	8.9
150°-160°	345.7	7.4
160°-170°	229.2	4.9
170°-180°	80.1	1.7
0°-30°	787.5	17.0
0°-40°	1222.8	26.3
0°-60°	1937.2	41.7
0°-90°	2276.3	49.0
90°-120°	503.4	10.8
90°-150°	1710.0	36.8
90°-180°	2365.0	51.0
0°-180°	4641.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1106	1101	1088	1097	1094	105
15°	1052	1040	1007	988	978	296
25°	955	922	856	816	800	439
35°	822	771	683	620	598	515
45°	672	605	500	429	405	519
55°	511	433	325	265	246	457
65°	345	264	174	140	137	342
75°	184	114	80	73	72	195
85°	43	22	19	19	19	49
90°	1	9	25	24	24	5
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	



TEST NUMBER: P921372

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1105.6	1105.6	1105.6	1105.6	1105.6
2.5°	1110.6	1105.6	1094.6	1104.7	1102.7
5°	1105.6	1100.6	1087.6	1096.6	1093.6
7.5°	1096.6	1090.7	1076.7	1080.6	1075.6
10°	1084.6	1077.6	1057.7	1054.5	1048.7
12.5°	1069.6	1060.6	1033.6	1027.6	1016.5
15°	1051.6	1040.5	1006.6	987.6	977.6
17.5°	1030.5	1014.6	972.5	950.6	934.5
20°	1006.6	986.5	936.5	911.6	889.5
22.5°	980.6	957.5	899.5	865.5	850.5
25°	954.6	922.5	856.5	815.5	800.4
27.5°	923.5	889.5	816.5	769.5	746.4
30°	890.6	852.5	772.4	721.5	694.4
32.5°	858.4	812.4	730.5	670.4	645.3
35°	822.5	771.4	683.4	620.4	598.3
37.5°	787.5	732.4	639.4	570.2	545.4
40°	750.5	690.5	593.3	522.3	496.3
42.5°	712.4	648.5	547.3	473.2	448.3
45°	672.4	605.3	500.3	429.2	405.2
47.5°	634.4	563.4	455.3	384.1	362.2
50°	592.4	521.3	411.3	342.1	321.2
52.5°	551.3	476.3	369.3	303.2	284.2
55°	511.2	433.2	325.1	265.2	246.2
57.5°	470.3	390.2	286.2	230.2	214.1
60°	428.2	348.2	245.1	194.1	178.2
62.5°	387.3	307.2	210.1	162.1	154.2
65°	345.2	264.1	174.1	140.1	137.1
67.5°	305.2	224.1	140.1	123.1	120.0
70°	263.1	185.1	116.0	106.0	102.0
72.5°	223.1	149.0	97.0	89.1	87.0
75°	184.0	114.0	80.1	73.0	72.1
77.5°	145.1	81.0	63.0	59.0	57.0
80°	109.1	58.1	48.0	44.1	44.1
82.5°	76.0	39.1	33.0	31.0	31.0
85°	43.0	21.9	19.0	19.0	19.0
87.5°	16.1	7.9	7.9	7.0	7.0
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9



TEST NUMBER: P921372

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1



TEST NUMBER: P921372
 CATALOG NUMBER: DFN2DIP-4P4F0-030D030US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.92	6.74	6.89	7.72	9.01	1.88	2.70	2.85	3.69	4.97
	3H	7.60	8.34	8.58	9.33	10.64	3.07	3.81	4.05	4.80	6.11
	4H	8.21	8.91	9.21	9.90	11.22	3.52	4.22	4.52	5.21	6.53
	6H	8.64	9.28	9.65	10.28	11.61	3.84	4.48	4.85	5.48	6.81
	8H	8.77	9.38	9.78	10.39	11.72	3.93	4.54	4.95	5.56	6.89
	12H	8.83	9.41	9.85	10.42	11.77	3.98	4.56	5.00	5.57	6.92
4H	2H	5.94	6.63	6.94	7.63	8.94	2.48	3.17	3.48	4.17	5.49
	3H	7.77	8.35	8.78	9.37	10.70	3.83	4.41	4.84	5.43	6.76
	4H	8.47	9.00	9.49	10.01	11.37	4.38	4.91	5.40	5.92	7.28
	6H	8.99	9.44	10.02	10.48	11.83	4.80	5.25	5.83	6.29	7.64
	8H	9.17	9.59	10.20	10.62	11.99	4.93	5.35	5.96	6.39	7.75
	12H	9.26	9.65	10.31	10.69	12.06	5.00	5.38	6.04	6.42	7.80
8H	4H	8.43	8.86	9.47	9.89	11.26	4.66	5.08	5.69	6.12	7.48
	6H	9.01	9.36	10.06	10.43	11.79	5.18	5.53	6.24	6.61	7.97
	8H	9.23	9.54	10.29	10.59	11.98	5.38	5.68	6.44	6.74	8.12
	12H	9.37	9.64	10.44	10.69	12.12	5.50	5.77	6.56	6.82	8.25
12H	4H	8.39	8.77	9.44	9.82	11.19	4.67	5.05	5.72	6.10	7.47
	6H	8.98	9.29	10.04	10.35	11.73	5.23	5.54	6.30	6.60	7.98
	8H	9.21	9.48	10.27	10.53	11.96	5.45	5.72	6.51	6.77	8.20